

FUJIFILM

DIGITAL CAMERA  
*FinePix* **A600 · A700**

6.3 MegaPixels (A600)

7.3 MegaPixels (A700)

3x Optical Zoom

2.4 inch LCD



Picture those Unforgettable Moments – Beautifully!



7.3 MegaPixels **A700**



6.3 MegaPixels **A600**

# High-performance Super CCD HR for images that beg to be enlarged

Fujifilm's high-performance Super CCD HR delivers exceptional image quality. Teamed with the precision optics of the Fujinon zoom lens, this sophisticated digital imaging technology gives you crisp, high-resolution pictures, with vivid detail and vibrant, true-to-life color, perfect for enlarged photo prints.



## Large, high-resolution LCD monitor

The large (2.4"), high-resolution (112,000 pixel) LCD monitor is housed in an attractive metallic-finish body that combines orthodox camera design with sleek, modern accents. The bright, sharp LCD lets you compose your photos with ease in all kinds of lighting conditions. And its generous size adds to the pleasure of sharing photo playback with family and friends.



Simulated LCD display image

## Full-featured, easy to use

The FinePix A600 & A700 are amazingly easy to operate: just switch on the power and you're ready to shoot. Controls have been arrayed for one-handed operation, eliminating the need to fumble with numerous buttons. The full range of functions includes a 3x optical zoom, a selection of convenient scene positions, enhanced macro mode, and slow synchro flash. You can even view your photos in 3:2 aspect to ensure that all the elements of your picture are included in your prints.



Macro Shooting



Scene Position (Sport)



3:2 Format

## Additional features

- Continuous shooting mode (A600 only)
- Internal memory (approx. 12MB)
- QVGA movie recording (10fps) with monaural sound
- Video output for TV monitor (NTSC / PAL)
- USB digital interface
- PictBridge compatible
- Multi-language LCD monitor
- xD-Picture Card™ compatible

Exif Print

PictBridge

## Specifications

Model	FinePix A600	FinePix A700
Number of effective pixels*	6.3 million pixels	7.3 million pixels
CCD sensor	1/1.7 inch Super CCD HR	1/1.6-inch Super CCD HR
Number of recorded pixels	Still image: 2,848 × 2,136 / 3,024 × 2,016 / 2,048 × 1,536 / 1,600 × 1,200 / 640 × 480 pixels Movie: 320 × 240 / 160 × 120 pixels (10 frames/sec.)	Still image: 3,072 × 2,304 / 3,264 × 2,172 / 2,304 × 1,728 / 1,600 × 1,200 / 640 × 480 pixels
Storage media	Internal memory (approx. 12MB) / xD-Picture Card™ (16MB – 2GB)	
File format	Still image: JPEG (Exif Ver. 2.2**) / Movie: AVI (Motion JPEG) [Design rule for Camera File system compliant / DPOF-compatible]	
Lens	Fujinon 3.0x Optical zoom lens, F2.8 – F5.2	
Lens focal length	F = 8.0 mm – 24.0 mm (Equivalent to 36 – 108 mm on a 35 mm camera)	
Focus	Auto Focus	
Focus distance	Normal: Approx. 50 cm / 1.6 ft. to infinity Macro: Approx. 10 cm – 80 cm / 3.9 in. – 2.6 ft.	
Shutter speed	2 sec. to 1/1600 sec. (depend on Exposure mode)	
Aperture	Wide-angle: F2.8 – F8, Telephoto: F5.2 – F14	
Sensitivity	AUTO (Equivalent to ISO 100 / 200 / 400)	
Exposure control	64-zone TTL metering	
Exposure mode	Programmed AE (Exposure compensation in manual mode)	
White balance	Automatic scene recognition / Preset (Fine, Shade, Fluorescent (Daylight), Fluorescent (Warm White), Fluorescent (Cool White), Incandescent)	
LCD monitor	2.4 inches, Aspect ratio: 4:3; 112,000 pixels Amorphous silicon TFT, Approx. 91% coverage	
Flash	Auto flash Effective range: Wide-angle (Approx. 0.5 m – 3.8 m / 1.6 ft. – 12.5 ft.) Telephoto (Approx. 0.6 m – 2.0 m / 2.0 ft. – 6.6ft.) Macro (Approx. 0.3 m – 0.8 m / 1.0 ft. – 2.6 ft.) Flash mode: Auto, Red-eye Reduction, Forced Flash, Suppressed Flash, Slow Synchro, Red-eye Reduction + Slow Synchro	
Self-timer	Approx. 10 sec./2 sec. delay	
Video output	NTSC/PAL selectable	
Digital interface	USB	
Power source	2 × AA-size Alkaline / Ni-MH battery (optional), AC power adapter AC-3VX (optional)	
Dimensions	93.0 (W) × 60.0 (H) × 30.1 (D) mm / 3.7 (W) × 2.4 (H) × 1.2 (D) in.	
Weight	Approx. 136 g / 4.8 oz.	Approx. 139 g / 4.9 oz.
	(excluding accessories, batteries and xD-Picture Card™)	
Camera functions		
Digital zoom	Approx. 6.2x (3x optical zoom lens is used together; Max. zoom scale: 18.6x)	Approx. 6.3x (3x optical zoom lens is used together; Max. zoom scale: 18.9x)
Shooting modes	Auto, Scene Position (Portrait, Landscape, Sport, Night Scene) Continuous shooting mode (A600 only)	
Movie recording	320 × 240 pixels: 10 frames/sec. 160 × 120 pixels: 10 frames/sec.	
Playback	Single frame, Trimming, Automatic playback, 9Multi-frame playback	
Copying image data	Copy image data between xD-Picture Card™ and internal memory; single-frame or all-frame selectable	
Optional accessories	xD-Picture Card™: 16MB, 32MB, 64MB, 128MB, 256MB, 512MB, 1GB, 2GB PC Card Adapter DPC-AD CompactFlash™ Card Adapter DPC-CF AC Power Adapter AC-3VX (Cannot be used as a battery charger for this model) Rechargeable Battery 2HR-3UF (2 × AA-size Ni-MH) Battery Charger with Battery (2 × AA-size Ni-MH) BK-NH2/BK-NH Soft Case SC-FXA03/SC-FXA04	

Accessory availability may vary by country. Please check with your local Fujifilm representative to confirm product availability.

\* Number of effective pixels: The number of pixels on the image sensor which receive input light through the optical lens, and which are effectively reflected in the final output data of the still image.

\*\* Exif 2.2 is a newly revised digital camera file format that contains a variety of shooting information for optimal printing.

Specifications are subject to change without notice.

xD-Picture Card™ and all other trademarks are the property of their respective holders.

## Number of images/recording time

Modesty	Still image						Movie	
	6M (Fine)	6M(Normal)	3:2 Format	3M	2M	0.3M	320	160
Quality	2848×2136	2848×2136	3024×2016	2048×1536	1600×1200	640×480	320×240 (10 fps)	160×120 (10 fps)
Number of recorded pixels	2848×2136	2848×2136	3024×2016	2048×1536	1600×1200	640×480	320×240 (10 fps)	160×120 (10 fps)
Internal Memories (12MB)	3	7	7	15	19	93	Approx. 71 sec.	Approx. 220 sec.
DPC-16 (16MB)	5	10	10	19	25	122	Approx. 94 sec.	Approx. 4.8 min.
DPC-32 (32MB)	10	20	20	40	50	247	Approx. 189 sec.	Approx. 9.7 min.
DPC-64 (64MB)	21	42	42	81	101	497	Approx. 6.4 min.	Approx. 19.5 min.
DPC-128 (128MB)	42	84	84	162	204	997	Approx. 12.7 min.	Approx. 3.9 min.
DPC-256 (256MB)	85	169	169	325	409	1997	Approx. 25.5 min.	Approx. 78.2 min.
DPC-512 (512MB)	170	339	339	651	818	3993	Approx. 51 min.	Approx. 156.3 min.
DPC-1GB (1GB)	341	680	680	1305	1639	7995	Approx. 102.1 min.	Approx. 313 min.
DPC-M2GB (2GB)	680	1360	1360	2558	3198	15992	Approx. 204.18 min.	Approx. 626.5 min.

Modesty	Still image						Movie	
	7M (Fine)	7M(Normal)	3:2 Format	4M	2M	0.3M	320	160
Quality	3072×2304	3072×2304	3264×2172	2304×1728	1600×1200	640×480	320×240 (10 fps)	160×120 (10 fps)
Number of recorded pixels	3072×2304	3072×2304	3264×2172	2304×1728	1600×1200	640×480	320×240 (10 fps)	160×120 (10 fps)
Internal Memories (12MB)	3	6	6	11	19	93	Approx. 71 sec.	Approx. 220 sec.
DPC-16 (16MB)	4	8	8	15	25	122	Approx. 94 sec.	Approx. 4.8 min.
DPC-32 (32MB)	8	17	17	31	50	247	Approx. 189 sec.	Approx. 9.7 min.
DPC-64 (64MB)	18	36	35	64	101	497	Approx. 6.4 min.	Approx. 19.5 min.
DPC-128 (128MB)	36	72	72	128	204	997	Approx. 12.7 min.	Approx. 3.9 min.
DPC-256 (256MB)	73	146	145	257	409	1997	Approx. 25.5 min.	Approx. 78.2 min.
DPC-512 (512MB)	146	292	290	515	818	3993	Approx. 51 min.	Approx. 156.3 min.
DPC-1GB (1GB)	294	586	581	1031	1639	7995	Approx. 102.1 min.	Approx. 313 min.
DPC-M2GB (2GB)	586	1162	1162	2065	3198	15992	Approx. 204.18 min.	Approx. 626.5 min.

The number of images and recording time will vary slightly depending on the type of subject.

For more information on the full range of Fujifilm digital products, please visit our Website:  
<http://www.fujifilm.com/products/digital>

**FUJIFILM**

FUJIFILM Corporation

26-30, NISHIAZABU 2-CHOME, MINATO-KU, TOKYO 106-8620, JAPAN