

INSTAX MINI 55i SPECIFICATIONS

Film:	Fujifilm Instant Color Film "instax mini"
Picture size:	62 X 46mm
Lens:	Move in/out type Fujinon Lens, 2 components, 2 elements, f=60mm, 1:12.7
Viewfinder:	Real image finder, 0.37X, with target spot
Focusing:	Motor-driven 2-range switching: 0.6 - 3m / 3m - ∞, Shooting range: 0.6m - ∞, Landscape Mode (3m - ∞)
Shutter Release:	Programmed electronic shutter release, 1/3 - 1/400 sec. shutter speeds, 2 shutter release buttons (vertical shooting/ horizontal shooting)
Exposure control:	Automatic, Interlocking range (ISO 800): LV5.0 - LV15.5, Exposure compensation (Lighten-Darken Control): ±2/3EV
Shutter Release:	Programmed electronic shutter release, 1/3 - 1/400 sec. shutter speeds, 2 shutter release buttons (vertical shooting/ horizontal shooting)
Exposure control:	Automatic, Interlocking range (ISO 800): LV5.0 - LV15.5, Exposure compensation (Lighten-Darken Control): ±2/3EV
Film Feeding Out Automatic	
Flash:	Built-in, Automatic electronic flash, Auto mode (Intelligent Flash for Brighter Backgrounds), Fill-in Flash Mode, 0.2 - 5sec. recycle time (when new batteries are used), with flashcharging lamp (red), effective flash lamp range: 0.6 - 3 m
Self-timer:	Electronically controlled, approx. 10 second delay, Continuous shooting mode, can be stopped mid-run
Liquid Crystal Display (LCD):	Exposure counter (number of unexposed films), Landscape Mode, lighten-darken control, Fill-in Flash Mode, Self-timer Mode (1 frame / 2 frames continuous shooting)
Power Supply:	Two CR2/DL CR2 lithium batteries, Capacity: 30 film packs (Based on our test conditions)
Others:	With film pack confirmation window, tripod socket, stylish illumination indicators
Dimensions & Weight:	112.0 X 96.5 X 49.5 mm 275g (without batteries, strap and film pack)

Specifications are subject to change without notice.