

FUJIFILM MICROFILM

Product Category	Application	Type	Prod. Code	Order Unit	Film Speed	Resolution (lines/mm)	Size	Film Base	Packaging		
Source Document Microfilms	A medium-speed film for producing ultra-high resolution images in rotary and planetary microfilmers.	FUJI Microfilm Negative Super HR	HR-21	14517556	100 rolls	Medium	850	16mm x 30.5M	PET-125μ	Pl. S pool	
		"	HR-23	14517594	100 rolls	"	"	16mm x 40M	PET-100μ	"	
		"	HR-38	14517611	100 rolls	"	"	16mm x 65.5M	PET-63μ	"	
			"	HR-20	14517647	50 rolls	"	"	35mm x 30.5M	PET-125μ	Pl. S pool
			"	HR-19	14517659	50 rolls	"	"	35mm x 40M	PET-100μ	"
	Pre-exposed HR-40 Control Strips is used for film processing control.	FUJI Control Strips	HR-40	14342391	Roll	"	"	16mm x 30.5M	PET-125μ	Pl. S pool	
	FUJI HR-II Films are suited for documents which have lower contrast such as pictures, colored books, and aged historical documents.	FUJI Microfilm Negative HR II	PT-21	14184579	100 rolls	Medium	850	16mm x 30.5M	PET-125μ	Pl. S pool	
A-38			14184608	100 rolls	"	"	16mm x 65.5M	PET-63μ	"		
		"	PT-20	14184153	50 rolls	"	"	35mm x 30.5M	PET-125μ	Pl. S pool	
		"	PT-19	14183551	50 rolls	"	"	35mm x 40M	PET-100μ	"	
A-50 film is used for Microfiche Application.	FUJI Microfiche Film HR II NP	A-50	10505775	100 sheets	"	"	10.5 x 14.8cm	PET-175μ			
Duplicating Microfilms	Silver reverse -image films used for making contact prints from camera microfilms and duplicate microfilms.	FUJI Mini Posi Film		14661668	20 rolls	Contact Speed	380	16mm x 305M	PET-100μ	T-Core	
		"		10856227	10 rolls	"	"	35mm x 305M	PET-100μ	K-Core	
	Silver direct-image films used for making contact prints from camera microfilms and duplicate microfilms.	FUJI Direct Duplicating Microfilm	DD-11	14659275	20 rolls	Contact Speed	1200	16mm x 310M	PET-100μ	Z-Core	
			DD-12	14659287	10 rolls	"	"	16mm x 488M	PET-100μ	Z-Core	
		"	DD-13	14645339	10 rolls	"	"	16mm x 762.5M	PET-63μ	Z-Core	
		"	DD-31	14645298	10 rolls	"	"	35mm x 310M	PET-100μ	U-Core	
Color Microfilm	Reversal-type color microfilm, which has high resolution and brilliant color reproduction, is designed for color microfilming of documents and diagrams.	FUJI Color Microfilm Type R II			10 rolls	ISO 100	160	35mm x 30M (No Perforation)	TAC-130μ	Pl. S pool	
Professional Films	Professional Surveillance films are designed for use in surveillance equipment.	FUJI Color Surveillance Film		14971192		ISO 400	Blank	35mm x 30.5M (Double Perforated)	TAC-130μ	Pl. S pool	
	This film produces very sharp images especially for low contrast material such as biological samples.	FUJI Electron Microscopic Film FG		10090603 10090627	100 sheets 100 sheets	Blank	Blank	5.9 x 8.2cm 8.2 x 11.8cm	PET-175μ PET-175μ		