

DIGITAL
VIDEOCASSETTE

D2
Composite Digital

D2001



Outstanding digital video and audio fidelity with FUJIFILM's new 19 mm D2001 metal videocassettes.

At Last, a Videocassette Designed Specifically for Today's Composite Digital VTR Systems.


FUJIFILM's D2001 D-2 videocassettes feature Super-Fine Metallix metal magnetic particles specially formulated to match the Performance characteristics of today's state-of-the-art digital video equipment. This ensures excellent video and audio S/N for improved picture and sound quality.

Our durable tape construction provides stable tape transport over a wide temperature range, delivering the consistent performance that professionals can count on. And thanks to advanced new surface treatment techniques, the tape surface is mirror-smooth for superior tape-to-head contact with minimal head wear.

Ultra-Low Error Rate

To keep the error rate to an absolute minimum, we developed a durable new binder material for our D2001 D-2 videocassettes. And to ensure that the rate stays low even after repeated recording and play-back, we developed a tough new backcoating material. When you consider the strict quality controls we apply at every step in the manufacturing process, it's no wonder that it all adds up to broadcast-grade performance.


Changes in Error Rate after Repeated Playbacks




Extended Still & High-Speed Playback

Extended still capability is offered to meet the critical demands of the editing room, where long pauses and high-speed searches are frequent. Due to the superior quality of our Super-Fine Metallix magnetic particle and binder formulations, decreases in RF output are minimal even after repeated search and pause operations.

Changes in Output Level after Still Playbacks (f=32 MHz)



Changes in Output Level after Repeated Playbacks



FUJIFILM D2001 Digital Videocassette Technical Data

Magnetic Properties	
Coercivity (Hc)	120 kA/m
Retentivity (Br)	265 mT
Physical Properties	
Tape Thickness: Total	12.5 µm
Base	9.4 µm
Magnetic Layer	2.5 µm
Backcoat	0.5 µm
Undercoating Layer	0.1 µm
Tape Width	19,010 mm
Yield Strength	30 N
Breaking Tensile Strength	90 N
Residual Elongation	0.04 %
Performance	
Video RF Output	0 dB*
Video S/N	0 dB*
Audio Sensitivity	0 dB*
Audio Frequency Response	0 dB*

FUJIFILM D2001 Digital Videocassette Line-up

Cassette	Size	Tape Length	Recording Time	Dimensions		Weight (With case)
				Cassette Shell	Case	
S	S - 6	56 ±0.2 m (184 ft.)	6 min.	172 x 109 x 33 mm	196 x 129 x 40 mm	400 g (0.83 lbs.)
	S - 12	103 ±0.2 m (338 ft.)	12 min.			415 g (0.92 lbs.)
	S - 22	183 ±0.2 m (600 ft.)	22 min.			445 g (0.98 lbs.)
	S - 32	262 ±0.2 m (860 ft.)	32 min.			475 g (1.05 lbs.)
M	M - 6	56 ±0.2 m (184 ft.)	6 min.	245 x 150 x 33 mm	284 x 176 x 40 mm	735 g (1.62 lbs.)
	M - 12	103 ±0.2 m (338 ft.)	12 min.			755 g (1.67 lbs.)
	M - 22	183 ±0.2 m (600 ft.)	22 min.			785 g (1.73 lbs.)
	M - 34	277 ±0.2 m (909 ft.)	34 min.			820 g (1.81 lbs.)
	M - 64	515 ±0.2 m (1,690 ft.)	64 min.			905 g (2.00 lbs.)
	M - 94	753 ±0.2 m (2,470 ft.)	94 min.			995 g (2.20 lbs.)
L	L-126	1,041 ±0.2 m (3,416 ft.)	126 min.	366 x 206 x 33 mm	430 x 284 x 51 mm	2,385 g (5.26 lbs.)
	L-156	1,251 ±0.2 m (4,105 ft.)	156 min.			2,500 g (5.51 lbs.)
	L-188	1,505 ±0.2 m (4,938 ft.)	188 min.			2,515 g (5.54 lbs.)
	L-208	1,663 ±0.2 m (5,456 ft.)	208 min.			2,665 g (5.88 lbs.)

Note: Figures are typical values based on Fujifilm's standard measurement procedures. The figures marked with * are comparisons with the Fujifilm reference tape. Specifications are subject to change without notice.



FUJI PHOTO FILM CO., LTD.

26-30, NISHIAZABU 2-CHOME, MINATO-KU, TOKYO 106-8620, JAPAN

Fuji Photo Film U.S.A., Inc.

Magnetic Markets Division 200 Summit Lake Drive, 2nd Floor Valhalla, New York 10595, U.S.A.

Fuji Photo Film Canada Inc.

600 Suffolk Court Mississauga, Ontario, L5R 4G4, Canada

Fuji Photo Film do Brasil Ltda.

Avenida Vereador Jose Diniz 3400, Campo Belo, Sao Paulo, CEP 04604-901, SP, Brasil

Fuji Magnetics G.m.b.H.

Fujistrasse 1, D-47533 Kleve, Germany

Fuji Photo Film (UK) Ltd.

Fuji Film House, 125 Finchley Road, Swiss Cottage, London NW3 6HY, U.K.

FUJIFILM Regional Services (Singapore) Pte Ltd.

10 New Industrial Road Singapore 536201