FUJ:FILM Value from Innovation

ApeosPort[®] Print C3830SD

A4 Colour Printer

Features




High Performance & Productivity

- Fast colour printing of up to 38 ppm, with a first page as fast as 7 seconds.
- Optional 650-sheet duo tray with 100-sheet Multipurpose Feeder and 550-sheet Tray supports high-capacity paper feeding of up to 1,451 sheets.
- Flexible media handling supports cardstock, small media, and envelopes.
- Flexible networking. Gigabit Ethernet capability enables faster communication between the printer and the network, and the optional Wi-Fi kit allows easy wireless connectivity.

Security

- Prevents information leakage with Confidential Print function
- Controls access to the Printer functions
- Supports IC card authentication*. You can easily authenticate without entering Username / Password.
 *Optional
- Supports settings to delete temporary data files in memory & hard disk as an option.





Easy Operation

- Equipped with 4.3-inch colour touch screen. Easy-to-understand and easy-to-use operations such as USB flash drive Print, Secure Print, and Job Verification.
- Compatible with Mopria[®] and AirPrint, you can easily print from mobile devices.
- Easy printing without PC. In addition to USB flash drive Print, Bookmark feature also allows you to print documents* on the server or the website.
 *PDF/TIFF/JPEG

Ecology

- Standard two-sided printing saves paper.
- Supports ECO mode for easy presetting of features that save paper and toner.



Specifications

Printing		
Display	4.3-inch (10.9 cm) Colour touch screen	
Print Speed: Up to	Black: 38 ppm (A4) / Colour: 38 ppm (A4)	
Time to First Page: As fast as ^{*1}	Black: 7 seconds / Colour: 7 seconds	
Print Resolution	Black: 1200 x 1200 dpi, 4800 Colour Quality (2400 x 600 dpi) / Colour: 1200 x 1200 dpi, 4800 Colour Quality (2400 x 600 dpi)	
Memory	1024 MB	
Hard Disk	Option available	
Supplies		
Toner Cartridge Yields (up to)	7,000-page Colour (CMY) Ultra High Yield Cartridges, 10,500-page Black Ultra High Yield Cartridge	
Imaging kit Estimated Yield: Up to	125,000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage	
Cartridge(s) Shipping with Product	2,000-page Colour (CMY) Toner Cartridges, 3,000-page Black Toner Cartridge	
Paper Handling		
Included Paper Handling	250-Sheet Input, 125-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed	
Optional Paper Handling	550-Sheet Tray, 650-Sheet Duo Tray	
Paper Input Capacity: Up to	Standard: 250+1 pages 75 gsm / Maximum: 1450+1 pages 75 gsm	
Paper Output Capacity: Up to	Standard: 125 pages 75 gsm	
Media Types Supported	Card Stock, Envelopes, Paper Labels, Plain Paper, Vinyl Labels	
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Hagaki Card, Letter, B5 Envelope Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope	
General Information		
Standard Ports	USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified port (Type A)	
Wi-Fi	Option available (802.11 a/b/g/n/ac Wireless)	
Noise Level: Operating	Print: 51 dBA	
Specified Operating Environment*2	Humidity: 8 to 80% ^{*3} Relative Humidity, Temperature: 10 to 32°C ^{*4} (excluding faults caused by condensation)	
Size (mm - H x W x D) / Weight (kg)	308 x 442 x 421 mm / 21 kg	

*1: The time from when the device starts the print job from standard sheet tray until the trailing edge of the first page exits into output tray. Numeric value may vary based on the output environment. *2: Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. *3: When the humidity is 80%, the temperature is 25.5°C or less. *4: Humidity 45% or less when the temperature is 32°C.

Options

Product Name	Product Code
550-Sheet Tray	EC104314
650-Sheet Duo Tray	EC104316
Wireless Print Server	EC104320
500 GB Hard Disk	EC104327
Contactless Authentication Device	EC104333

Consumables*1

Conformation			
Product Name	Product Code	Product Life	
Black Ultra High Yield Use & Return Toner Cartridge ^{*2}	CT203466	Up to 10,500 pages	
Cyan Ultra High Yield Use & Return Toner Cartridge ^{*2}	CT203467	Up to 7,000 pages	
Magenta Ultra High Yield Use & Return Toner Cartridge ^{*2}	CT203468	Up to 7,000 pages	
Yellow Ultra High Yield Use & Return Toner Cartridge ^{*2}	CT203469	Up to 7,000 pages	
Black Ultra High Yield Regular Toner Cartridge	CT203512	Up to 10,500 pages	
Cyan Regular Toner Cartridge	CT203513	Up to 7,000 pages	
Magenta Regular Toner Cartridge	CT203514	Up to 7,000 pages	
Yellow Regular Toner Cartridge	CT203515	Up to 7,000 pages	
Black Use and Return Imaging Kit*2	CT300294	Up to 125,000 pages	
Black and Color Use and Return Imaging Kit *2	CT300295	Up to 125,000 pages	
Black Regular Imaging Kit	CT300298	Up to 125,000 pages	
Black and Color Regular Imaging Kit	CT300299	Up to 125,000 pages	
Waste Toner Bottle	CWAA0972	Up to 25,000 pages	
*1. Average continuous black or continuous composite Colour (CMV) declared viold in one cided (cimplex)			

*1: Average continuous black or continuous composite Colour (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798.

*2: The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

For more information or detailed product specification, please call or visit us at

FUJIFILM Business Innovation Australia Pty Ltd

8 Khartoum Road MACQUARIE PARK NSW 2113 Australia

Tel. +61 2 9856 5000

fujifilm.com/fbau

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements. •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort is registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. •Mopria® the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.