



**Fiery® VC11**

**Fiery FS500 Pro**

# Intelligent production to power real business results.

Fiery® VC11, driving the FUJIFILM ApeosPro C810/C750/C650, delivers outstanding performance, intelligent automation, and exceptional image quality.

## Process more high-value jobs, faster

- Meet critical customer turnaround times and increase production capacity with the Fiery VC11, which processes jobs 36% faster than Fiery VC12C.
- Increase efficiency with automation benefits from the built-in, browser-based Fiery JobFlow™ Base.

## Built-in print intelligence

- Maximise printer throughput with built-in Fiery JobExpert™ that analyses print jobs and dynamically chooses the optimal print settings.

## Outstanding output quality

- Fiery Edge™ profiles deliver stunning colour with the smoothest colour blends, maximum shadow details, and superb image definition.
- Built-in Fiery Preflight provides basic preflight checks to help spot file problems before printing.
- Fiery Spot-On™ and Fiery TrueBrand ensure accurate brand colour reproduction, like PANTONE® or custom spot colours - even from Microsoft Office files.
- Add the optional Fiery Graphic Arts Pro Package for advanced spot colour management, correcting colour and images on the fly, and generating soft proofs.
- Ensure consistent, predictable output in an end-to end Adobe® workflow with Adobe PDF Print Engine rendering technology.

## Differentiate with personalisation

- Fiery FreeForm™ Create, an included application, allows you to quickly and simply create personalised jobs for print production. Add variable elements such as text, images, or barcodes with just a few clicks.
- Accepts all VDP formats, like PDF/VT-1 and 2, PPML 3.0, and Creo VPS.

## A unified print room

- Manage all your Fiery Driven™ printers from Fiery Command WorkStation to centralise job management.
- Integrate your print production workflow with management information systems, Web-to-Print systems, and popular prepress workflows for end-to-end automation.
- Easily perform complex document preparation using the intuitive Fiery Impose-Compose and the optional Fiery JobMaster™.



# Fiery® VC11 specifications

## Fiery Driven™ engines

- FUJIFILM Business Innovation ApeosPro C810/C750/C650
- Supports all engine finishing devices

## Hardware and platform

- Fiery® FS500 Pro software
- Intel® Core™ i5-8500 Processor
- SSD boot drive for OS and Fiery software + 1 TB HDD
- 8 GB RAM
- Fiery QuickTouch™ software
- USB 3.0 ports: 2 rear ports, 3 on Fiery QuickTouch panel. USB 2.0: 4 rear ports.
- Microsoft® Windows® 10 IoT Enterprise 2019 LTSC
- Fiery Installer Builder

## Colour and imaging

- FOGRA CERT VPS - FOGRA39, FOGRA51
- Fiery Edge™ colour profiles
- Fiery Ultra Smooth Gradients (1,200 x 1,200 dpi x 10-bit rendering)
- Fiery Spot-On™
- Fiery TrueBrand
- PANTONE® Color Enabled
- Fiery Calibrator
- Composite overprint
- Image smoothing
- Image enhance
- Fiery Image Enhance Visual Editor

## Performance

- SmartRIP
- Spool-RIP-Print
- Strict ordered printing
- Print Time Estimation

## Adobe interpreter support

- Adobe® PDF Print Engine® 5.5\*\*\*\*
- CPSI version 3020

## Productivity and workflow

- Fiery Command WorkStation®
- Fiery JobExpert™
- Fiery JobFlow™ Base
- Fiery Impose-Compose
- Fiery Preflight
- Fiery Hot Folders/Virtual Printers
- Fiery drivers for Linux, Windows Mac®, and PCL
- Fiery Essential Driver
- Fiery VUE
- Fiery WebTools™
- Fiery server presets
- Fiery Go (Android™ and iOS)
- Fiery Paper Catalog
- Booklet Maker
- Set Page Device Mapping
- Fiery Custom Crease
- Fiery IQ: Dashboard, Insight, Notify, Go

## Variable data printing

- Fiery FreeForm™ Create
- Supported file formats: Fiery FreeForm Plus, PPML v3.0, PDF/VT-1 and 2, Creo VPS
- VDP Record and Set Level Finishing, VDP Record Range Printing, Define Record Length, VDP Resource Manager, VDP Raster Preview, VDP imposition

## File format support

- Adobe® PostScript® Levels 1, 2, 3; Adobe PDF; PDF/X-1a, 3, and 4; Optimised PDF and PS; Enhanced PCL6/PCL5
- JPEG, EPS, TIFF (via Hot Folders)
- Microsoft Office document formats: doc, docx, xls,xlsx, ppt, pptx, pps, ppsx, pub (via Hot Folders)

## Networking/Connectivity

- TCP/IP, AppleTalk, Bonjour support, SNMP, Port 9100, IPP, FTP, SMB, WSD, point and print, print via email (PS/PDF), IPv6 support, LDAP authentication

## Integration

- Fiery JDF v1.8
- Fiery API
- MIS and Web-to-Print integration ready
- Prepress workflow integration (FUJIFILM XMF Workflow, Agfa® Apogee, Kodak® PRINERGY, Heidelberg® Prinect, SCREEN EQUIOS)

## Security

- Secure Erase, Security profiles, Security Audit Log
- FIPS 140-2 compliant data encryption
- ISO/IEC 15408 & IEEE Std 2600 (Common Criteria) compliant\*\*\*
- Port blocking, IP filtering, 802.1X authentication, IPsec encryption, HTTPs with TLS 1.3 support
- Enhanced certificate management. Fiery self-signed certificates are recreated automatically
- Secure printing, PostScript security, USB security
- Digitally signed software updates
- Option to use a customer hardened Windows OS image to meet security compliance requirements
- Digitally signed software updates
- Authentication/Accounting

## EMI/EMC

- FCC Title 47, Part 15 Subpart B; ISED of Canada, ICES-003; EN55032: 2015 + A11:2020; EN61000-3-2: 2013 + A11:2019; EN61000-3-3: 2013 + A11:2019; EN55035: 2019 + A11:2020; AS/NZS CISPR 32: 2013; EN62311: 2008; CCC-China; Korea; BSMI-Taiwan

## Safety

- CB Scheme-IEC-62368-1, 2<sup>nd</sup> Edition; CE Mark (EU); UKCA-Mark (UK); UL/CSA C.22.2 No. 62368-1: 2019 (TUV-NRTL); T-Mark EN IEC 62368-1:2020 + A11; CCC-China; Argentina; BSMI-Taiwan; Oman; Kuwait; Mexico; South Africa; UAE - RoHS

## Power

- Auto-switching: 100–240 VAC
- 50/60 Hz, 6 Amps @100 VAC, 5 Amps @240 VAC
- Maximum power usage: 350 W
- Typical power usage: 100 W

## Dimensions/Weight

- 527.05 mm (20.75") H x 234.95 mm (9.25") W x 463.55 mm (18.25") D
- 16.5 kg (36.5 lbs)

## Optional Fiery software and hardware

- Fiery JobMaster™ \*\*,\*\*\*
- Fiery Graphic Arts Pro Package \*\*,\*\*\*
  - Fiery Spot Pro, Fiery ImageViewer, Fiery Preflight Pro, Fiery Postflight, Fiery Control Bar
- Fiery Color Profiler Suite
- ES-3000 spectrophotometer
- ES-6000 spectrophotometer
- Fiery JobFlow™
- Adobe® Acrobat® Pro Kit
- Fiery IQ Manage
- Fiery disk drive security kits
- Fiery NX Station GL

\* Free 30-day trial available

\*\* Available as a 5-year term license

\*\*\* With proper configuration by end customer or service provider

\*\*\*\* Updated with enhancements and service releases on an ongoing basis

**FUJIFILM Business Innovation Australia Pty Ltd**  
Authorized Distributor

[fujifilm.com/fbau](http://fujifilm.com/fbau)



6453 Kaiser Drive  
Fremont, CA 94555

[www.fiery.com](http://www.fiery.com)

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

**Trademarks** •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •Apeos and ApeosPro are registered trademarks or trademarks of FUJIFILM Business Innovation Corp.

Nothing herein should be construed as a warranty in addition to the express warranty statement provided with Fiery, LLC products and services. ColorGuard, ColorRight, Command WorkStation, ColorWise, Fiery, the Fiery logo, Fiery Compose, Fiery Driven, the Fiery Driven logo, Fiery Edge, Fiery Essential, Fiery HyperRIP, Fiery Impose, Fiery Impress, Fiery ImageViewer, Fiery Intensify, Fiery JobExpert, Fiery JobFlow, Fiery JobMaster, Fiery Prep-It, Fiery Prints, the Fiery Prints logo, Fiery TrueBrand, FreeForm, MicroPress, IQ, PrintMe, RIPChips, RIP-While-Print, Spot-On, Spot Pro, and WebTools are trademarks or registered trademarks of Fiery, LLC and/or its wholly owned subsidiaries in the U.S. and/or certain other countries. All other terms and product names may be trademarks or registered trademarks of their respective owners and are hereby acknowledged.  
© 2023 FIERY, LLC. ALL RIGHTS RESERVED.

FTL\_Fb\_042.10.22