

Acuity Prime series: Overview

The benchmark platform for versatile print production

A true flatbed with a unique, exceptional design and high value, the Acuity Prime offers high quality printing on a range of rigid and flexible media, supported by its five dedicated vacuum zones and jettable primer. This range is available at a cost effective price point and offers an excellent return on investment.

Key features

- ▶ Dedicated flatbed design
- ▶ High resolution greyscale printheads
- ▶ Standard (2.54 m x 1.27 m)
- ▶ Up to 150 m²/hr throughput
- ▶ Registration pins
- ▶ 5 dedicated vacuum zones to minimise masking
- ▶ Powerful instant curing LED UV system
- ▶ Fujifilm Uvijet LED UV curing inks
- ▶ Standard 4 colour plus white with clear and optional jettable primer
- ▶ Automatic Printhead Maintenance System (APMS)



Acuity Prime



Produce a wide range of high value print

Lower cost of ownership and excellent ROI

With variable drop-size printheads and highly pigmented inks, Acuity Prime printers lay down a thin ink film, which minimises production costs, and in combination with a competitive system price, support an excellent ROI.

Produce a wide range of applications

With outstanding image quality and excellent adhesion to a broad range of rigid and flexible media, materials and objects, the Acuity Prime can produce an amazing variety of printed products for distance and close viewing. The vacuum table can handle almost any sheet material. It secures rigid and flexible media and holds it perfectly flat for high quality print across every sheet.

Expand your creative options

The option to print with white and clear inks, and to print directly to almost any material in perfect registration, enables the Acuity Prime to produce high value, creative work that could offer opportunities for new revenue. With the jettable primer option, the Acuity Prime can adhere to a wide variety of industrial media.

Designed with the operator in mind

At Fujifilm we understand the value of production time and usability, so we designed the Acuity Prime with the operator in mind. With a new and user-friendly GUI, easy clean printhead maintenance and visible status lights for the ink tanks, operators are able to spend less time maintaining the machine and more time printing.



FUJIFILM

For more information or detailed product specification, please call or visit us at

FUJIFILM Business Innovation Australia Pty Ltd

8 Khartoum Road MACQUARIE PARK NSW 2113 Australia | Tel. +61 2 9856 5000 | fujifilm.com/fbau

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.
V1.0 April 2021