



**SC-T3200**  
24"

**SC-T5200 / T5200D**  
36"

**SC-T7200 / SC-T7200D**  
44"  
(shown with optional scanner)

## Epson SureColor Technical Range

- Designed for CAD, GIS, POS, design and presentation work
- Optional wide format scanner for copy and scan-to-file functionality
- Produce an A1 print in as little as 28s
- Convenient operation with all consumables loaded from the front
- Low energy usage and a choice of economical ink cartridges in 110ml, 350ml and 700ml sizes
- HP-GL/2 emulation and optional high speed Adobe® PostScript® 3™ with 320GB HDD
- Utilises Epson's latest PrecisionCore™ printhead with variable size droplet technology (VSDT)
- Epson all-pigment UltraChrome™ XD ink for scratch and moisture resistant prints with super-fine detail, solid dark areas and vibrant colour

# Epson SureColor Technical Range

## SC-T3200/T5200/T7200/T5200D/T7200D

### Product Specifications

| PRINT SPECIFICATIONS          |                                                                                                                                                   | INK AND CONSUMABLES                              |                |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------|----------------|
| Printhead                     | PrecisionCore™ TFP™ with VSDT & Auto Head Alignment                                                                                               | UltraChrome XD 110ml K,C,M,Y,MK,PK               | C13T692100-500 |
| Printing Resolution           | 2,880 × 1,440dpi                                                                                                                                  | UltraChrome XD 350ml K,C,M,Y,MK,PK               | C13T693100-500 |
| Ink type                      | UltraChrome™ XD aqueous pigment ink                                                                                                               | UltraChrome XD 700ml K,C,M,Y,MK,PK               | C13T694100-500 |
| Colours                       | Magenta, Yellow, Cyan, Matte Black, Photo Black                                                                                                   | Maintenance Tank                                 | C13T619300     |
| Ink cartridge size            | 110ml/350ml/700ml                                                                                                                                 | <b>CONFIG BUILDS</b>                             |                |
| Maximum printing speed        | 28sec/A1 on plain paper                                                                                                                           | T3200 Desktop 1Yr Warranty                       | SCT3200DT1YR   |
| Nozzle Configuration          | 720 Nozzles per colour                                                                                                                            | T3200 Desktop 3Yr Warranty                       | SCT3200DT3YR   |
| Interface                     | USB2.0 1000/100/10Base-T                                                                                                                          | T3200 Floor Standing 1Yr Warranty                | SCT32001YR     |
| RAM                           | 1GB                                                                                                                                               | T3200 Floor Standing 3Yr Warranty                | SCT32003YR     |
| HDD                           | 320GB (Optional) <sup>8</sup>                                                                                                                     | T3200 Floor Standing Postscript 1Yr Warranty     | SCT3200P1YR    |
| PostScript                    | Adobe® PostScript® 3™ (Optional) <sup>5</sup>                                                                                                     | T3200 Floor Standing Postscript 3Yr Warranty     | SCT3200P3YR    |
| Emulation                     | HP-GL/2, HP RTL <sup>4</sup>                                                                                                                      | T5200 Floor Standing 1Yr Warranty                | SCT52001YR     |
| Power                         | Energy Star compliant                                                                                                                             | T5200 Floor Standing 3Yr Warranty                | SCT52003YR     |
| PAPER HANDLING                |                                                                                                                                                   | T5200 Postscript 1Yr Warranty                    | SCT5200P1YR    |
| Roll paper replacement        | Front access, spindle-less                                                                                                                        | T5200 Postscript 3Yr Warranty                    | SCT5200P3YR    |
| Maximum media width           | T3200: 24inch, T5200: 36inch, T7200: 44inch                                                                                                       | T5200 Postscript Scanner 1Yr Warranty            | SCT5200PS1YR   |
| Paper thickness               | 0.08mm-1.5mm (single sheets)                                                                                                                      | T5200 Postscript Scanner 3Yr Warranty            | SCT5200PS3YR   |
|                               | 0.08mm to 0.5mm (roll)                                                                                                                            | T7200 Floor Standing 1Yr Warranty                | SCT72001YR     |
|                               | Rigid board supported                                                                                                                             | T7200 Floor Standing 3Yr Warranty                | SCT72003YR     |
| OPTIONAL SCANNER <sup>7</sup> |                                                                                                                                                   | T7200 Postscript 1Yr Warranty                    | SCT7200P1YR    |
| Optical resolution            | 600dpi                                                                                                                                            | T7200 Postscript 3Yr Warranty                    | SCT7200P3YR    |
| Light source                  | Dual LED (RGB)                                                                                                                                    | T7200 Postscript Scanner 1Yr Warranty            | SCT7200PS1YR   |
| Scanning method               | CIS                                                                                                                                               | T7200 Postscript Scanner 3Yr Warranty            | SCT7200PS3YR   |
| Scan width                    | 153mm to 914.4mm <sup>3</sup> (36")                                                                                                               | T5200D Dual Roll Floor Standing 1Yr Warranty     | SCT5200D1YR    |
| Scanning destination          | Printer, or electronic file to: HDD (Option), shared folder, send by email (SMTP)                                                                 | T5200D Dual Roll Floor Standing 3Yr Warranty     | SCT5200D3YR    |
| Scanned file format           | JPEG, PDF                                                                                                                                         | T5200D Dual Roll Postscript 1Yr Warranty         | SCT5200DP1YR   |
| Scanning accuracy             | +/-0.2% of the specified vector length or +/-0.13mm (whichever the greater)                                                                       | T5200D Dual Roll Postscript 3Yr Warranty         | SCT5200DP3YR   |
| Scan speed                    | Approx. 8.4cm/sec(200dpi) <sup>1</sup>                                                                                                            | T5200D Dual Roll Postscript Scanner 1Yr Warranty | SCT5200DPS1YR  |
| Copy speed                    | Approx. 39sec/A1 <sup>2</sup>                                                                                                                     | T5200D Dual Roll Postscript Scanner 3Yr Warranty | SCT5200DPS3YR  |
| Scanning Resolution           | 200, 300, 360, 400, 600 dpi                                                                                                                       | T7200D Dual Roll Floor Standing 1Yr Warranty     | SCT7200D1YR    |
| Copying Resolution            | Scanning: 300dpi, Printing: 360 dpi                                                                                                               | T7200D Dual Roll Floor Standing 3Yr Warranty     | SCT7200D3YR    |
| Media Thickness               | 0.05mm to 1.3mm                                                                                                                                   | T7200D Dual Roll Postscript 1Yr Warranty         | SCT7200DP1YR   |
| Media Width                   | 153mm to 965.2mm (38")                                                                                                                            | T7200D Dual Roll Postscript 3Yr Warranty         | SCT7200DP3YR   |
| Supported paper types         | Plain Paper, Recycled paper, Tracing paper, Matte film, Blueprint copy, Matte paper for ink jet printers, Synthetic paper, Newspaper, Photo paper | T7200D Dual Roll Postscript Scanner 1Yr Warranty | SCT7200DPS1YR  |
|                               |                                                                                                                                                   | T7200D Dual Roll Postscript Scanner 3Yr Warranty | SCT7200DPS3YR  |
|                               |                                                                                                                                                   | OPTIONS                                          |                |
|                               |                                                                                                                                                   | Additional Roll Media Adapter Set                | C12C811401     |
|                               |                                                                                                                                                   | 44" Auto Take Up Reel System <sup>6</sup>        | TSATSKIT       |
|                               |                                                                                                                                                   | 320GB Hard Disk Drive                            | C12C848031     |
|                               |                                                                                                                                                   | 36" Large Format Scanner Upg Kit                 | SCT36MFP       |
|                               |                                                                                                                                                   | 44" Large Format Scanner Upg Kit                 | SCT44MFP       |



T7200D with Scanner

### Better Products for a Better Future

Epson is the registered trademark of Seiko Epson Corporation. All other names and company names used herein are for identification purpose only and may be the trademarks or registered trademarks of their respective owners. Epson disclaims any and all rights in those marks. All print samples shown herein are simulations. Specifications are subject to change without notice. V 1.0 September 2014.



## FUJIFILM

For more information or detailed product specification, please call or visit us at

**FUJIFILM Business Innovation Australia Pty Ltd**

8 Khartoum Road MACQUARIE PARK NSW 2113 Australia

Tel. +61 2 9856 5000

fujifilm.com/fbau

FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. V1.0 April 2021

\*refer to [www.epson.com.au/technical](http://www.epson.com.au/technical) for more detailed information.

\*1 Copy & Scan speed is measured based on First Copy out SEF (Short Edge Feed).

\*2 Maximum copy speed is measured based on First Copy out LEF (Long Edge Feed) Product specifications are subject to change without notice.

\*3 The actual maximum image width or length to be scanned is reduced by a default scanning margins of 3mm to all four directions.

\*4 HP-GL/2 & HP RTL are trademarks of Hewlett-Packard Company. Printer may not print HP-GL/2 or HP RTL language data accurately depending on your system environment or type of print data use. In order to ensure correct printing results, please make sure that you run a printing test prior to deciding on purchasing the printer. Ask your local Epson representative or Epson authorised resellers for your test.

\*5 Adobe® & PostScript® 3™ are trademarks of Adobe Systems Incorporated in the United States & other countries.

\*6 The Auto take up reel system works with the SC-T7200 only.

\*7 The optional scanner works with the 36" and 44" models only. It is included with all the MFP models.

\*8 The optional HDD is incorporated with all postscript models or it can be purchased as a stand-alone option.