

New Times, New Apeos

The new "Apeos" offers advanced features with high security level and easy operability to help business diversify with times. "Apeos" devices are able to connect smoothly with a variety of solutions and services to realise an all new agile remote workstyle of working anytime, anywhere.





Small - Smart - Scalable Solution for your everyday business requirements

Apeos 3560 / 3060 / 2560

Copy/Print	Scan	Fax ^{*4}	Printing Resolution	Control Panel	
*1	Colour/Monochrome 2 sided Scanning 80 ppm*2*3 1 sided Scanning 55 ppm*3	Super G3 FAX	1,200 × 1,200 dpi*5	7" Tilted Colour Touchscreen	•Wireless LAN Supported •Mobile Supported •Cloud Interactive

^{*1:} A4 LEF. *2: Single pass DADF model (2 sided scanning). *3: A4 LEF 200 dpi to Folder. *4: Optional. *5: Print Function.

Various combinations



Standard Configuration Model-1T



With 1 Tray Module with Cabinet*



With 3 Tray Module*



With Side Tray Supports distribution output for each of copy, print, and fax jobs

Uncompromising usability along with compatibility

Multipurpose device with small footprint and easy setup

- Compact design with width of 590 x depth of 659 mm
- Select a right configuration of 1, 2 or 4 trays as per your growing

Compact design allows you to place it on your desktop



Shared machines for offices.

Increase to maximum paper capacity of 2096 sheets*.

* 80 gsm Paper, Standard + 3 Tray Module (optional).



Uncompromising Image quality

- High-resolution printing of 1,200 x 1,200 dpi achieved with LED printhead
- Image Enhancement processing reproduces diagonal lines and the outlines of characters, which can become jagged when printed, more smoothly
- Achieved print that is eye-friendly and easy to scan by taking advantage of the low temperature fusing properties of EA-Eco LGK toner with lower


Quick startup and output for greater efficiency

- Fast Boot Mode prepares the operation panel in 6 seconds*1
- The control panel becomes operatable from Low Power Mode in approximately 1 second*2
- Quick warm up in less than 28 second
- First Copy Output Time in 4.5 seconds*3
- *1: Depending on the status of the main unit and configuration of options, it may not operate or take more than 6 seconds.
- *2: Please specify the time to Sleep Mode longer than the time to Low Power Mode.
- *3: A4 LEF.

Quick scanning of high-volume originals*1

- Up to 80 ppm can be read at high speed in Scan^{*2}
- Up to 130 sheets can be loaded
- One pass DADF will not damage the original document
- Instantly scan without manual entry of each original size
- Automatically converts custom size originals to standard size
- *1: Single pass DADF model.
- *2: 1 pass 2 sided scanning. Our Standard Paper (A4 LEF), 200 dpi, to Folder.





Direct scan to or print from USB* for efficient operations

- You can directly print the documents stored on a USB flash drive or scanned data can be directly stored on a USB flash drive without using a PC
- * Optional.



Various finishing options are available according to your needs


Finisher-A2



Finisher-B5 with Booklet Maker Unit



Supports single and double Staple-free Stapling *1



- 1: Staple-free stapling is available with Finisher-B5.
- *2: Optional.

 *3: Booklet Maker Unit is required. When specifying Saddle Staple or Single Fold with Finisher-B5, paper is not folded but creased.

Quick and simple operability

Simple layout with easy navigation

Black and gray tone UI gives better contrast for easy recognition.

- Icons are evenly spread for easy recognition
- Consistent operation steps of each function for easy recall
- Home screen personalisation for ease of access to commonly used functions
- Pin regular settings for registering frequent or repeated jobs
- Clear visible light notifications for completed or error jobs
- Subtle sound notification for alert and attention



Smartphone becomes a "portable operation panel"

Seamless connectivity with mobile devices for Copy, Fax, Print, Scan^{*1} jobs using the Print Utility*² application.

- Mobile device can be used as an alternative UI for operations control to minimise common touch points
- Frequent settings can be saved as "Favourites"
- Directly send fax or email with the addresses stored in the smartphone
- Minimise printer touch points for hygiene reasons
- Quickly establish direct Wi-Fi connection by scanning the QR code on the user panel

Note: Connect to machine via wireless environment or Wi-Fi Direct connection.

- *1: Scan to Mobile, E-mail, Scan to Folder.
- *2: It can be downloaded free of charge from Google Play™ or App Store.

Flexibility in office layout

Supports wireless LAN environment*1.

- Supports free addressing in the office with Wi-Fi support
- Up to five Wi-Fi Direct multifunction devices can be connected at the same time
- Supports direct mobile printing*2
- Print Utility, AirPrint, and Mopria® Print Service are supported
- *1: Optional.
- *2: When connecting to Wi-Fi Direct.

Print out from any multifunction device within the office

With Server-less On-Demand Print*, you have the flexibility to print and collect the print outs from any of the connected multifunction devices.

- Improves productivity by printing from another available multifunction device when the current device is in use
- Up to 100 units can be linked
- Specific job settings can be revised at the device level to save time (1 sided to 2 sided, adding staple)
- * Optional.

Simple device management with Server-less Authentication

Server-less Authentication* enables user information to be synchronised among multifunction devices in the same group and allows administrators to reduce their workloads.

- Simply tap your card to link the user ID with the multifunction device
- The ID information is automatically shared with the other multifunction devices in the same network
- Authentication can be performed with any devices in the office
- * Optional.



Various features saving time and effort in scanning operation


Scanned data can be transferred through a variety of methods including Email, URL, and send to PC (SMB/FTP/SFTP).

- Data can be sent by using multiple features simultaneously
- Improve your digitalisation process with features including automatic orientation of scanned page to upright position, correcting the skewed page, or removing blank pages
- In addition to TIFF and JPEG, the scanned data can be converted to OCR-enabled* or high compression/ specific colour PDF or DocuWorks documents. Also they can be converted to editable Excel/Word documents*
- With ScanAuto, you can easily send the scanned data to your e-mail address by simply pressing a button
- * Optional.

Digitisation of paper documents for effortless document management

With Scan Delivery*, you can automatically process and store scanned images by simply pressing the preset button for each workflow or document type.

- Automate to set file format, file name, OCR*, etc.
- Automatically stores scanned and processed documents in the appropriate destination
- Specify particular words or characters in a document as the folder or file name
- $\, \bullet \,$ 0 and other frequently mis-recognised characters can be read correctly
- * Optional.





QR codes and bar codes application


Where QR code or bar code is available on the headsheet or content body of the original document for scanning, Scan Delivery will recognise and process the information accordingly.

Streamline operations for remote work style

Share information anytime, anywhere

With Working Folder* and internet access, documents can be viewed regardless of time and location.

- Can be linked smoothly with multifunction devices, DocuWorks, and mobile devices
- Documents in Working Folder can be printed from the control panel
- Scanned documents will be assigned a file name and stored in Working Folder. An email notification will be sent to relevant users



* Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.

Supporting Universal Print by Microsoft

By registering multifunction devices to Universal Print by Microsoft in advance, users*1 authenticated with Microsoft Entra ID*2 can print from anywhere through cloud.

- *1: Organizations with or Microsoft Windows Enterprise or Microsoft 365 subscriptions.
- *2: Formerly Azure Active Directory.

Easy and secure output even when you are working remotely

FUJIFILM IWpro* is an all-in-one secure platform solution for business digitisation, provide workspace for collaboration, workflow optimisation, efficient document management of metadata and documents, and versatile cloud-based printing capabilities.

- FUJIFILM IWpro* is accessible via a web browser from any location that has internet service, such as from branch office or on the go
- High-quality and secure print environment is available regardless of your location, either in or out of your office
- Users can select and print the document that store in the cloud with the multifunction device outside of office




In headquarters / branch office In factory / warehouse In coworking space / shared office

* Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.

Centralised cloud integration

Cloud Service Hub* allows single sign-on to multiple cloud storage services.

- Specific storage location can be assigned for scanned documents directly from the multifunction device
- Searching documents from multiple cloud services is supported
- Full-text search on scanned documents can be performed with OCR



 \star Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.

Initiatives for environmental consideration



We are working to develop environmentally conscious products, including technologies that reduce the power consumption of multifunction devices and printers to achieve lower environmental impact.

Fujifilm Group introduced the certification program in which we clarify the environmental value of each product by

assessments at the time of product development, conduct the evaluation based on our in-house certification criteria and certify the products* that are excellent in reducing environmental impact as "Green Value Products".

This product was certificated as a "Silver" rank product that reduces environmental impact at a higher level than

industries' standard.

* Products and services excellent in reducing environmental impact are those designed in consideration of environmental impact throughout their life cycle from acquisition of raw materials, production, usage, disposition, to reuse.

Initiatives for energy conservation

- Adopt the LED printhead that enables space and energy saving design
- Reduce the power consumption with the smart power saving feature that solely powers on the required parts according to the functions being used by customers

Initiatives for resources conservation

- Staple-free stapling that helps reducing waste and that also can be used with peace of mind at certain places where need considerations for safety or any contamination
- Functions contributing to paper consumption reduction
 -Private Charge Print, Scan, Paperless Fax, Pages per
- -Private Charge Print, Scan, Paperless Fax, Pages per Side/Multiple-Up etc.
- Adopt design for making products easy to reuse/recycle after use

Safeguard important information

Information is an important asset which should be protected at all cost

Protect from unauthorised user

Multiple options of setting user authorisation allow administrator to select a right combination as per given environment.

- Local Authentication
- Authentication by Remote Server*
- IC Card Authentication*
- User-specific feature access
- Private Charge Print
- * Optional

Additional layer of unwanted access can be created for specific users (e.g. guests).

- Secondary Ethernet Kit*
- * Optional.

Protects Data

Protects against any malicious intent of hacking, tampering with device / system settings.

- Encryption of stored data
- Uses TPM* 2.0 chip for encryption key management
- Deletes settings and document information all at once
- * Trusted Platform Module

Protects the information by means of strong encryption while transferring it between devices, servers etc.

- Encryption of communication paths by SSL/TLS or IPsec
- Encryption when transferring via SMBv3 and SFTP
- Scan file encryption/signature
- Email encryption and signature by S/MIME
- TLS version limit
- Elliptic curve cryptography
- WPA3

Protect from unauthorised access

Protects device settings at multiple levels by clearly demarking change restrictions for different target audience - End users, IT administrators and Service Engineers.

- Service representative operation restriction
- Account lock to prevent unauthorised access
- Information for changing the default password
- Warnings displayed when using global IP address

Prevents unauthorised program from installing without notice. Robust IT audits are supported with device data logs for easy tracking.

- Software signature verification
- Remote update restrictions
- IP address filtering
- Tampering detection at startup and automatic restoration when tampering is detected
- Prevention of tampering during operation
- Audit log
- Audit log system transfer

Prevents operation errors

Prevents information leakage due to inadvertent mistakes by administrators and users.

- Scan documents to be delivered to fixed destination
- Re-enter fax recipient
- Annotations
- Hidden text printing*
- * Optional.

Security certifications

 Certified with ISO/IEC 15408, which is the international standard for designing and operating IT security

Reliable support system

Easy solutions to resolve problems

From supplies replacement to unexpected device failures, most problems can be resolved without waiting for the service representatives or sales representatives.

1. Resolve problem using the "Help" function on the device

- Self Help information is available on the control panel
- Self Help information can be accessed via the mobile device by scanning the QR code displayed on the control panel





2. "Remote Assistance" with the help of operators

- Connects directly to the Support Centre
- An operator will remotely access the multifunction device to resolve the problem by guiding through the steps on the shared control panel

Keeping a close eye on your multifunction device on a daily basis

Monitoring the multifunction device status to minimise operation down time.

- Check billing meter
- Automatically delivers consumables when cartridges level is low
- Detect machine errors for early invention to rectify the problem

Note: You need to apply for using the EP-BB Enabling Smart Remote Service. (free of charge) $\,$

Making a backup of multifunction device's settings

Device Setup Editor is a free tool which helps you both, in editing device setting and creating a much-needed information backup for business continuity reasons.

- A back up the device / printer settings can be created onto the PC
- Administrator can optimize device usage by viewing/editing these settings, best suited for their environment.
- When installing a new device, these settings can be migrated (or cloned) from the existing device to the new device

Apeos 3560 / 3060 / 2560 **Functions & Specifications**

Basic Specifications / Copy Function

Item		3560	3060	2560
		Desktop / Console		
		4 GB (Max: 4 GB)		
Storage Devi	ce Capacity*1	128 GB		
Scan Resolut	ion	600 x 600 dpi		
Printing Reso	lution	1,200 × 1,200 dpi		
Warm-up Time*2		When enabled: 28 temperature)	,	degrees Celsius room degrees Celsius room
Recovery Time f	ne rom Sleep Mode)		23 degrees Celsius ro	
Original Size		Maximum of A3, 11 x	: 17", 297 x 432 mm fo	or both Sheet and Book
	Max	A3, 11 x 17"		
Paper Size	Min	A5 [Postcard (100 x	148 mm), when using	g Bypass Tray]
1 aper 3ize	Image loss width	Lead edge 4.0 mm,	Trail edge 2.0 mm, R	ight/Left edge 2.0 mm
Paper	Paper Tray	60 to 256 gsm		
Weight*⁴	Bypass Tray	60 to 216 gsm		
First Copy Ou	utput Time	4.5 sec. (A4 LEF)		
	A4 LEF / JIS B5 LEF	35 ppm	30 ppm	25 ppm
Continuous	A4	26 ppm	23 ppm	19 ppm
Copy Speed*5	JIS B5	13 ppm	13 ppm	11 ppm
	JIS B4	22 ppm	20 ppm	16 ppm
	A3	19 ppm	17 ppm	14 ppm
	Standard	500 sheets x 1-tray	+ Bypass Tray 96 s	heets
Paper Tray Capacity*6	Optional	1 Tray Module with 0 3 Tray Module: 500	Cabinet: 500 sheets x Sheets x 3-tray	1-tray
	Max	2,096 sheets [Stand	dard + 3 Tray Modul	le]
Output Tray Capacity*7		Upper Center: 250 Lower Center: 250		
Power Supply		AC220-240 V +/- 1	.0 %, 8 A, 50/60 Hz	common
Maximum Power Consumption		Sleep Mode: 0.4 W (1 W (AC230 V +/- 10	, ,
Dimensions Model-CPS-B		with Cabinet is inst	1,118 mm (when o alled.)	ptional 1 Tray Module ptional 3 Tray Module
Weight*8	Model-CPS-B	57 kg 79 kg (when option 82 kg (when option	al 1 Tray Module with al 3 Tray Module is	n Cabinet is installed.) installed.)

- *1: The Storage Device Capacity is not totally available for customers.

 *2: It may change depending on usage conditions.

 *3: Embedded Plug-ins / Custom Services are enabled as factory default. You can change the settings if needed.

 *4: It is recommended to use our recommended paper. Correct print output may not be possible depending on the requirement.

 *5: The speed may be reduced due to the image quality adjustment.

 *6: 80 gsm paper.

 *7: 70 gsm paper.

 *8: Including Toner Cartridge.

Print Function

Item		Description	
Type		Built-in type	
Continuous	Print Speed*1	Same as the Basic Specifications / Copy Function	
Printing	Standard	[PCL Driver] Standard: 600 x 600 dpi, High Resolution: 1,200 x 1,200 dpi	
Resolution	Optional	[Adobe® PostScript® 3™ Driver] Standard: 600 x 600 dpi, High Resolution: 1,200 x 1,200 dpi	
Page	Standard	PCL5 / PCL6	
Description Language	Optional	Adobe® PostScript® 3™	
	Standard	[PCL Driver] Windows 11 (64 bit), Windows 10 (32 bit / 64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit)	
Supported Operating		[Mac OS X Driver] macOS 14 / 13 / 12 / 11 / 10.15 / 10.14	
System*2	Optional	[Adobe® PostScript® 3™ Driver] Windows 11 (64 bit), Windows 10 (32 bit / 64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit) macOS 14 / 13 / 12 / 11 / 10.15 / 10.14	
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T, USB3.0	
meriace	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)	

^{*1:} The speed may be reduced due to the image quality adjustment. The printing speed may be reduced depending on the document.
*2: Please refer to our official website for the latest supported OS.

Scan Function

Item		Description
Туре		Colour Scanner
Scan Resolution		600 x 600 dpi, 400 x 400 dpi, 300 x 300 dpi, 200 x 200 dpi
Scan Speed		Same as the Scan Speed for the Duplex Automatic Document Feeder
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T
interrace	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)

Fax Function (Optional)

	•
Item	Description
Original Size	Max: A3, 11 x 17", Long document (Longest 600 mm)
Recording Paper Size	Max: A3, 11 x 17"; Min: A5
Transmission Time	2 seconds and more but fewer than 3 seconds*1
Transmission Mode	ITU-T G3
Applicable Lines	Telephone subscriber line, PBX, Fax communication (PSTN),

^{*1:} When A4 size document with approximately 700 characters is transmitted in standard image-quality (8 x 3.85 lines/mm) and in high-speed mode (28.8 kbps or faster, JBIG). Only indicates the time for transmitting the image information and does not include the communication control time. The total communication time will vary depending on the contents of the document, the type of machine receiving the fax, and line condition.
*2: No. of FAX lines is up to 3 ports. Port refers to number of channels for FAX.

Duplex Automatic Document Feeder [1 pass, 2 sided scanning]

			- '	,
Item		3560	3060	2560
Original Size /			7"; Min: A6*1 In Duplex: 50 to 1	128 gsm)*2
Capacity*3	Capacity*3			
Scan	Copy (A4 LEF, Simplex)	35 ppm	30 ppm	25 ppm
Speed*4	Scan	B/W: 55 ppm, Colour: 55 ppm (1 pass, 2 sided scanning: B/W 80 ppm, Colour 80 ppm)[Standard Document (A4 LEF), 200 dpi, to Folder]		

- Note: Installed for Model-CPS-B as standard.
 *1: The minimum custom size is 49×85 mm.
 *2: Custom sizes from 49 x 85 mm to 55 x 91 mm are available from 38 to 209 gsm.
 *3: 70 gsm paper.
 *4: The scanning speed varies depending on the documents.

Side Tray

Item	Description
Paper Capacity*	100 sheets
Dimensions	W 347 x D 419 x H 201 mm

^{* 70} gsm paper.

Finisher-A2 (Optional)

Item		Description
Type		Sort (Offset available) / Stack (Offset available)
Paper Size		Max: A3, 11 x 17"; Min: Postcard (100 x 148 mm)
Paper Weight		60 to 256 gsm
Paper Capacity*1		[Without Stapling] A4: 500 sheets; JIS B4: 250 sheets; A3 or larger: 200 sheets; Mixed Size Stacking*2: 250 sheets [With Stapling] 30 sets
	Capacity	A4: 50 sheets (90 gsm or less), JIS B4 or larger: 30 sheets (90 gsm or less)
Charala	Paper Size	Max: A3, 11 x 17"; Min: JIS B5 LEF
Staple	Paper Weight	60 to 256 gsm
	Position	Single stapling, Dual stapling
Dimensions*3 / Weight		W 658 x D 461 x H 238 mm, 11 kg
4.4. 70		

*1: 70 gsm paper.
*2: When larger size sheets are stacked on top of smaller size sheets.
*3: Width 478 mm when the paper support is stored.

- 1) If the storage media of the base unit fail, loss of received data, accumulated data, registered setting data, etc. may occur. In no event shall "the company" be liable for any damages whatsoever arising from loss of data.
- Functional spare parts will be available for at least 7 years after the product is no longer manufactured.

Finisher-B5 (Optional)

	` '	
Item		Finisher-B5
Туре		Sort (Offset available*1*2) / Stack (Offset available*1*2)
Paper Size*3		Max: A3, 11 x 17"; Min: A5
Paper Weigh	t	60 to 256 gsm
Paper Capaci	ity* ⁴	[Without Stapling] A4: 2,000 sheets, JIS B4 or larger: 1,000 sheets, Mixed Size Stacking*5: 300 sheets [With Stapling] A4: 100 sets or 1,000 sheets*6, JIS B4 or larger: 75 sets or 750 sheets [With Booklet Finishing*7] 50 sets or 600 sheets [With Fold*7] 500 sheets
	Capacity	Staple: 50 sheets (90 gsm or less), Staple-free Staple*8*9: 10 sheets (80 gsm or less)
Ctonlo	Paper Size*10	Max: A3, 11 x 17"; Min: A5 LEF
Staple	Paper Weight	Staple: 60 to 256 gsm, Staple-free Staple*8*9: 60 to 105 gsm
	Position	Single stapling, Dual stapling
	Number of Holes	2-hole / 4-hole punch or 2-hole / 3-hole punch (US Specifications)
Punch*11	Paper Size*12	Max: A3, 11 x 17"; Min: A5 LEF
	Paper Weight	60 to 220 gsm
D lul - t	Capacity	Saddle Staple: 15 sheets; Single Fold: 5 sheets
Booklet Finishing*7	Paper Size	Max: A3, 11 x 17"; Min: A4, Letter
i iiiisiiiiig	Paper Weight	Saddle Staple: 60 to 80 gsm ^{*13} , Single Fold: 60 to 105 gsm
Dimensions*14		W 607 x D 653 x H 1,041 mm With Booklet Maker Unit: W 607 x D 673 x H 1,079 mm
Weight		29 kg, Punch Module: + 2 kg, Booklet Maker Unit: + 10 kg

Note: Finisher-B5 is available only when optional 1 Tray Module with Cabinet or 3 Tray Module is attached to Main Unit.

Note: Both stapled stapling and staple-free stapling are available with Finisher-B5.

*1: The offset feature is set to disabled by factory default. The setting can be changed as necessary.

*2: Outputs less than 210 mm width are delivered without offset stacking.

*3: Paper in the sizes larger than A3 or 11 x 17" or smaller than A5 are delivered to the Centre Tray.

*3 : Paper in the sizes larger than A3 or 11 x 17" or smaller than A5 are delivered to the Centre Tray.
*4 : 70 gsm paper.
*5 : When larger size sheets are stacked on top of smaller size sheets.
*6 : 75 sets or 750 sheets with dual stapling.
*7 : The Booklet Finishing function requires the optional Booklet Maker Unit for Finisher-B. Make a crease allows you to fold easily. After a job with the Booklet Finishing function specified has been output, the next job may not be delivered until the sheets are removed from the output tray. Also, if larger size sheets are stacked on top of smaller size sheets after a job with the Booklet Finishing function specified has been run, the next job may not be delivered until the sheets are removed from the output tray.
*8 : Staple-free stapling is available with Finisher-B5.
*9 : Staple-free stapling does not have binding force equal to stapled stapling. Bound part may be easily separated depending on the paper, temperature, humidity, and how the page is turned over.
*10: Available staple positions vary depending on the paper size.
*11: The Punch function requires the optional 2/4 Hole Punch Module for Finisher-B or US 2/3 Hole Punch Module for Finisher-B.
*12: Available number of punch holes varies depending on the paper size.
*13: Covers can be up to 220 gsm (Extra Heavyweight).
*14: Inner connector within the body is excluded.

Enhanced basic functions

Copy

- Paper SupplyReduce/Enlarge
- Slight Reduction
- Auto 2 Sided Output
- Pages per Side (2 Pages / 4 Pages / 8 Pages)
- Copy Output (uncollated/collated)Copy (ID Card)
- Mixed Size Originals
- Original Size
 Background Suppression
 Book Copying
- Edge Erase • Image Shift
- Mirror Image / Negative Image
 Image Rotation

- Booklet CreationMultiple-Up x Booklet Creation
- 2 Sided Book Copying
- Covers Poster
- Repeat Image
- Preset Repeat Image
 Annotations
- · Watermark(optional)
- Joint Job
- Sample Job
- Delete Outside / Delete Inside
- Form Overlay Staple / Staple-free Staple / Punch / Crease / Saddle Staple

Print

- Adobe® PostScript® 3™
- (optional)
- Multi-Model Print Driver 2
- Microsoft Universal Print
- Secure Print
- Sample SetDelayed Print
- Print from FolderForm Registration
- Multiple-Up
- Booklet Creation
- Multiple-Up x Booklet Creation
- Poster
- Covers / Separators Envelope printing

- Private Charge Print
 Charge Print
 Print from USB (optional)
 Staple / Staple-free Staple /
 Punch / Crease / Saddle Staple (optional) • Server-less On-Demand Print

Fax (Optional)

- G3 × maximum 3 ports (optional) Internet Fax
- SIP Fax (optional) Send Direct Fax
- Address Book (maximum 5,000 entries)
- Broadcast Transmission / Group Transmission
- Redial / Resend Unsent Documents
- Rotate 90 Degrees
- Preview
- 2 Sided Scanning Resolution
- Lighten / Darken
- Original TypeMixed Size Originals
- Transmission Header
- Priority Send / Delay Start
 Cover Page
 Remote Folder
- Transmission Report
- Activity Report
 Re-enter Recipient
- Prevents Unsolicited Faxes
- Prohibit Direct FaxReceive Paperless Fax
- Simple Image Log Support

Scan

- Scan to Folder (TWAIN driver/Web browser)
- Transfer via SMB/FTP/SFTP
- Email
- Scan (URL)
- Scan to USB (optional)
- Simultaneous transmission such as Email / Transfer via SMB, etc.
- ScanAuto
- Preview
- Color Scanning
- 2 Sided Scanning

- Mixed Size Originals
 File Format: TIFF / JPEG / PDF*1 / XDW(DocuWorks)*2
- Microsoft Excel/Word format(optional)
 Single File for Each Page
- Searchable Text(optional)
- Background Suppression
 Shadow Suppression
 Auto Upright Orientation
 Skew Correction

- Skip Blank Pages
- Book Scanning

/ Signature

- Job Flow Sheets Scan Delivery (optional)
- *1: High Compression / Specific *1: High Compression / Specific Color / Searchable Text / Security / Signature / Optimise For Quick web View *2: High Compression / Specific Color / Searchable Text / Security

Others

- Local Authentication
- Remote Authentication
 Microsoft Entra ID* linked
 authentication (optional)
- IC Card Log In (optional)Serverless Authentication (optional)
- Secondary Ethernet (optional)Wi-Fi Support (optional)

- Data EncryptionData Overwrite (optional)
- Image Log (optional)Message screen from an administrator
- Job History Export
- * Formerly Azure Active Directory

Note: More options may need to be added depending on the model.

fujifilm.com/fbau



FUJIFILM Business Innovation Australia Ptv Ltd

8 Khartoum Road MACQUARIE PARK NSW 2113 Australia Tel. +61 2 9856 5000

The available model varies depending on the country/region. Please ask the sales representatives for details

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements. Reproduction Prohibitions Please note that reproduction of the following is prohibited by law: *Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. *Unused postage stamps, post cards, etc. *Certificate stamps stipulated by law: *Peproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, drawings, photographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

family use or other similar uses within a limited circle.

Trademarks - FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

*Apeos, DocuWorks, Working Folder, and Cloud Service Hub are registered trademarks or trademarks of FUJIFILM Business Innovation Corp.

*Microsoft, Active Directory, Azure, Microsoft Entra, Microsoft Edge, Excel, OneDrive, PowerPoint, SharePoint, Microsoft Teams, Windows, and Windows Server are registered trademarks of US Microsoft Corporation in the U.S. and other countries *Apple, Max, macOS, OS X, MirPint, and AlriPrint logo are trademarks of Apple Inc. registered in the U.S. and other countries and regions. *Adobe, Adobe logo, PostScript, and PostScript logo are either registered trademarks or trademarks of Adobe in the United States and/or other countries. *Mopria, the Mopria Logo, and the Mopria Alliance word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, inc. in the United States and other countries. *QR Code is a registered trademarks or trademarks of Denso Denso Wave Incorporation in this brochure are trademarks or registered trademarks of their respective companies.



For Your Safety

Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection Otherwise, electronic shock may result in the case of a failure or short circuit.