





FUJIFILM Business Innovation Corp.

New Times, New Apeos

The new "Apeos" offers advanced features with high security level and easy operability to help business diversify with times. "Apeos" devices are able to connect smoothly with a variety of solutions and services to realise an all new agile remote workstyle of working anytime, anywhere.



Flagship model of A4 Monochrome MFP that responds to work group operations with its high productivity

Apeos 6340 A4

	Copy/Print	Scan	Fax ^{*3}	Printing Resolution	Control Panel	Finisher/ Mailbox
	co *1	Colour 83 ppm ^{*2}		7" Tilted Colour	.*5	
	63 ppm ^{*1}	Monochrome 110 ppm ^{*2}	Super G3 FAX	1,200 × 1,200 dpi ^{*4}	Touchscreen Optiona	Optional ^{*5}
ľ	Wireless LAN supported Mobile supported Cloud interactive Security					

*1: On A4/B5 size paper. Print speed may drop due to image quality adjustment. *2: When using the Duplex Automatic Document Feeder. (1 pass, 2 sided scanning. Our Standard Paper (A4), 200 dpi, to Folder.) Scanning speed varies by the document. *3: Optional. *4: Print Function. *5: Only supports Model-CPS-EX.

Speedily Usable

Speedily usable

High-speed printing of 63 ppm*1.

- Fast Boot Mode prepares the operation panel in 6 seconds^{*2}
- The control panel becomes operatable from Low Power Mode in approximately 1 second*³
- High-speed printing of 63 ppm*¹
- FCOT: Prints out in about 6.0 seconds
- *1: For A4/B5 size paper. Speed may drop due to image quality adjustment.
 *2: Depending on the status of the main unit and configuration of options, it may not
- operate or take more than 6 seconds.

*3: Please specify the time to Sleep Mode longer than the time to Low Power Mode.

Expandability that responds to bulk printing.

- Paper feeding of 700 sheets*
- as standard Four tray modules can be added to support various
- media/ sizes printing • Four tray modules can be added for printing various sizes of business forms
- Robust flexible options to suit your printing needs
- * For 80 gsm paper.




550-Sheet Feeder + High Capacity Feeder

Standard + four optional 550-Sheet Feeder + Caster

Compact equipment to automate post-processing

- Space-saving Finisher-S*
- Automates stapling
- * Optional, Only supports Model-CPS-EX



Quick scanning of high-volume originals

Single-pass colour duplex scanning of 83 ppm*.

- Equipped with Duplex Automatic Document Feeder (DADF)
- You can scan both sides of the original at once. Since the original is not inverted, it protects the original document
- You can load originals up to 100 sheets
- * When the DADF is used. (1 pass, 2 sided scanning. Our Standard Paper (A4), 200 dpi, to Folder.) Scanning speed varies by the document.

User-friendly 7-inch colour touch panel

- Customisable screen icon layout
- Makes your routine workflow simple and smooth
- Provides the same operability as A3 multifunction devices



High-definition/high-quality printing that make documents more appealing

- Equipped with LED printhead, achieving high image quality at 1,200 x 1,200 dpi
- Uses Super EA-Eco toner that features the industry's smallest particle size achieving both power saving and high glossy printout



Efficiently combining A4 and A3 devices

The Apeos 6340 multifunction devices have the same UI and features as A3 devices. This leads to the optimum use of both A3 and A4 devices in one office and makes it easier to build the environment for Server-less On-Demand Print, minimising the trouble that comes with device management.



Reducing wasted time during customer service

Being compact, the Apeos 6340 series fits into a counter service area. You can copy or scan documents without leaving the counter and making your customer wait.



It can be used for the need for large volumes of forms

In order to output a large amount of forms, this unit, which boasts high durability, contributes. In addition, since various types of paper can be set in each tray, it is expected to improve operational efficiency by reducing the time and effort of paper replacement each time.

Quick and simple operability

Simple layout with easy navigation

Black and gray tone UI gives better contrast for easy recognition.

- Icons are evenly spread for easy recognition
- Consistent operation steps of each function for easy recall
- Home screen personalisation for ease of access to commonly used functions
- Pin regular settings for registering frequent or repeated jobs
- Clear visible light notifications for completed or error jobs
- Subtle sound notification for alert and attention

Smartphone becomes a "portable operation panel"

Seamless connectivity with mobile devices for Copy, Fax, Print, Scan¹ jobs using the Print Utility² application.

- Mobile device can be used as an alternative UI for operations control to minimise common touch points
- Frequent settings can be saved as "Favourites"
- Directly send fax or email with the addresses stored in the smartphone
- Minimise printer touch points for hygiene reasons
- Quickly establish direct Wi-Fi connection by scanning the QR code on the user panel
- Note: Connect to machine via wireless environment or Wi-Fi Direct connection.

*1: Scan to Mobile, E-mail, Scan to Folder.

*2: It can be downloaded free of charge from Google Play™ or App Store.

Flexibility in office layout

Supports wireless LAN environment^{*1}.

- Supports free addressing in the office with Wi-Fi support
- Up to five Wi-Fi Direct multifunction devices can be connected at the
- same time
 Supports direct mobile printing^{*2}
- Print Utility, AirPrint, and Mopria® Print Service are supported

*1: Optional.

*2: When connecting to Wi-Fi Direct.

Print out from any multifunction device within the office

With Server-less On-Demand Print*, you have the flexibility to print and collect the print outs from any of the connected multifunction devices.

- Improves productivity by printing from another available multifunction device when the current device is in use
- Up to 100 units can be linked
- Specific job settings can be revised at the device level to save time (1 sided to 2 sided, adding staple)
- * Optional.

Simple device management with Server-less Authentication

Server-less Authentication* enables user information to be synchronised among multifunction devices in the same group and allows administrators to reduce their workloads.

- Simply tap your card to link the user ID with the multifunction device
- The ID information is automatically shared with the other multifunction devices in the same network
- Authentication can be performed with any devices in the office

* Optional





Various features saving time and effort in scanning operation


Scanned data can be transferred through a variety of methods including Email, URL, and send to PC (SMB/FTP/SFTP).

- Data can be sent by using multiple features simultaneously
- Improve your digitalisation process with features including automatic orientation of scanned page to upright position, correcting the skewed page, or removing blank pages
- In addition to TIFF and JPEG, the scanned data can be converted to OCR-enabled* or high compression/ specific colour PDF or DocuWorks documents. Also they can be converted to editable Excel/Word documents*
- With ScanAuto, you can easily send the scanned data to your e-mail address by simply pressing a button
- * Optional.

Digitisation of paper documents for effortless document management

With Scan Delivery*, you can automatically process and store scanned images by simply pressing the preset button for each workflow or document type.

- Automate to set file format, file name, OCR*, etc.
- Automatically stores scanned and processed documents in the appropriate destination
- Specify particular words or characters in a document as the folder or file name
- Ø and other frequently mis-recognised characters can be read correctly
 * Optional.
- optional.



Where QR code or bar code is available on the headsheet or content body of the original document for scanning, Scan Delivery will recognise and process the information accordingly.

Streamline operations for remote work style

Do not miss any faxes when you are working remotely


Paperless fax function automatically stores received faxes into folders which can be transferred to a PC or sent as emails.

- Received faxes can be forwarded to your mobile device by email
- Received faxes can be transferred to Working Folder^{*1}
- It can be sorted by fax number, date received, and person in charge^{*2}
- $\bullet\,$ Incoming fax processing can be switched by time, day of the week and ${\rm period}^{*2}$
- For example, you can switch from paper-based output to an electronic transfer in a single operation.^{*2}
- *1: Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.
- *2: Optional.

Share information anytime, anywhere

With Working Folder* and internet access, documents can be viewed regardless of time and location.

- Can be linked smoothly with multifunction devices, DocuWorks, and mobile devices
- Documents in Working Folder can be printed from the control panel
 Scanned documents will be assigned a file name and stored in Working
- Folder. An email notification will be sent to relevant users



* Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.

Supporting Universal Print by Microsoft

By registering multifunction devices to Universal Print by Microsoft in advance, users^{*1} authenticated with Microsoft Entra ID^{*2} can print from anywhere through cloud.

*1: Organizations with or Microsoft Windows Enterprise or Microsoft 365 subscriptions. *2: Formerly Azure Active Directory.

Initiatives for environmental consideration

We are working to develop environmentally conscious products, including technologies that reduce the power consumption of multifunction devices and printers to achieve lower environmental impact. Fujifilm Group introduced the certification program in which we clarify the environmental value of each product by assessments at the time of product development, conduct the evaluation based on our in-house certification criteria and certify the products* that are excellent in reducing environmental impact as "Green Value Products". This product was certificated as a "Gold" rank product that contributes to reduction of environmental impact at industries' highest level.

* Products and services excellent in reducing environmental impact are those designed in consideration of environmental impact throughout their life cycle from acquisition of raw materials, production, usage, disposition, to reuse.

Initiatives for energy conservation

- Achieve both high image quality and energy conservation by equipping the LED printhead that enables space and energy saving design, as well as Super EA-Eco toner that has lowtemperature fusing performance
- Reduce the power consumption with the smart power saving feature that solely powers on the required parts according to the functions being used by customers

Easy and secure output even when you are working remotely


With Cloud On-Demand Print*, you can register documents from a PC or mobile device to the cloud server and print them from the designated multifunction device.

- Can be operated securely using a User ID and password
- Fear of loss or stolen data is minimised
- No dedicated driver is required
- \star Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.

Centralised cloud integration

Cloud Service Hub* allows single sign-on to multiple cloud storage services.

- Specific storage location can be assigned for scanned documents directly from the multifunction device
- Searching documents from multiple cloud services is supported
- Full-text search on scanned documents can be performed with OCR



* Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.

Initiatives for resources conservation

- Functions contributing to paper consumption reduction

 Private Charge Print, Scan, Paperless Fax, Pages per Side/ Multiple-Up etc.
- Adopt design for making products easy to reuse/recycle after use

Safeguard important information

Information is an important asset which should be protected at all cost

Protect from unauthorised user

Multiple options of setting user authorisation allow administrator to select a right combination as per given environment.

- Local Authentication
- Authentication by Remote Server*
- IC Card Authentication*
- User-specific feature access
- Private Charge Print
- * Optional.

Protects Data

Protects against any malicious intent of hacking, tampering with device / system settings.

- Encryption of stored data
- Uses TPM* 2.0 chip for encryption key management
- Deletes settings and document information all at once
- * Trusted Platform Module

Protects the information by means of strong encryption while transferring it between devices, servers etc.

- Encryption of communication paths by SSL/TLS or IPsec
- Encryption when transferring via SMBv3 and SFTP
- Scan file encryption/signature
- Email encryption and signature by S/MIME
- TLS version limit
- Elliptic curve cryptography
- WPA3

Reliable support system

Easy solutions to resolve problems

From supplies replacement to unexpected device failures, most problems can be resolved without waiting for the service representatives or sales representatives.

1. Resolve problem using the "Help" function on the device

- Self Help information is available on the control panel
- Self Help information can be accessed via the mobile device by scanning the QR code displayed on the control panel

Reip Print

2. "Remote Assistance" with the help of operators

- · Connects directly to the Support Centre
- An operator will remotely access the multifunction device to resolve the problem by guiding through the steps on the shared control panel

Protect from unauthorised access

Protects device settings at multiple levels by clearly demarking change restrictions for different target audience - End users, IT administrators and Service Engineers.

- Service representative operation restriction
- Account lock to prevent unauthorised access
- Information for changing the default password
- Warnings displayed when using global IP address

Prevents unauthorised program from installing without notice. Robust IT audits are supported with device data logs for easy tracking.

- Software signature verification
- Remote update restrictions
- IP address filtering
- Tampering detection at startup and automatic restoration when tampering is detected
- Prevention of tampering during operation
- Audit log
- Audit log system transfer

Prevents operation errors

Prevents information leakage due to inadvertent mistakes by administrators and users.

- Scan documents to be delivered to fixed destination
- Re-enter fax recipient
- Annotations
- Hidden text printing*
- * Optional.

Security certifications

 Certified with ISO/IEC 15408, which is the international standard for designing and operating IT security

Keeping a close eye on your multifunction device on a daily basis

Monitoring the multifunction device status to minimise operation down time.

- Check billing meter
- Automatically delivers consumables when cartridges level is low
- Detect machine errors for early invention to rectify the problem Note: You need to apply for using the EP service. (free of charge)

Making a backup of multifunction device's settings

Device Setup Editor is a free tool which helps you both, in editing device setting and creating a much-needed information backup for business continuity reasons.

- A back up the device / printer settings can be created onto the PC
- Administrator can optimize device usage by viewing/editing these settings, best suited for their environment.
- When installing a new device, these settings can be migrated (or cloned) from the existing device to the new device



Basic Specifications / Copy Function

Item		Model-CPS-EX	Model-CPS
Туре		Desktop / Console	
Memory Capacity		4 GB (Max: 4 GB)	
Storage Dev	ice Capacity*1	128 GB (Max: 128 GB)	
Scan Resolution		600 x 600 dpi	
Printing Res	olution	1,200 x 1,200 dpi	
Warm-up Ti	me ^{*2}	32 seconds or less (23 degrees	s Celsius room temperature)
Recovery Tir (Recovery Time	me from Sleep Mode)	20 seconds or less (23 degree	s Celsius room temperature)
Original Size	1	Maximum of A4, Letter, Legal f	or both Sheet and Book
	Max	A4, Letter, Legal	
Paper Size	Min	A6 ^{*3} [64 x 127 mm when using B	ypass Tray]
r aper Size	Image loss width	Lead edge 4.0 mm, Trail edge 4.	0 mm, Right/Left edge 4.0 mm
Paper	Paper Tray	60 to 220 gsm	
Weight*4	Bypass Tray	60 to 220 gsm	
First Copy O	utput Time	6.0 sec. (A4)	
Continuous	Copy Speed*5	63 ppm	
	Standard	Standard Tray: 550 sheets, By	
Paper Tray Capacity*6	Optional	550-Sheet Feeder: 550 sheets High Capacity Feeder: 2,000 s	
Capacity	Max	3,250 sheets [Standard + 550 Feeder]	-Sheet Feeder + High Capacity
Output Tray Capacity*6		500 sheets	400 sheets
Power Supply		AC220-240 V +/- 10 %, 8 A, 5	
Maximum Power		1,220 W (AC220 V +/- 10 %), 1,370 W (AC240 V +/- 10 %)	1,170 W (AC220 V +/- 10 %), 1,310 W (AC240 V +/- 10 %)
Consumptio		Sleep Mode: 0.4 W (AC230 V) Low Power Mode: 11 W (AC23 Ready Mode: 68 W (AC230 V)	30 V)
Dimensions*7		W 470 x D 503 x H 844 mm	W 470 x D 503 x H 644 mm
Weight*8		34.8 kg	30.6 kg

 34:.0 kg
 50:0 kg

 *1: The Storage Device Capacity is not totally available for customers.

 *2: It may change depending on usage conditions.

 *3: When using A6 size paper with the Standard Tray, the optional A5 LEF / A6 Tray Guide is required.

 *4: It is recommended to use our recommended paper. Correct print output may not be possible depending on the requirement.

 *5: The speed may be reduced due to the image quality adjustment.

 *6: 80 gsm paper.

 *7: 550-Sheet Feeder (height): 123 mm (The height increment when the option is installed).

 *8: Including Toner Cartridge. 550-Sheet Feeder: 6.6 kg.

Print Function

Item		Description	
Туре		Built-in type	
	Max	A4, Letter, Legal [215.9 x 520 mm when using Bypass Tray]	
Paper Size	Min	A6 ^{*1} [64 x 127 mm when using Bypass Tray]	
i aper size	Image loss width	Lead edge 4.0 mm, Trail edge 4.0 mm, Right/Left edge 4.0 mm	
Continuous I	Print Speed*2	Same as the Basic Specifications / Copy Function	
Printing	Standard	[PCL Driver] Standard: 1,200 x 1,200 dpi, High Quality: 1,200 x 1,200 dpi, High Resolution: 1,200 x 1,200 dpi	
Resolution	Optional	[Adobe [®] PostScript [®] 3 [™] Driver] High Speed (Standard): 1,200 x 1,200 dpi, High Quality: 1,200 x 1,200 dpi, High Resolution: 1,200 x 1,200 dpi	
Page	Standard	PCL5 / PCL6	
Description Language	Optional	Adobe® PostScript® 3™	
	Standard	[PCL Driver] Windows 11 (64 bit), Windows 10 (32 bit / 64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit), Windows Server 2012 R2 (64 bit), Windows Server 2012 (64 bit)	
Supported Operating		[Mac OS X Driver] macOS 13 / 12 / 11 / 10.15 / 10.14	
System*3	Optional	[Adobe [®] PostScript [®] 3 [™] Driver] Windows 11 (64 bit), Windows 10 (32 bit / 64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit), Windows Server 2012 R2 (64 bit), Windows Server 2012 (64 bit) macOS 13 / 12 / 11 / 10.15 / 10.14	
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T, USB3.0	
muenace	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)	

*1: When using A6 size paper with the Standard Tray, the optional A5 LEF / A6 Tray Guide is

required. *2: The speed may be reduced due to the image quality adjustment. The printing speed may be reduced depending on the document. *3: Please refer to our official website for the latest supported OS.

Scan Function

Item		Description
Туре		Colour Scanner
Scan Resolution		600 x 600 dpi, 400 x 400 dpi, 300 x 300 dpi, 200 x 200 dpi
Scan Speed		Same as the Scan Speed for the Duplex Automatic Document Feeder
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T
Interface	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)

Fax Function (Optional)

Item	Description
Original Size	Max: A4, Legal
Recording Paper Size	Max: A4, Legal; Min: A5
Transmission Time	2 seconds and more but fewer than 3 seconds ^{*1}
Transmission Mode	ITU-T G3
Applicable Lines	Telephone subscriber line, PBX, Fax Communication (PSTN), Maximum 1 port*2 (G3-1 port)
the Million Addies do support with a second control 200 object stars is the second the discrete doub	

*1: When A4 size document with approximately 700 characters is transmitted in standard image-quality (8 x 3.85 lines/mm) and in high-speed mode (28.8 kbps or faster, JBIG). Only indicates the time for transmitting the image information and does not include the communication control time. The total communication time will vary depending on the contents of the document, the type of machine receiving the fax, and line condition.
*2: No. of FAX lines is up to 1 port. Port refers to number of channels for FAX.

Duplex Automatic Document Feeder

Item		Description
		Max: A4, Letter, Legal; Min: A5 ^{*1} 60 to 128 gsm
Capacity*2		100 sheets
Scan	Copy (A4, Simplex)	63 ppm
Speed ^{*3}	Scan	B/W: 63 ppm, Colour: 52 ppm (1 pass, 2 sided scanning; B/W: 110 ppm, Colour: 83 ppm) [Standard Document (A4), 200 dpi, to Folder]
44 TI '' I I I I I I I I I I I I I I I I I		

*1: The minimum custom size is 139.7 x 139.7 mm. *2: 80 gsm paper. *3: The scanning speed varies depending on the documents.

High Capacity Feeder (Optional)

ltem	Description
Paper Size	A4 LEF, Letter LEF
Paper Weight	60 to 176 gsm
Feeding Capacity / Number of Tray*	2,000 sheets x 1-tray
Dimensions / Weight	W 725 x D 773 x H 459 mm, 24.0 kg

* 80 gsm paper.

F

E

Finisher-S (Optional)

Item		Description	
Туре		Sort (Offset available) / Stack (Offset available)	
Paper Size		A4, JIS B5, Letter, 8.5 x 13" (215.9 x 330.2 mm), Legal Custom Size: Width 176.0 to 215.9 mm, Length 250.0 to 355.6 mm	
Paper Weigh	t	60 to 220 gsm	
Paper	Finishing Tray	[Without Stapling] 500 sheets (80 gsm or less) [With Stapling] 60 sets, or 300 sheets (90 gsm or less)	
Capacity*1	Output Tray	500 sheets	
	Capacity	50 sheets (90 gsm or less)	
	Paper Size*2	Max: A4, Letter; Min: JIS B5	
Staple	Paper Weight	60 to 220 gsm	
	Position	Single stapling	
Dimensions / Weight		W 478 x D 451 x H 248 mm, 6.8 kg	
Note: The unit can be installed on Model-CPS-EX. *1: 70 gsm paper.			

*2: Available staple positions vary depending on the paper size.

Mailbox (Optional)

ltem		Description
Туре	Mailbox	4-bin Sort / Stack
Paper Size	Mailbox	A4, JIS B5, Letter, 8.5 x 13" (215.9 x 330.2 mm), Legal Custom Size: Width 176.0 to 215.9 mm, Length 250.0 to 355.6 mm
Paper Weight*	Mailbox	60 to 176 gsm
Paper	Mailbox	Each bin 100 sheets
Capacity	Output Tray	400 sheets
Dimensions /	/ Weight	W 411 x D 451 x H 248 mm, 5.3 kg
Note: The unit can be installed on Model-CPS-EX.		

* 70 gsm paper.

Notes 1) If the storage media of the base unit fail, loss of received data, accumulated data, registered setting data, etc. may occur. In no event shall "the company" be liable for any damages whatsoever arising from loss of data.

2) Functional spare parts will be available for at least 7 years after the product is no longer manufactured.

Enhanced basic functions

Copy

- Paper Supply
- Reduce/Enlarge Slight Reduction
- Auto 2 Sided Output
- Pages per Side (2 Pages / 4 Pages / 8 Pages)
- Copy Output (uncollated/collated)
- Copy (ID Card)
 Mixed Size Originals
- Original Size
- Background Suppression
- Book Copying
- Edge Erase
- Image Shift
- Mirror Image / Negative Image Image Rotation
- Booklet Creation
- Multiple-Up x Booklet Creation
 2 Sided Book Copying
- Covers
- Repeat Image
- Preset Repeat Image
 Annotations
- Watermark(optional)
- Joint Job
- Sample Job
- Delete Outside / Delete Inside
- Form OverlayStaple (optional)

Print

Secure Print

Sample Set

Delayed Print

Multiple-Up

Poster

• Print from Folder

Booklet Creation

Covers / Separators

Long Paper Printing

Envelope printing
 Private Charge Print

Staple (optional)

Charge Print
 Print from USB (optional)

• Server-less On-Demand Print (optional)

Form Registration

Adobe[®] PostScript[®] 3[™] (optional)

Multi-Model Print Driver 2

Microsoft Universal Print

• PCL

Fax (Optional)

- G3 × 1 port
- Internet Fax
 Send Direct Fax
- Address Book (maximum 5,000 entries)
- Broadcast Transmission / Group Transmission
- Redial / Resend Unsent Documents
- Rotate 90 Degrees
- Preview 2 Sided Scanning
- Resolution
- Lighten / Darken
- Original Type
 Mixed Size Originals
- Transmission Header Priority Send / Delay Start
- Cover Page
- Remote Folder
- Transmission Report
- Activity ReportRe-enter Recipient
- Prevents Unsolicited Faxes
- Prohibit Direct FaxReceive Paperless Fax
- - Simple Image Log Support
 - Paperless Fax Delivery (optional)

Scan

Scan to Folder

- (TWAIN driver/Web browser) Transfer via SMB/FTP/SFTP
- Email • Scan (URI)
- Scan to USB (optional)
- Simultaneous transmission such as Email / Transfer via SMB, etc.
- ScanAuto
- Preview
- Color Scanning2 Sided Scanning
- Mixed Size Originals
- File Format: TIFF / JPEG / PDF^{*1} / XDW(DocuWorks)^{*2}
- Microsoft Excel/Word format(optional)
- Single File for Each Page
- Searchable Text (optional)
 Background Suppression
- Shadow Suppression
- Auto Upright Orientation
- Skew Correction
- Skip Blank Pages
- Book Scanning Job Flow Sheets
- Scan Delivery (optional)

- Local Authentication Remote Authentication (optional)
 Microsoft Entra ID^{*3} linked
- authentication (optional)

Others

- IC Card Log In (optional)
 Serverless Authentication (optional)
- Wi-Fi Support (optional)
- Data EncryptionData Overwrite (optional)
- Image Log (optional)
- Message screen from an administrator
- Job History Export

*1: High Compression / Specific color / Searchable Text / Security / Signature / Optimise For Quick Web View

*2: High Compression / Specific color / Searchable Text / Security / Signature

*3: Formerly Azure Active Directory

fujifilm.com/fbau



FUJIFILM Business Innovation Australia Ptv Ltd

8 Khartoum Road MACQUARIE PARK NSW 2113 Australia Tel. +61 2 9856 5000

The available model varies depending on the country/region. Please ask the sales representatives for details. The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

Reproduction Prohibitions Please note that reproduction of the following is prohibited by law : •Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. Unused postage stamps, post cards, etc. Certificate stamps stpulated by law. •Reproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

tamily use or other similar uses within a limited circle. **Trademarks** •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. *Apeos, DocuWorks, Working Folder, Cloud Service Hub, and Cloud On-Demand Print are registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Microsoft, Active Directory, Azure, Microsoft Entra, Microsoft Edge, Excel, OneDrive, PowerPoint, SharePoint, Microsoft Teams, Windows, and Windows Server are registered trademarks of US Microsoft Corporation in the US. and other countries. +Apple, Mac. macOS, OS X, MirPrint, and AlrPrint logo are trademarks of Apple Inc. registered in the US. and other countries and regions. •Adobe, Adobe logo, PostScript, and PostScript Rogo are either registered trademarks of trademarks of Adobe in the United States and/or other countries. •Mopria, the Mopria Logo, and the Mopria Alliance word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. •QR Code is a registered trademark for DENSO WAYE INCORPORATED. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.



For Your Safety

Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection Otherwise, electronic shock may result in the case of a failure or short circuit.

- Multiple-Up x Booklet Creation