

## Operating Environment of Print Utility

Item	Description
<b>Network Protocol</b>	LPD
<b>&lt;iOS&gt; Supported Models / Supported Operating System</b>	iPad (5th generation) or later, iPad mini 2 or later, iPad Air and later, iPad Pro, iPhone 5s or later, iPod touch (6th generation) or later iPad/iPhone/iPod touch iOS 13.0 or later, iPad OS 13.0*1
<b>&lt;Android&gt; Tested devices &amp; OS versions</b>	Google Pixel7a (Android™14.0) Google Pixel7 (Android™13.0) Lenovo Yoga Tab 11 (Android™12.0) Google Pixel4 (Android™ 10.0) Google Pixel (Android™ 10.0) Sony Xperia 5 (Android™ 10.0) Sony Xperia XZ3 (Android™ 9.0) Samsung Galaxy S10 (Android™ 9.0) OPPO R15 Neo (Android™ 8.1.0) Huawei Nexus6P (Android™ 8.1.0) Huawei P20 lite (Android™ 8.0) Samsung Galaxy S8 (Android™ 9.0) Samsung Galaxy Tab S5e (Android™ 9.0) Vivo iQoo (Android™ 9.0) HTC Nexus9 (Android™ 7.1.1) Samsung Galaxy S6 (Android™ 7.0) Xiaomi Mi 5 (Android™ 8.0) LG Nexus5 (Android™ 6.0.1) Samsung Galaxy S4 (Android™ 5.0.1)
<b>Supported Languages</b>	English, Chinese (Simplified / Traditional), Korean, Japanese, Thai, Vietnamese, Indonesian
<b>Features*2</b>	Print <ul style="list-style-type: none"> <li>- Printing photos saved in the photo album</li> <li>- Printing photos taken by the internal camera</li> <li>- Printing DocuWorks and PDF documents Printing from Application</li> <li>- Server-less On-Demand Print</li> <li>- Working with ApeosWare Management Suite 2</li> </ul> Scan to Mobile Capture Copy E-mail Scan to Folder Fax Favorites Linking with NFC

Item		Description
Print	Printing photo/image/website	Specify the number of copies (max 99) Paper size: A3, A4, Letter, A5, B4, B5, 4 x 6" (101.6 x 152.4 mm), 8.5x 14", 11 x 17", 2L-size (127 x 178 mm), Postcard (100 x 148 mm) Image orientation: Portrait / Landscape Output Colour: On / Off 2-sided print: On / Off Pages Per Sheet: 2 Pages Up / 4 Pages Up / 8 Pages Up / 16 Pages Up / 32 Pages Up (32 Pages up only for printing from photo gallery) Stapling: Off / 1 Staple Top Left Paper tray: Automatically Select / Bypass tray Paper type: Plain / Heavy weight / Heavy weight Reload Authentication and Accounting
	For PDF/ DocuWorks documents	Specify the number of copies (max 99) Paper size: Same as Paper Size, A4, A3, A5, B4, B5, Letter, Legal Collated: On / Off Output Colour: On / Off 2-sided print: 1sided Print / 2sided Print / 2sided, Flip on short Edge Pages Per Sheet: 2 Pages Up / 4 Pages Up Stapling: Off / 1 Staple Top Left Hole Punch: No hole punch, 2-hole punch, 3-hole punch, 4-hole punch Paper tray: Automatically Select / Bypass tray Authentication and Accounting
Scan to Mobile <sup>*2</sup>		File Format (JPEG / PDF / DocuWorks), Scan Method, Image Type (Full Colour / Grayscale), Scan Size (A4 / Letter), Resolution (200 dpi / 300 dpi)
Copy <sup>*2</sup>		Quantity, Output Colour, Original Size, 2 Sided, Paper Supply, Reduce / Enlarge, Paper per Side, Lighten / Darken, Staple, Original Type, Original Orientation, Background Suppression, Negative Image
Fax <sup>*2</sup>		Resolution, Original Size, 2 Sided, Lighten / Darken, Original Type You can select the recipient e-mail address from the phonebook of your smartphone or tablet.
E-mail <sup>*2</sup>		File Format (PDF, XDW, TIFF/JPEG Auto, TIFF), Colour Scanning, Original Size, 2 Sided, Resolution, Quality / File Size, Original Type, Original Orientation, Skip Blank Pages, Background Suppression You can select the recipient e-mail address from the phonebook of your smartphone or tablet. Only one e-mail address can be specified as a recipient.
Scan to Folder <sup>*2</sup>		Colour Scanning, Original Size, 2 Sided, Resolution, Quality / File Size, Original Type, Original Orientation, Skip Blank Pages, Background Suppression.
Operability		Text to Speech, Colour inversion, Enlarged screen display, Gesture UI, External keyboard can be connected
Supported authentication methods		Non-authentication (including Deemed authentication) Local authentication (including Server-less Authentication Kit)

\*1: Use of the latest version is recommended.

\*2: These functions may not be available depending on the type of MFP.