

# ApeosPort<sup>®</sup> Print 4020SD

A4 Monochrome Printer

## Features



B/W



40 ppm



Print



## High Performance & Productivity

- Fast printing of 40 ppm, with FPOT as fast as 5.9 seconds
- Supports standard media input capacity of 350 sheets and up to a maximum of 900 sheets including 100-Sheet Multipurpose Feeder and optional 550-Sheet Tray
- Easy to connect with built-in Wi-Fi, Ethernet or USB

## Security



- Prevents information leakage with Confidential Print function
- Controls access to the Printer functions
- Supports settings to delete temporary data files in memory

## Easy Operation

- Two-line display lets you configure and monitor vital system information
- Compatible with Mopria<sup>®</sup> and AirPrint, you can easily print from mobile devices

## Ecology

- Standard two-sided printing saves paper
- Supports ECO mode for easy presetting of features that save paper and toner



## Specifications

Printing	
Display	2-line All Points Addressable (APA) monochrome LCD display
Print Speed: Up to	Black: 40 ppm (A4)
Time to First Page: As fast as* <sup>1</sup>	Black: 5.9 seconds
Print Resolution	Black: 2400 Image Quality, 600 x 600 dpi
Memory	256 MB
Hard Disk	Not Available
Supplies	
Toner Cartridge Yields (up to)	6,000 -page Black High Yield Cartridge / up to: 20,000 -page Black Extra High Yield Cartridge
Imaging Unit Estimated Yield: Up to	40000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage
Cartridge(s) Shipping with Product	3,000 -page Toner Cartridge
Paper Handling	
Included Paper Handling	100-Sheet Multipurpose Feeder, Integrated Duplex, 150-Sheet Output Bin, 250-Sheet Input
Optional Paper Handling	550-Sheet Tray
Paper Input Capacity: Up to	Standard: 350 pages 75 gsm / Maximum: 900 pages 75 gsm
Paper Output Capacity: Up to	Standard: 150 pages 75 gsm / Maximum: 150 pages 75 gsm
Media Types Supported	Paper Labels, Card Stock, Plain Paper, Envelopes
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope
General Information	
Standard Ports	Ethernet 10/100 Base TX (RJ-45), USB Compatible with USB 2.0 Specification (Type B) , 802.11 b/g/n Wireless
Noise Level: Operating	53 dBA (Print)
Specified Operating Environment* <sup>2</sup>	Humidity: 8 to 80%* <sup>3</sup> Relative Humidity, Temperature: 10 to 32°C* <sup>4</sup> (excluding faults caused by condensation)
Size (mm - H x W x D) / Weight (kg)	222 x 368 x 363 mm / 9.3 kg

\*1: The time from when the device starts the print job from standard sheet tray until the trailing edge of the first page exits into output tray. Numeric value may vary based on the output environment. \*2: Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. \*3: When the humidity is 80%, the temperature is 25.5°C or less. \*4: Humidity 45% or less when the temperature is 32°C.

## Option

Product Name	Product Code
550-Sheet Tray	EL300955

## Consumables\*<sup>1</sup>

Product Name	Product Code	Product Life
Black High Yield Use and Return Toner Cartridge* <sup>2</sup>	CT203550	Up to 6,000 pages
Black Extra High Yield Use and Return Toner Cartridge* <sup>2</sup>	CT203478	Up to 20,000 pages
Black Extra High Yield Regular Toner Cartridge	CT203524	Up to 20,000 pages
Imaging Unit	CT351280	Up to 40,000 pages

\*1: Average standard page yield value declared in accordance with ISO/IEC 19752.

\*2: The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

### Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

For more information or detailed product specification, please call or visit us at  
**Branch of FUJIFILM Business Innovation Asia Pacific Pte. Ltd.** (Cambodia Branch)

No. 321, City Tower 5th Floor, Room 5B, Mao Tse Toung Blvd, Phsar Depo 1, Khan Toul Kork, Phnom Penh, Cambodia  
 Tel. +855-0-2396-4501 Fax. +855-0-2396-4505

[fujifilm.com/fbca](http://fujifilm.com/fbca)

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

\*FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. \*ApeosPort is registered trademarks or trademarks of FUJIFILM Business Innovation Corp. \*Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. \*Mopria®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. \*All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

The information is as of April, 2023.

PIC-0202 CA (2111-R1)