

ApeosPort® 4730SD

A4 Monochrome Multifunction Printer



Features



B/W



A4



47 ppm



Optional

Copy

Print

Fax

Scan

High Performance & Productivity

- High-speed printing of 47 ppm with a small footprint
- 1-pass Duplex automatic document feeder supports high-speed scanning of 94 ppm for Monochrome and 60 ppm for Colour
- Supports 650 sheets paper feeding as standard, including 100-sheet Multipurpose Feeder. Up to 3 optional 550-Sheet Tray can be added to support maximum capacity of up to 2,300 sheets
Different types of trays can be combined
- Supports Gigabit Ethernet, USB, and optional Wi-Fi for flexible networking

Security

- Prevents information leakage with Confidential Print function
- Controls access to the MFPs functions
- Supports IC card authentication*. You can easily authenticate without entering Username / Password.
*Optional
- Supports settings to delete temporary data files in memory & hard disk as an option

Easy Operation

- Intuitive 7.0-inch touch panel offers smooth, tablet-like interaction
- Supports customizable applications such as Card Copy and Scan Centre, providing flexibility to extend functionality
- Compatible with Mopria® and AirPrint, you can easily print from mobile devices
- Direct print* from/ scan to a USB flash drive without using a computer
*PDF/TIFF/JPEG"


Ecology

- Standard two-sided printing saves paper
- Supports ECO mode for easy presetting of features that save paper and toner



- Optional **250-sheet tray***
- Optional **550-sheet tray***
- Optional **550-sheet Lockable tray***

* : Up to 3 stages can be added. (Different types of trays can be combined)



Specifications

Printing	
Display	7-inch (17.8 cm) Colour touch screen
Print Speed: Up to	Black: 47 ppm (A4)
Time to First Page: As fast as ^{*1}	Black: 6 seconds
Print Resolution	Black: 1200 Image Quality, 1200 x 1200 dpi, 2400 Image Quality, 600 x 600 dpi
Memory	2048 MB
Hard Disk	Option available
Copying	
Copy Speed: Up to	Black: 47 ppm (A4)
Time to First Copy: As fast as ^{*2}	Black: 6.1 seconds
Scanning	
Scanner Type / ADF Scan	Flatbed scanner with ADF / DADF (single pass Duplex)
A4/Ltr Duplex Scan Speed: Up to	Black: 94 / 100 ppm / Colour: 60 / 64 ppm
A4/Ltr Simplex Scan Speed: Up to	Black: 47 / 50 ppm / Colour: 30 / 32 ppm
ADF Paper Input Capacity: Up to	100 pages 75 gsm
Faxing	
Modem Speed	ITU T.30, V.34 Half-Duplex, 33.6 Kbps
Supplies	
Toner Cartridge Yields (up to)	25,000-page Ultra High Yield Cartridge
Imaging Unit Estimated Yield: Up to	60000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage
Cartridge(s) Shipping with Product	6,000-page Toner Cartridge
Paper Handling	
Included Paper Handling	550-Sheet Input, 100-Sheet Multipurpose Feeder, Integrated Duplex, 250-Sheet Output Bin
Optional Paper Handling	250-Sheet Tray, 550-Sheet Tray, 550-Sheet Lockable Tray
Paper Input Capacity: Up to	Standard: 650 pages 75 gsm / Maximum: 2300 pages 75 gsm
Paper Output Capacity: Up to	250 pages 75 gsm
Media Types Supported	Card Stock, Envelopes, Paper Labels, Plain Paper, Transparencies
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Letter, Statement, Executive, Universal, DL Envelope, Folio, 10 Envelope
General Information	
Standard Ports	One Internal Card Slot, Rear USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified port (Type A), Rear USB 2.0 Specification Hi-Speed Certified Port (Type A)
Wi-Fi	Option available (802.11 a/b/g/n/ac Wireless)
Noise Level: Operating	Print: 55 dBA / Copy: 56 dBA / Scan: 55 dBA
Specified Operating Environment ^{*3}	Humidity: 8 to 80% ^{*4} Relative Humidity, Temperature: 10 to 32°C ^{*5} (excluding faults caused by condensation)
Size (mm - H x W x D) / Weight (kg)	545 x 489 x 476.5 mm / 22.3 kg

*1: The time from when the device starts the print job from standard sheet tray until the trailing edge of the first page exits into output tray. Numeric value may vary based on the output environment. *2: Numeric value varies depending on the output environment. *3: Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. *4: When the humidity is 80%, the temperature is 25.5°C or less. *5: Humidity 45% or less when the temperature is 32°C.

Options

Product Name	Product Code
250-Sheet Tray	EL300954
550-Sheet Tray	EC104315
550-Sheet Lockable Tray	EC104334
Wireless Print Server	EC104320
500 GB Hard Disk	EC104326
Contactless Authentication Device	EC104333

Consumables^{*1}

Product Name	Product Code	Product Life
Black Ultra High Yield Use and Return Toner Cartridge ^{*2}	CT203475	Up to 25,000 pages
Black Ultra High Yield Regular Toner Cartridge	CT203521	Up to 25,000 pages
Black Use and Return Imaging Unit ^{*2}	CT351279	Up to 60,000 pages
Black Regular Imaging Unit	CT351308	Up to 60,000 pages

*1: Average standard page yield value declared in accordance with ISO/IEC 19752.

*2: The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

For more information or detailed product specification, please call or visit us at
Branch of FUJIFILM Business Innovation Asia Pacific Pte. Ltd. (Cambodia Branch)

No. 321, City Tower 5th Floor, Room 5B, Mao Tse Toung Blvd, Phsar Depo 1, Khan Toul Kork, Phnom Penh, Cambodia
 Tel. +855-0-2396-4501 Fax. +855-0-2396-4505

fujifilm.com/fbca

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

•FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort is registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. •Mopria®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

The information is as of April, 2023.

PIC-0195 CA (2111-R2)