## **Print Utility for iOS / Print Utility for Android Operating Environment**

## Operating Environment of Print Utility for iOS / Print Utility for Android

Item	Description
Network Protocol	LPD
<ios> Supported Models / Supported Operating System</ios>	iPad (5th generation) or later, iPad mini 2 or later, iPad Air and later, iPad Pro, iPhone 5s or later, iPod touch (6th generation) or later iPad/iPhone/iPod touch iOS 13.0 or later, iPadOS *1
<android™> Tested devices &amp; OS versions</android™>	Google Pixel4 (Android <sup>™</sup> 10.0) Google Pixel (Android <sup>™</sup> 10.0) Sony Xperia 5 (Android <sup>™</sup> 10.0) Sony Xperia XZ3 (Android <sup>™</sup> 9.0) Samsung Galaxy S10 (Android <sup>™</sup> 9.0) OPPO R15 Neo (Android <sup>™</sup> 8.1.0) Huawei Nexus6P (Android <sup>™</sup> 8.1.0) Huawei P20 lite (Android <sup>™</sup> 8.0) Samsung Galaxy S8 (Android <sup>™</sup> 9.0) Samsung Galaxy Tab S5e (Android <sup>™</sup> 9.0) Vivo iQoo (Android <sup>™</sup> 9.0) HTC Nexus9 (Android <sup>™</sup> 7.1.1) Samsung Galaxy S6 (Android <sup>™</sup> 7.0) Xiaomi Mi 5 (Android <sup>™</sup> 8.0) LG Nexus5 (Android <sup>™</sup> 6.0.1) Samsung Galaxy S4 (Android <sup>™</sup> 5.0.1)
Supported Languages	English, Chinese (Simplified / Traditional), Korean, Japanese, Thai, Vietnamese, Indonesian
Features *2	Print - Printing photos saved in the photo album - Printing photos taken by the internal camera - Printing DocuWorks and PDF documents Printing from Application - Server-less On-Demand Print - Working with ApeosWare Management Suite Scan to Mobile Capture Copy E-mail Store to Folder Fax Favorites Linking with NFC

	Item	Description
Print	Printing photo/image/website	Specify the number of copies (max 99)  Paper size: A3, A4, Letter, A5, B4, B5, 4 x 6" (101.6 x 152.4 mm), 8.5 x 14", 11 x 17", 2L-size (127 x 178 mm), Postcard (100 x 148 mm)  Image orientation: Portrait / Landscape  Output Colour: On / Off  2-sided print: On / Off  Pages Per Sheet: 2 Pages Up / 4 Pages Up / 8 Pages Up / 16 Pages Up / 32  Pages Up (32 Pages up only for printing from photo gallery)  Stapling: Off / 1 Staple Top Left  Paper tray: Automatically Select / Bypass tray  Paper type: Plain / Heavy weight / Heavy weight Reload  Authentication and Accounting
	For PDF/DocuWorks documents	Specify the number of copies (max 99)  Paper size: Same as Paper Size, A4, A3, A5, B4, B5, Letter, Legal  Collated: On / Off  Output Colour: On / Off  2-sided print: 1sided Print / 2sided Print / 2sided, Flip on short Edge  Pages Per Sheet: 2 Pages Up / 4 Pages Up  Stapling: Off / 1 Staple Top Left  Hole Punch: No hole punch, 2-hole punch, 3-hole punch, 4-hole punch  Paper tray: Automatically Select / Bypass tray  Authentication and Accounting
Scan to N	Mobile *2	File Format (JPEG / PDF / DocuWorks), Scanning Method, Image Type (Full Colour / Grayscale), Scan Size (A4 / Letter), Resolution (200 dpi / 300 dpi)
Copy *2		Quantity, Output Colour, Original Size, 2 Sided, Paper Supply, Reduce / Enlarge, Paper per Side, Lighten / Darken, Staple, Original Type, Original Orientation, Background Suppression, Negative Image
Fax *2		Resolution, Original Size, 2 Sided, Lighten / Darken, Original Type You can select the recipient e-mail address from the phonebook of your smartphone or tablet.
E-mail *2		File Format (PDF, XDW, TIFF/JPEG Auto, TIFF), Colour Scanning, Original Size, 2 Sided, Scan Resolution, Quality / File Size, Original Type, Original Orientation, Skip Blank Pages, Background Suppression You can select the recipient e-mail address from the phonebook of your smartphone or tablet.  Only one e-mail address can be specified as a recipient.
Store to I	Folder *2	Colour Scanning, Original Size, 2 Sided, Scan Resolution, Quality / File Size, Original Type, Original Orientation, Skip Blank Pages, Background Suppression
Operability		Text to Speech, Colour inversion, Enlarged screen display, Gesture UI, External keyboard can be connected

Item	Description
Supported authentication methods	Non-authentication (including Deemed authentication)  Local authentication (including Server-less Authentication Kit)

<sup>\*1:</sup> Use of the latest version is recommended.

<sup>\*2:</sup> These functions may not be available depending on the type of MFP.