

Xerox Nuvera® 288/314 EA and MX Perfecting Production System

SPECIFICATIONS



PRINT CONTROLLER

RIP

- Xerox® FreeFlow® Print Server
- Parallel RIP (available for PDF, PS, Xerox® VIPP® data streams)
- 3.0 GHz Dual Core Processor (optional second dual core processor with additional 8 GB memory)
- Server Class Processors:
 - AMD® Opteron™ Technology
 - Sun® Solaris® 11 OS
- 19" color flat panel monitor (attached), USB keyboard, USB mouse
- Data Stream options:
 - TIFF/PCL®5e and PCL6/ASCII-standard Adobe® PDF; Adobe PostScript® Level 3; Multi-page TIFF; PPML; LCDS/Metacode; IPDS™—includes support for QR barcodes, True Type® fonts (UTF-8)
- Connectivity:
 - Ethernet interface (10/100BaseT; 1 GB)

STORAGE

- Memory: 8 GB (RAM)
- Hard Drive: 500 GB SATA
- DVD + RW Drive (CD write only)
- Optional: 1 TB SATA Drive

PRINT SUBMISSION DRIVERS

- Microsoft® Windows® up to Windows 11
- Apple® Macintosh® through macOS Monterey 12
- Sun Microsystems™ Solaris 2.6, 7.x, 8.x, 9.0, 10
- Linux® 2.x
- Web User Interface

SECURITY

- Solaris 11 OS
- Four administrator-selectable security modes and levels
- Fully customizable profiles for each level
- Encrypted job submission modes
- Secure print mode (restricts page reprints)
- IP address access filtering
- Strong password support
- Data overwrite option

PRINTER MODULE

Image Quality

- 1200 x 1200 dpi RIP resolution
- 4800 x 600 dpi print resolution
- Halftone screens: 85, 106, 134, 156 lpi
- Operator adjustable settings: light/dark, contrast sharpness, Toner Saver
- Semi Conductive Magnetic Brush Technology (SCMB) with Emulsion Aggregation (EA) Toner
- Silicon/Teflon™ fusing for sharper halftones
- Dual beam Raster Output Scanner (ROS)
- Print path image-to-sheet and front-to-back registration ± 0.65 mm

Toner

- EA Toner: 210,000 prints/4.1 kg bottle (one bottle per system, second optional)
- MICR Toner: 90,000 prints/5 kg bottle (two bottles per system)

Print Speed

- Duplex 8.5 x 11"/A4 speeds of 288 or 314** impressions per minute
- Duplex 11 x 17"/A3 speeds of 144 or 157** impressions per minute

SHEET ENHANCEMENT MODULE

- Post-process module provides:
 - Outstanding stack quality
 - Sheet flatness for enhanced reliability of finishing options (booklet makers, perfect binders, stackers, etc.)
 - Automatically adjusts per individual media type

MEDIA FEEDING AND INSERTION OPTIONS

Sheet-Feed and Insertion Modules*

- Four trays
- Total 5,800 sheets per module
- Vacuum Air Shuttle feed system
- Optional: Up to four modules available in any combination
- Tray 1: 1,600 sheets (140 x 210 mm to 229 x 320 mm)
- Tray 2: 3,100 sheets (140 x 210 mm to 229 x 320 mm)
- Tray 3 and 4: 550 sheets each (182 x 203 mm to 320 x 470 mm)

OVERSIZED HIGH CAPACITY SHEET-FEED AND INSERTION MODULES*

- Two trays
- Total 3,200 sheets per module
- Vacuum Air Shuttle feed system
- Optional second module available
- Tray 1: 1,600 sheets (182 x 203 mm to 320 x 491 mm)
- Tray 2: 1,600 sheets (182 x 203 mm to 320 x 491 mm)

*Capacity based on 75 gsm

**EA Configuration only

Xerox Nuvera® 288/314 EA and MX Perfecting Production System

SPECIFICATIONS

EA MEDIA LATITUDE

- Uncoated: 44–300 gsm
- Coated: 90–300 gsm

MICR MEDIA LATITUDE

- Uncoated: 52–300 gsm
- Coated: 90–140 gsm

XEROX® PRODUCTION STACKER*

Maximum Stack Capacity

- 2,850/2,600 with Stack Cart Kit
- Stack-nesting design enables the delivery of up to 2,850 sheets at a time—without interruption
- Unload while run (with one/each unit) keeps production moving
- Top Tray: 250 sheets (80 gsm)
- Xerox® DS3500 Stacker: 3,500 single sheets (80 gsm), 7,000 dual sheets (80 gsm) and 350.5 mm
- Media Sizes:
 - Top Tray: 140 x 203 mm to 320 x 491 mm
 - Bypass with Rotation: 177.8 x 254 mm to 320 x 364 mm
 - Bypass without Rotation: 140 x 203.2 mm to 320 x 491 mm
 - Stacker: 177.8 x 203.2 mm to 320 x 491 mm
- Specialty Media: Carbonless, Tabs, NeverTear, and Pre-printed Offset
- Compatibility: Xerox Nuvera® 144/157 EA and MX
- Maximum number of stackers per configuration: 3
- Optional Stack Cart

ELECTRICAL REQUIREMENTS

- Dual 187–240 VAC (nominal), 50 Amp, 50/60 Hz line service
- Feeders and Finisher Modules will require additional power
- Power Consumption (Ready)
 - Production Stacker Model : 1600 W
 - Basic Finisher Model : 1316 W
 - Tape Binder Model : 1758 W
- Consult the Installation Planning Guide for detailed power requirements

ENVIRONMENTAL REQUIREMENTS

- Temperature: 10°C to 31°C
- Relative humidity: 15% to 85%; wet bulb limitation 25°C
- Run mode heat emissions: Configuration dependent; consult Installation Planning Guide

PHYSICAL CHARACTERISTICS

Sheet-Feed and Insertion Module			
Width	Depth	Height	Weight
805 mm	711.2 mm	1,133 mm	192 kg
Print Engine			
Width	Depth	Height	Weight
2,235 mm	737 mm	1,565 mm	726 kg**
Sheet Enhancement Module			
Width	Depth	Height	Weight
381 mm	711.2 mm	1,054 mm	76.2 kg
Xerox® Production Stacker			
Width	Depth	Height	Weight
889 mm	768.4 mm	1,133 mm	237 kg

*Capacity based on 75 gsm

**With consumables loaded

For more information, visit www.xerox.com.

Note : Some models or features are available only in selected countries.

© 2022 Xerox Corporation. All rights reserved. Xerox®, Xerox Nuvera®, VIPP®, and FreeFlow® are trademarks of Xerox Corporation in the United States and/or other countries.

xerox™

FUJIFILM Business Innovation Asia Pacific Pte. Ltd.

Authorized Distributor

Reg. No. 199202000004 (993478-A) ST No. W10-1808-32000018

Head Office:

Ground Floor, Axis Business Park, Block C, No. 10 Jalan Bersatu 13/4, 46200 Petaling Jaya, Selangor, Malaysia.
Tel: 03-7882 2888 Fax: 03-7882 2828 Customer Service Hotline: 1300-88-1163

Branches:

Penang: No. 3-G, 3-1 & 3-2, Persiaran Bayan Indah, Bayan Bay, 11900 Bayan Lepas Penang.
Tel: 04-643 5000 Fax: 04-644 4677

Johor Bahru: No.21 & 23, Jalan Setia Tropika 1/28, Taman Setia Tropika, 81200 Kempas, Johor Bahru.
Tel: 07-238 7868 Fax: 07-238-2678

Melaka: No.17, Jalan KL3/11, Kota Laksamana, 75200 Melaka.
Tel: 06-281 0466 Fax: 06-281 0408

Kota Kinabalu: Block K, Lot 65, Ground-5th Floor, KK Time Square, 88100 Kota Kinabalu, Sabah.
Tel: 088-486 888 Fax: 088-486 668

Kuching: No. 201, Lot 3050, Eastmoore Centre, 2 1/2 Mile Jalan Rock, 93200 Kuching, Sarawak.
Tel: 082-240 633, 082-254 633 Fax: 082-418 733

fujifilm.com/fbmy

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

Trademarks •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •Adobe, Adobe logo, Adobe PDF, PostScript and PostScript logo are either registered trademarks or trademarks of Adobe in the United States and/or other countries. •Microsoft and Windows are trademarks of the Microsoft group of companies. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.