



Modern Architecture

For architecture in the present day

Modern architecture, or modernist architecture, was an architectural movement or architectural style based upon new and innovative technologies of construction, particularly the use of glass, steel, and reinforced concrete; the idea that form should follow function (functionalism); an embrace of minimalism; and a rejection of ornament.[1] It emerged in the first half of the 20th century and became dominant after World War II until the 1980s, when it was gradually replaced as the principal style for institutional and corporate buildings by postmodern architecture. The revolution in materials came first, with the use of cast iron, drywall, plate glass, and reinforced concrete, to build structures that were stronger, lighter, and taller. The cast plate glass process was invented in 1848, allowing the manufacture of very large windows.



The Brighter Choice

Lamp-Free High Brightness
Business & Education Projectors

3rd GEN LED TECHNOLOGY FOR GREATER SUSTAINABILITY



**8 Hours Perday
Last For 10 Years**



Maintenance Free



Lamp Free



**Ultra-Large Screen with
Lower Cost-per-inch**



**Greater Sustainability with a
Lamp-Free Light Source
Up to 5000 ANSI Lumens**



**Adaptable to Any
Environment with Optical Zoom**



**Sealed Optical
Engine with IP5X**



**360 Degrees of Projections for
Versatile Application**



**H/V Lens Shift for Easier
Positioning**





	LS550WHE	LS510WE	LS860WU	LS710HD	LS832WU	LS920WU
Projection System	WXGA		WUXGA	FHD	WUXGA	
Native Resolution	1280x800		1920x1200	1920x1080	1920x1200	
Brightness (ANSI Lumens)	3000	3800	5000	4200	5000	6000
Contrast Ratio	3000000:1					
Light Source Type	LED			Phosphor		
Light Source Life	30000			20000		
(Normal)	157W	240W	430W	245W	504W	450W
Throw Ratio	0.49	1.55- 1.70	0.81-0.89	0.49	0.252	1.36-2.18
Keystone	V:+36°/-40°	± 40° (V)	H:+/-40°, V:+/-40°	H:+/-15°, V:+/-15°	H:+10°/-8°, V:+/-10°	H:+/-40°, V:+/-40°
Optical Zoom	Fixed	1.1X		Fixed		1.6X
Audible Noise (Nor/Eco)	30dB/26dB	34dB/28dB		34dB/31dB	36dB/29dB	
Input						
Computer In	N/A	1	1	N/A	1	
Composite	N/A		1	N/A	1	
S-Video	N/A		1	N/A	1	
Audio in (3.5mm)	1		1	N/A	1	
HDMI	1		2			
Output						
Monitor Out	N/A	1	1	N/A	1	
Audio Out (3.5mm)	1					
Speaker	2W		10Wx2	15Wx2	10W Cubex2	10W
USB Type A	1 (5V/2A)			1 (5V/1.5A)		
Control						
RS232 (male)	1					
RJ45	1	N/A		1		
USB Type A (service)	1 (share with USB A Output)				N/A	1 (share with USB A Output)

fujifilm.com/fbmy

FUJIFILM

FUJIFILM Business Innovation Asia Pacific Pte. Ltd.

Reg. No. 199202000004 (993478-A) ST No. W10-1808-32000018

Head Office:

Ground Floor, Axis Business Park, Block C, No. 10 Jalan Bersatu 13/4, 46200 Petaling Jaya, Selangor, Malaysia.
Tel: 03-7882 2888 Fax: 03-7882 2828 Customer Service Hotline: 1300-88-1163

Branches:

Penang: No. 3-G, 3-1 & 3-2, Persiaran Bayan Indah, Bayan Bay, 11900 Bayan Lepas, Penang.
Tel: 04-643 5000 Fax: 04-644 4677

Johor Bahru: No.21, Jalan Setia Tropika 1/28, Taman Setia Tropika, Kempas, 81200 Johor Bahru, Johor.
Tel: 07-238 7868 Fax: 07-238-2678

Melaka: No.17, Jalan KL3/11, Kota Laksamana, 75200 Melaka.
Tel: 06-281 0466 Fax: 06-281 0408

Kota Kinabalu: Block K, Lot 65, Ground Floor, KK Times Square, 88100 Kota Kinabalu, Sabah.
Tel: 088-486 888 Fax: 088-486 668

Kuching: No. 201, Lot 3050, Eastmoore Centre, 2 1/2 Mile, Jalan Rock, 93200 Kuching, Sarawak.
Tel: 082-240 633 Fax: 082-418 733

The available model varies depending on the country/region. Please ask the sales representatives for details.

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

Reproduction Prohibitions Please note that reproduction of the following is prohibited by law : •Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. •Unused postage stamps, post cards, etc. •Certificate stamps stipulated by law. •Reproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, drawings, photographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

Trademarks •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.



For Your Safety

Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection. Otherwise, electronic shock may result in the case of a failure or short circuit.