



Newline Q+ Pro Series

Power Up Your Collaborative Workspace.



Newline Q+ Pro Series

Effortless Collaboration for Corporate Spaces with the Newline Q+ Pro

Streamline communication and boost productivity in your corporate meeting and huddle rooms with the Newline Q+ Pro. Designed for modern workspaces, it's the ultimate tool for next-generation collaboration.

This all-in-one collaboration hub combines 4K clarity, immersive sound with a subwoofer, intuitive touch technology, and TÜV-certified antimicrobial coating for a secure and seamless experience.

Integrated features like a built-in camera, microphone array, and plug-and-play functionality ensure effortless teamwork. With compatibility for Google apps, Zoom, and Teams, the Newline Q+ Pro empowers professionals to connect, present, and collaborate with ease.



4K AI camera



8m pick-up range
microphone built in



2 x 20W speaker +
1 x 20W sub woofer



Available in 65", 75" and 86"



Wireless casting



Google EDLA
certified



Blue light filter



4K resolution and
178° viewing angle



TÜV-certified
antimicrobial
display coating



Compatible with
Zoom, Teams, Google,



Intelligent IR touch
technology



Optical bonding
technology

With a wide choice of sizes and plug 'n play versatility – choose the model to best suit your needs



Huddle room

Meeting room

Simply a powerful all-rounder collaborative device.



The power of all-in-one.

Simplify and streamline by consolidating traditional communication devices into an all-in-one setup. Say goodbye to projectors, microphones, cameras, interactive whiteboards, PC's, speakers, trailing cables, and technical interruptions. The Newline Q+ Pro can also be mobile or fixed in place, thanks to wireless connectivity.




Health and safety comes first.

Newline Q+ Pro has a TÜV-certified antimicrobial coating, a physical blue-light filter, and optical bonding. This means your display is light but sturdy, safer than non-bonded touchscreens, with improved viewing angles and touch accuracy.



Collaboration made easy.

Take charge with simple, intuitive controls - no need to have a technical expert in the room, with wireless plug 'n' play versatility. You can change presenters at will, make changes using the interactive touch screen, and see and hear everyone in the meeting with wide-view 4K clarity and powerful 2-way sound quality.



Keep your information safe and feel supported.

The Newline Q+ Pro has multiple security defences and settings like a USB lock, profile passkey, meeting data administrative protection, plus Android 13 OS and WIFI 6 certification. With easy web-based device management and the FUJIFILM Business Innovation New Zealand customer service advantage - be assured that support is available wherever you are, should you need it.



Almost limitless capabilities.

Compatible with Zoom, Teams, Google, and more. You can also access a broad range of apps with Android connectivity to encourage engagement and problem-solving for any audience.

Product Specifications

Newline Q+ Pro Series

Model		TT-6523QCA+		TT-7523QCA+		TT-8623QCA+	
Display	Active Screen Size	65"		75"		86"	
	Screen Type	LCD (Direct LED Backlight)					
	Display Area	1428 × 803 mm		1650 × 928 mm		1895 × 1066 mm	
	Display Ratio	16:9					
	Resolution	3840 × 2160 (4K)					
	Refresh Rate	60 Hz					
	Colors	1.07Billion					
	After Glass Center Brightness	≥ 400 cd/㎡					
	Typ. Static Contrast Ratio	4000:1 or 1200:1 by OC					
	Typ. Response Time	8ms					
	Viewing Angle	178°					
	Display Life Time (MTBF)	50000 hours					
Smart System	CPU	ARM A76*4 + A55*4					
	GPU	ARM G610 MC4					
	RAM	16GB					
	ROM	256GB					
	SD Card	64GB					
	Android Version	Android 13					
	OS Version	EDLA					
	OPS Slot	Yes					
	SDM-S Slot	Yes					
	WiFi Version	WiFi 5: 2.4G+5G, WiFi 6: 2.4G+5G					
	Bluetooth	BT5.2					
	Built-in Microphone	8-Mic Array, Upper Front					
NFC	Yes						
I/O	Front/Side	1 (PD 100W), 1 × HDMI In, 1 × USB Touch, 2 × USB 3.0, 1 × Mic In					
	Rear	2 × HDMI In, 1 × DP, 1 × Type C (no PD), 1 × Type C Out (no PD), 2 × USB 3.0 Public, 1 × USB 3.0 Android, 3 × USB Touch 3.0, 1 × HDMI Out, 1 × S/PDIF Out, 1 × Line Out, 1 × RS232, 1 × LAN In, 1 × LAN Out					
Speakers	Speaker Position	Bottom Front					
	Speaker Power (Max.)	20W × 2					
	Speaker Power (Avg.)	15W × 2					
	Speaker Rated Impedance	6Ω					
	Speaker Freq. Response	250Hz-20KHz SPL -10dB					
	Output S.P.L.	80±3dB					
Subwoofer	Speaker Position	Back Center					
	Speaker Power (Max.)	20W × 1					
	Speaker Power (Avg.)	20W × 1					
	Speaker Rated Impedance	4Ω					
	Speaker Freq. Response	80Hz-2.5KHz SPL -10dB					
	Output S.P.L.	77±3dB					
Touch Panel	Glass Surface Treatment	Anti-Glare+Anti-Fingerprint + Antimicrobial Tempered Glass					
	Glass Hardness	9H(Pencil)					
	Glass Thickness	3.2 mm					
	Glass Transparency	88%±3					
	Glass Haze	4-8%					
	Bonding Type	Zero bonding					
	Touch Solution	IR					
	Touch Points	Android 20, Windows 40					
Writing Tool	Stylus or Finger						
Electronic Capacity	Working Voltage	AC100-240V Max. 5.5A / 6.2A / 6.5A					
	Working Power Consumption	≤ 550W		≤ 620W		≤ 650W	
	Power Consumption (Standby Mode)	<0.5W					
Transportation & Storage	Storage Temperature&Humidity	-20~60°C, 0~90%RH (non-condensing)					
	Working Temperature/Humidity	0~40°C, 20~80%RH (non-condensing)					
	Installation Method (optional)	wall-mounted / mobile stand					
	Outline Dimension (without wall mount bracket)	1513 × 927 × 119 mm		1735 × 1051 × 122 mm		1982 × 1191 × 119 mm	
	Packing Dimension	1640 × 207 × 1036 mm		1859 × 207 × 1160 mm		2119 × 227 × 1290 mm	
	VESA Mount Pattern	600 × 400mm		800 × 400mm			
	Net Weight	39 kg		51.5 kg		64.5 kg	
Gross Weight	50 kg		65 kg		82.5 kg		

fujifilm.com/fbnz

FUJIFILM

FUJIFILM Business Innovation New Zealand Ltd

10 - 12 Landing Drive
Mangere, Auckland 2022

For advice on display solutions contact your
local sales representative

09 356 4200

fujifilm.com/fbnz

FUJIFILM and FUJIFILM logo are registered trademarks or
trademarks of FUJIFILM Corporation.