

ApeosPort® Print 3410SD

A4 Monochrome Printer

Features



B/W



34 ppm



Print



High Performance & Productivity

- Compact design fits comfortably on your desktop or small work space
- Fast monochrome printing of 34 ppm, with FPOT as fast as 8 seconds
- Standard 250-sheet tray allows printing without interruptions
- Easy to connect with built-in Wi-Fi, Ethernet or USB

Security



- Prevents information leakage with Confidential Print function
- Controls access to the Printer functions.
- Supports settings to delete temporary data files in memory

Easy Operation

- Two-line LCD lets you configure and monitor vital system information
- Compatible with Mopria® and AirPrint, you can easily print from mobile devices

Ecology

- Standard two-sided printing saves paper
- Supports ECO mode for easy presetting of features that save paper and toner



Specifications

Printing	
Display	2-line All Points Addressable (APA) monochrome LCD display
Print Speed: Up to	Black: 34 ppm (A4)
Time to First Page: As fast as* ¹	Black: 8 seconds
Print Resolution	Black: 1200 Image Quality, 2400 Image Quality, 300 x 300 dpi, 600 x 600 dpi
Memory	256 MB
Hard Disk	Not Available
Supplies	
Toner Cartridge Yields (up to)	3,000-page High Yield Cartridge, 6,000-page Extra High Yield Cartridge,
Imaging unit Estimated Yield: Up to	12000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage
Cartridge(s) Shipping with Product	700-page Toner Cartridges
Paper Handling	
Included Paper Handling	250-Sheet Input, 150-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed
Paper Input Capacity: Up to	251 pages 75 gsm
Paper Output Capacity: Up to	150 pages 75 gsm
Media Types Supported	Card Stock, Envelopes, Paper Labels, Plain Paper
Paper Input Capacity: Up to	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope, Hagaki
General Information	
Standard Ports	Ethernet 10/100BaseTX (RJ-45), USB 2.0 Specification Hi-Speed Certified (Type B), 802.11b/g/n Wireless
Noise Level: Operating	Print: 53 dBA
Specified Operating Environment* ²	Humidity: 15 to 80%* ³ Relative Humidity, Temperature: 10 to 32°C* ⁴ (excluding faults caused by condensation)
Size (mm - H x W x D) / Weight (kg)	215 x 355 x 333 mm / 8.1 kg

*1: The time from when the device starts the print job from standard sheet tray until the trailing edge of the first page exits into output tray. Numeric value may vary based on the output environment *2: Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. *3: When the humidity is 80%, the temperature is 25.5°C or less. *4: Humidity 45% or less when the temperature is 32°C.

Consumables*¹

Product Name	Product Code	Product Life
Black High Yield Use and Return Toner Cartridge* ²	CT203483	Up to 3,000 pages
Black Extra High Yield Use and Return Toner Cartridge* ²	CT203482	Up to 6,000 pages
Black Extra High Yield Regular Toner Cartridge	CT203528	Up to 6,000 pages
Black Imaging Unit	CT351281	Up to 12,000 pages

*1: Average standard page yield value declared in accordance with ISO/IEC 19752.

*2: The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

For more information or detailed product specification, please call or visit us at

FUJIFILM Business Innovation Philippines Corp.

25th Floor, SM Aura Tower, 26th St. Corner McKinley Parkway, Taguig City 1630 Philippines Tel. 632-8878-5200

fujifilm.com/fbph

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements

•FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort is registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. •Mopria®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

The information is as of April, 2023.

PIC-0203 PH (2111-R1)