

ApeosPort[®] Print C2410SD

A4 Colour Printer

Features



Colour



24 ppm



High Performance & Productivity

- Compact design fits anywhere on your work space
- Fast colour printing of up to 24 ppm, with FPOT as fast as 10.9 seconds
- Flexible media processing supports cardstock, small media, and envelopes
- Easy to connect with built-in Wi-Fi, gigabit Ethernet or USB

Security

- Prevents information leakage with Confidential Print function
- Controls access to the Printer functions
- Supports settings to delete temporary data files in memory



Easy Operation

- Two-line display lets you configure and monitor vital system information
- Compatible with Mopria[®] and AirPrint, you can easily print from mobile devices

Ecology

- Standard two-sided printing saves paper
- Supports ECO mode for easy presetting of features that save paper and toner

2-line Monochrome LCD Display



Specifications

Printing	
Display	2-line All Points Addressable (APA) monochrome LCD display
Print Speed: Up to	Black: 24 ppm (A4) / Colour: 24 ppm (A4)
Time to First Page: As fast as ^{*1}	Black: 10.9 seconds / Colour: 10.9 seconds
Print Resolution	Black: 4800 Colour Quality, 600 x 600 dpi / Colour: 600 x 600 dpi, 4800 Colour Quality
Memory	512 MB
Hard Disk	Not Available
Supplies	
Print Cartridge Yields (up to)	4,500 -page Black High Yield Cartridge / 4,500 -page Colour (CMY) High Yield Cartridges / 1,500 -page Black Cartridge / 1,500 -page Colour (CMY) Cartridges
Cartridge(s) Shipping with Product	750 -page Black Toner Cartridge, 500 -page Colour (CMY) Toner Cartridge
Paper Handling	
Included Paper Handling	100-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed, 250-Sheet Input
Paper Input Capacity: Up to	250+1 pages 75 gsm
Paper Output Capacity: Up to	100 pages 75 gsm
Media Types Supported	Paper Labels, Card Stock, Plain Paper, Envelopes, Glossy Paper
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Hagaki Card, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope
General Information	
Standard Ports	802.11b/g/n Wireless, USB 2.0 Specification Hi-Speed Certified (Type B), Ethernet 10/100/1000 BaseTX (RJ-45)
Noise Level: Operating	Operating: 52 dBA (Print)
Specified Operating Environment ^{*2}	Humidity: 8 to 80% ^{*3} Relative Humidity, Temperature: 10 to 32°C ^{*4} (excluding faults caused by condensation)
Size (mm - H x W x D) / Weight (kg)	244 x 412 x 395 mm / 16.1 kg

^{*1}: The time from when the device starts the print job from standard sheet tray until the trailing edge of the first page exits into output tray. Numeric value may vary based on the output environment. ^{*2}: Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. ^{*3}: When the humidity is 80%, the temperature is 25.5°C or less. ^{*4}: Humidity 45% or less when the temperature is 32°C.

Consumables^{*1}

Product Name	Product Code	Product Life
Black Use & Return Print Cartridge ^{*2}	CT351267	Up to 1,500 pages
Cyan Use & Return Print Cartridge ^{*2}	CT351268	Up to 1,500 pages
Magenta Use & Return Print Cartridge ^{*2}	CT351269	Up to 1,500 pages
Yellow Use & Return Print Cartridge ^{*2}	CT351270	Up to 1,500 pages
Black High Yield Use & Return Print Cartridge ^{*2}	CT351263	Up to 4,500 pages
Cyan High Yield Use & Return Print Cartridge ^{*2}	CT351264	Up to 4,500 pages
Magenta High Yield Use & Return Print Cartridge ^{*2}	CT351265	Up to 4,500 pages
Yellow High Yield Use & Return Print Cartridge ^{*2}	CT351266	Up to 4,500 pages
Black High Yield Regular Print Cartridge	CT351291	Up to 4,500 pages
Cyan High Yield Regular Print Cartridge	CT351292	Up to 4,500 pages
Magenta High Yield Regular Print Cartridge	CT351293	Up to 4,500 pages
Yellow High Yield Regular Print Cartridge	CT351294	Up to 4,500 pages
Waste Print Bottle	CWAA0973	Up to 15,000 pages

^{*1}: Average continuous black or continuous composite Colour (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798.

^{*2}: The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

For more information or detailed product specification, please call or visit us at

FUJIFILM Business Innovation Philippines Corp.

25th Floor, SM Aura Tower, 26th St. Corner McKinley Parkway, Taguig City 1630 Philippines Tel. 632-8878-5200

fujifilm.com/fbph

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements

•FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort is registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. •Mopria®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

The information is as of April, 2023.

PIC-0200 PH (2111-R1)