

SPECIFICATIONS

|                                     |   |   |   |                      |
|-------------------------------------|---|---|---|----------------------|
| MODEL NUMBER                        | SC-T3130 / SC-T3130N  |   | SC-T3130X   | SC-T5130             |
| Printer Width                       | 24"   |   |   | 36"                  |
| Printing Technology                 |   |   |   |                      |
| Print Head                          | PrecisionCore TFP Printhead   |   |   |                      |
| Nozzle Configuration                | 3,200 nozzles (800 nozzles x 4 channels x 1 head)   |   |   |                      |
| Maximum Resolution                  | 2,400 x 1,200 dpi   |   |   |                      |
| Minimum Ink Droplet Volume          | 4.0 pl  |   | 3.5 pl  | 4.0 pl               |
| Line Accuracy                       | ±0.1% or ±0.26 mm   |   |   |                      |
| Print Speed                         | CAD (A1): 34 seconds  |   |   | CAD (A1): 31 seconds |
| Ink System                          |   |   |   |                      |
| Ink Type                            | UltraChrome XD2 Pigment Ink   | Black: Pigment, Colour: Dye   | UltraChrome XD2 Pigment Ink   |                      |
| Colours                             | Cyan, Magenta, Yellow, Black  |   |   |                      |
| Paper Handling                      |   |   |   |                      |
| Maximum Roll Diameter / Weight      | 2" core, Max 110 mm/3kg   | 2" core, Max 119 mm/4.2kg   | 2" core, Max 110 mm/5kg   |                      |
| Paper Width                         | Roll: 329 mm - 610 mm   | Roll: 297 mm - 610 mm   | Roll: 329 mm - 914 mm   |                      |
|                                     | Cutsheet: 210 mm - 610 mm   |   | Cutsheet: 210 mm - 914 mm   |                      |
| Side Margin                         | 3mm   |   |   |                      |
| Media Thickness                     | Roll: 0.05 mm to 0.21 mm, ASF/Cutsheet: 0.12 mm to 0.27 mm  |   |   |                      |
| Auto-Sheet Feeder                   | A4 to A3  |   |   |                      |
| Paper Capacity for ASF              | 50 sheets plain paper / 5 sheets special media  |   |   |                      |
| Connectivity                        |   |   |   |                      |
| Interface                           | USB 3.0, Ethernet (100BASE-TX/1000BASE-T), Wi-Fi (IEEE802.11b/g/n)  |   |   |                      |
| Wi-Fi Direct                        | Wi-Fi Direct (Simple AP)  |   |   |                      |
| Control Panel                       | 4.3" Touch Screen   |   |   |                      |
| Printer Languages                   | ESC/P raster, HP-GL/2HP RTL   |   |   |                      |
| Scanner Integration                 | Epson WorkForce DS-530<br>Epson WorkForce DS-650<br>Epson WorkForce DS-60000  |   |   |                      |
| Memory                              | 1GB   |   |   |                      |
| Operating System Requirements       | Windows XP SP3 or later / Vista / 7 / 8 / 8.1 / 10, Windows Server 2003 / 2008 / 2012 / 2016 / 2019, Mac OS X 10.6.8 or later |   |   |                      |
| Electrical Specifications           |   |   |   |                      |
| Rated Voltage / Frequency / Current | AC 100 to 240V, 50/60Hz, 1.4A   |   |   |                      |
| Power Consumptions                  | Operating: Approx. 28W<br>Ready: Approx. 8W<br>Sleep: Approx. 1.6W<br>Power Off (Stand by):<br>Approx. 0.2W                   | Operating: Approx. 22W<br>Ready: Approx. 8W<br>Sleep: Approx. 1.6W<br>Power Off (Stand by):<br>Approx. 0.2W | Operating: Approx. 28W<br>Ready: Approx. 8W<br>Sleep: Approx. 1.6W<br>Power Off (Stand by):<br>Approx. 0.2W |                      |
| Environmental Conditions            |   |   |   |                      |
| Temperature                         | Operating: 10°C to 35°C, Storage: -20°C to 40°C   |   |   |                      |
| Humidity                            | Operating: 20 - 80% (No Condensation), Storage: 5 - 85% (No Condensation)   |   |   |                      |
| Sound Pressure                      | Operating: Approx. 49dB(A), Sleep: Approx. 32dB(A)  |   |   |                      |
| Sound Power                         | Operating: Approx. 7.5B(A)  |   |   |                      |
| Printer Dimensions                  |   |   |   |                      |
| Dimension With Stand (W x H x D)    | 970 x 913 x 696 mm  | 970 x 928 x 577 mm  | 1,268 x 913 x 696 mm  |                      |
| Dimension Without Stand (W x H x D) | 970 x 230 x 505 mm  | 970 x 245 x 577 mm  | 1,268 x 230 x 505 mm  |                      |
| Weight With Stand                   | 38 kg   | 40 kg   | 46 kg   |                      |
| Weight Without Stand                | 27 kg   | 29 kg   | 33 kg   |                      |
| What's In The Box                   | Printer, Printer Stand <sup>*1</sup> , Initial Ink Cartridge, AC Power Cable, Setup Guide, Software CD-Rom, Maintenance Box   |   |   |                      |
| Warranty                            | 3-years Warranty  | 1-year Warranty   | 3-years Warranty  |                      |

\*1 No stand included for SC-T3130N model.

Dimensions and Weight

SC-T3130  
Weight: 38kg




SC-T3130N  
Weight: 27kg



SC-T3130X  
Weight: 29kg



SC-T5130  
Weight: 46kg



© 2021 Epson Singapore Pte Ltd. All Rights Reserved. Reproduction in part or in whole, without the written permission from Epson, is strictly prohibited. EPSON and EXCEED YOUR VISION are registered trademarks of Seiko Epson Corporation. All other product names and other company names used herein are for identification purposes only and are the trademarks or registered trademarks of their respective owners. Epson disclaims any and all rights in those marks. Print samples shown are simulations only. Specifications and product availability are subject to change without notice and may vary between countries. Please check with local Epson offices for more information.

Partner's Stamp

Information correct at time of printing  
Printed June 2021

SPECIFICATIONS

|                                     |   |   |
|-------------------------------------|---|---|
| MODEL NUMBER                        | SC-T3130M   | SC-T5130M   |
| Printer Width                       | 24"   | 36"   |
| Printing Technology                 |   |   |
| Print Head                          | PrecisionCore TFP Printhead   |   |
| Nozzle Configuration                | 3,200 nozzles (800 nozzles x 4 channels x 1 head)   |   |
| Maximum Resolution                  | 2,400 x 1,200 dpi   |   |
| Minimum Ink Droplet Volume          | 4.0 pl  |   |
| Line Accuracy                       | ±0.1% or ±0.26 mm   |   |
| Minimum Line Width                  | 0.07mm <sup>*1</sup> (0.02mm <sup>*2</sup> )  |   |
| Print Speed                         | CAD (A1): 34 seconds  | CAD (A1): 31 seconds  |
| Ink System                          |   |   |
| Ink Type                            | UltraChrome XD2 Pigment Ink   |   |
| Colours                             | Cyan, Magenta, Yellow, Black  |   |
| Paper Handling                      |   |   |
| Maximum Roll Diameter / Weight      | 2" core, Max 110 mm/3kg   | 2" core, Max 119 mm/5.9kg   |
| Paper Width                         | Roll: 329 mm - 610 mm<br>Cutsheet: 210 mm - 610 mm  | Roll: 297mm - 914 mm<br>Cutsheet: 210 mm - 914 mm   |
| Side Margin                         | 3mm   |   |
| Media Thickness                     | Roll: 0.05 mm to 0.21 mm, ASF/Cutsheet: 0.12 mm to 0.27 mm  |   |
| Auto-Sheet Feeder                   | A4 to A3  |   |
| Paper Capacity for ASF              | 50 sheets plain paper / 5 sheets special media  |   |
| Scanning                            |   |   |
| Sensor                              | CIS   |   |
| Light Source                        | RGB LED   |   |
| Optical Resolution                  | 600 dpi   |   |
| Scan Speed (200 dpi)                | 1.5 ips (Colour) / 4.5 ips (Mono)   |   |
| Minimum Document Size               | 148 mm x 148 mm   |   |
| Maximum Document Size               | 609.6 mm x 2,720 mm   |   |
| Scan Formats                        | JPEG, PDF (Single Page), PDF (Multi Page), PDF/A (Single/Multi), TIFF   |   |
| Scan to Destination                 | Scan to Network Folder, Scan to FTP Server, Scan to Email, Scan to Memory Device  |   |
| Copy                                |   |   |
| Copy Speed                          | 77 sec (Colour) / 60 sec (Mono)   |   |
| Scaling                             | 25 to 400%  |   |
| Maximum Copies                      | 99  |   |
| Connectivity                        |   |   |
| Interface                           | USB 3.0, Ethernet (100BASE-TX/1000BASE-T), Wi-Fi (IEEE802.11b/g/n)  |   |
| Wi-Fi Direct                        | Wi-Fi Direct (Simple AP)  |   |
| Control Panel                       | 4.3" Touch Screen   |   |
| Printer Languages                   | ESC/P raster, HP-GL/2HP RTL   |   |
| Memory                              | 1GB + 8GB <sup>*3</sup>   |   |
| USB Direct Print                    | PDF <sup>*4</sup> , TIFF, JPEG  |   |
| Operating System Requirements       | Windows XP SP3 or later / Vista / 7 / 8 / 8.1 / 10, Windows Server 2003 / 2008 / 2012 / 2016 / 2019, Mac OS X 10.6.8 or later |   |
| Electrical Specifications           |   |   |
| Rated Voltage / Frequency / Current | AC 100 to 240V, 50/60Hz, 1.4A   |   |
| Power Consumptions                  | Operating: Approx. 24W<br>Ready: Approx. 11W<br>Sleep: Approx. 2.0W<br>Power Off (Stand by): Approx. 0.2W                     | Operating: Approx. 26W<br>Ready: Approx. 12W<br>Sleep: Approx. 2.0W<br>Power Off (Stand by): Approx. 0.2W |

|                                     |   |                            |
|-------------------------------------|---|----------------------------|
| Environmental Conditions            |   |                            |
| Temperature                         | Operating: 10°C to 35°C, Storage: -20°C to 40°C   |                            |
| Humidity                            | Operating: 20 - 80% (No Condensation), Storage: 5 - 85% (No Condensation)   |                            |
| Sound Pressure                      | Operating: Approx. 47dB(A)  | Operating: Approx. 50dB(A) |
| Sound Power                         | Operating: Approx. 6.6B(A)  |                            |
| Printer Dimensions                  |   |                            |
| Dimension With Stand (W x H x D)    | 970 x 974 x 696 mm  | 1,268 x 975 x 696 mm       |
| Dimension Without Stand (W x H x D) | 970 x 292 x 505 mm  | N/A                        |
| Weight With Stand                   | 44.4 kg   | 54.8 kg                    |
| Weight Without Stand                | 33.4 kg   | N/A                        |
| What's In The Box                   | Printer, Printer Stand <sup>*5</sup> , Initial Ink Cartridge, AC Power Cable, Setup Guide, Software CD-Rom, Maintenance Box |                            |
| Warranty                            | 1-year Warranty   |                            |


\*1 ISO/IEC 24790, Single weight matte paper, CAD/Line Drawing, Max Quality, High Speed=Off, Finest Detail=On.  
\*2 Addressable.  
\*3 For scanner data processing.  
\*4 PDF available only for files scanned by integrated scanner.  
\*5 No stand included for SC-T3130M model.

Dimensions and Weight

SC-T3130M  
Weight: 33.4kg



SC-T5130M  
Weight: 54.8kg



© 2021 Epson Singapore Pte Ltd. All Rights Reserved. Reproduction in part or in whole, without the written permission from Epson, is strictly prohibited. EPSON and EXCEED YOUR VISION are registered trademarks of Seiko Epson Corporation. All other product names and other company names used herein are for identification purposes only and are the trademarks or registered trademarks of their respective owners. Epson disclaims any and all rights in those marks. Print samples shown are simulations only. Specifications and product availability are subject to change without notice and may vary between countries. Please check with local Epson offices for more information.

Partner's Stamp  
FUJIFILM

For more information or detailed product specification, please call or visit us at  
FUJIFILM Business Innovation Philippines Corp.  
26th Floor M&A Tower, 26th St. Corner McKinley Parkway, Taguig City 1630 Philippines  
Tel: 632-8879-5200  
fujifilm.com/biph

Information correct at time of printing  
Printed June 2021

GO BIG ON  
POSSIBILITIES  
AND PRECISION.



Distinctive Quality Meets Endless Possibilities For Your Creative Ideas.

Take your ideas to a bigger scale with greater performance and precision with the Epson SureColor T-series printers. With PrecisionCore printhead technology and UltraChrome XD2 ink<sup>\*2</sup> to bring about fast printing speeds, enjoy a seamless work process and top-class accuracy in every print. Showcase your ideas and plans in a big way right down to the finest detail.

GO BIG on the details and find out more from our printing experts.



IT'S IN THE DETAILS.

Detailed Accuracy

PrecisionCore printhead technology produces impressive accuracy and sharpness at outstanding speeds.

Reliable Efficiency

In-built functions such as Continuous Ink Supply System<sup>\*3</sup> and seamless scan to print ensure high productivity.

Small Footprint

Minimally designed to fit effortlessly into tight working spaces.

\*1 SC-T3130X stand is optional and is not included in the initial packaging. \*2 For SC-T3130/T3130M/T5130/T5130M only. \*3 For SC-T3130X only.

Find out more at [www.epson.com.sg/technical-printing](http://www.epson.com.sg/technical-printing)

EpsonSingapore EpsonSingapore EpsonSoutheastAsia Epson Singapore

Epson Singapore Pte Ltd  
Epson Customer Care Centre  
438B Alexandra Road, #04-01/04 Block B Alexandra Technopark, Singapore 119968. Tel: (65) 6586-5500  
100G Pasir Panjang Road, #01-09 Interlocal Centre, Singapore 118523. Epson Helpdesk: 800 120 5564  
Opening hours: Monday – Friday, 9am to 5pm. Closed on Saturday, Sunday and Public Holiday. Please refer to [www.epson.com.sg/contact](http://www.epson.com.sg/contact) for updated opening hours.

Find out more at [www.epson.com.sg/technical-printing](http://www.epson.com.sg/technical-printing)

EpsonSingapore EpsonSingapore EpsonSoutheastAsia Epson Singapore

Epson Singapore Pte Ltd  
Epson Customer Care Centre  
438B Alexandra Road, #04-01/04 Block B Alexandra Technopark, Singapore 119968. Tel: (65) 6586-5500  
100G Pasir Panjang Road, #01-09 Interlocal Centre, Singapore 118523. Epson Helpdesk: 800 120 5564  
Opening hours: Monday – Friday, 9am to 5pm. Closed on Saturday, Sunday and Public Holiday. Please refer to [www.epson.com.sg/contact](http://www.epson.com.sg/contact) for updated opening hours.

EPSON  
EXCEED YOUR VISION






LARGE FORMAT PRINTERS  
SURECOLOR™ SC-T3130/T3130N/T3130X/T3130M/T5130/T5130M



For accuracy right down to the finest details, the Epson SureColor T-series printers fulfils all your business needs. Using core technologies such as PrecisionCore printheads and UltraChrome XD2 ink, prints are delivered at an outstanding speed with impressive accuracy and clarity. Let your ideas impress your audience with prints that are consistently fast, precise and reliable.

PrecisionCore Printhead Technology


Equipped with the next-generation PrecisionCore printhead technology as well as Variable Size Dot Technology, piezo elements are used to mechanically eject ink from the SureColor T-series' PrecisionCore Micro TFP printhead, allow the ink droplets to be controlled to the finesse of 3.5 picolitres, producing incredibly precise line detail, sharp text and photographic-quality graphics. T-series' industry-leading output quality and accuracy will provide a reliable and productive long-term operation.



Impressive Print Speeds


The PrecisionCore printhead technology enables remarkable print speeds that will print A1 printouts in 31 seconds\*.

\*Print speed is based on the SC-T5130.



Nozzle Verification Technology

Print without interruptions with the advanced built-in Nozzle Verification Technology (NVT). This technology monitors nozzle health and adjusts print quality automatically without interruption, even during printing.



The piezo element (sensor) detects the residual vibration (pressure change) in the ink chamber and diagnoses the nozzle condition.

If a clogged nozzle is indicated by an irregular vibration pattern, the printer automatically adjusts the print quality.

Compact, User-friendly Design



Control At Your Fingertips

A 4.3 inch touch panel on the T-series gives you the convenience of an easy setup and a PC-less operation that just makes things extra efficient.



Small Footprint

Sleek and minimally designed, the T-series is of a comfortable size that fits into tight work spaces effortlessly. At just 970 x 245 x 577mm without the stand, the SC-T3130X has one of the smallest footprint in its class.



Trusted Productivity

Ink Tank System

The SC-T3130X increases cost savings as it brings on a seamless workflow, eliminating the need for ink replacements that will delay print jobs. With an efficiently designed ink tank and system, ink refills during print jobs can be easily and effortlessly done, without compromising on efficiency.



Wireless Connectivity

The T-series is integrated with Wi-Fi and Wi-Fi Direct, making it convenient to print right from smart devices anywhere in the office. The Wi-Fi Direct function acts as an access point, allowing devices to connect directly to the printer without a router. Additionally, the T-series printers come equipped to allow direct wireless printing from any Apple devices through Apple AirPrint\*, without the need for any additional drivers.



\*Apple AirPrint is a trademark of Apple Inc.

Epson Cloud Solution PORT

Epson Cloud Solution PORT is a cloud-based solution for Epson end users. This software provides users with the status of the connected printer and alerts for troubleshooting if required. The Production Monitor allows users to visualise printer operational status, track usage and print job cost, conveniently from their PC or smart devices.



Seamless Scan To Print

Scan and enlarge your printouts in just four easy steps without needing to connect to a computer. Using compatible Epson scanners\* for the SC-T3130/T3130N/T3130X/T5130, you can seamlessly scan and print directly from the T-series printers.



\*Recommended scanners: WorkForce DS-530, DS-6500, DS-60000.

Consumables & Options

| Model                   |                       | Size       | SC-T3130/SC-T5130/<br>SC-T3130M/SC-T5130M | SC-T3130X  |                             |          |           |          |           |           |
|-------------------------|-----------------------|------------|---|------------|-----------------------------|----------|-----------|----------|-----------|-----------|
| INK CARTRIDGES          | Black Ink Cartridge   | 50ml       | C13T40A100                                |            | Options                     | SC-T3130 | SC-T3130X | SC-T5130 | SC-T3130M | SC-T5130M |
|                         | Cyan Ink Cartridge    | 26ml       | C13T40A200                                |            | Roll Feed Spinder (24")     | ●        | ●         |          | ●         |           |
|                         | Magenta Ink Cartridge | 26ml       | C13T40A300                                |            | C12C935701                  |          |           |          |           |           |
|                         | Yellow Ink Cartridge  | 26ml       | C13T40A400                                |            | Roll Feed Spinder (36")     |          |           | ●        |           | ●         |
|                         | Black Ink Cartridge   | 80ml       | C13T40B100                                |            | C12C933131                  |          |           |          |           |           |
|                         | Cyan Ink Cartridge    | 50ml       | C13T40B200                                |            | Printer Stand (24")         | ●        | ●         |          | ●         |           |
|                         | Magenta Ink Cartridge | 50ml       | C13T40B300                                |            | C12C933151                  |          |           |          |           |           |
| INK BOTTLES             | Yellow Ink Cartridge  | 50ml       | C13T40B400                                |            | Printer Stand (34")         |          |           | ●        |           | ●         |
|                         |                       |            |   |            | C12C933091                  |          |           |          |           |           |
|                         | Black Ink Bottle      | 140ml      | -   | C13T49K100 | Document Carrier Sheet [A1] |          |           |          | ●         | ●         |
|                         | Cyan Ink Bottle       | 140ml      | -   | C13T49K200 | C12C936101                  |          |           |          |           |           |
|                         | Magenta Ink Bottle    | 140ml      | -   | C13T49K300 | Document Carrier Sheet [A0] |          |           |          |           | ●         |
|                         | Yellow Ink Bottle     | 140ml      | -   | C13T49K400 | C12C936461                  |          |           |          |           |           |
| Others                  |                       |            |   |            |                             |          |           |          |           |           |
| Maintenance Box         |                       | C13S210057 |   |            |                             |          |           |          |           |           |
| Auto Cutter Spare Blade |                       | C13S210055 |   |            |                             |          |           |          |           |           |