








One good printing experience is all it takes to set new standards. The Epson SureColor™ SC-P10070 and SC-P20070 are professional production printers designed for the best results. Advanced PrecisionCore™ MicroTFP printhead technology yields high speeds of up to 17.5 m²/h*, with accurate dot placement for stand-out visuals. To top it off, the Epson UltraChrome™ PRO nine-colour pigment ink system develops vibrant prints with lasting durability and the high-precision media feeding system ensures smooth, reliable operations.



SC-P10070



SC-P20070

- 
 2.64" Printhead
- 
 Up to 64" Wide**
- 
 Versatile Media Handling
- 
 Up to 1.5mm Thick
- 
 Ethernet



ENGINEERED FOR BUSINESS

| | | |
|---|---|---|
| <p>Swift Speeds For Maximum Output New PrecisionCore MicroTFP printhead utilises 8000 nozzles, for class-leading print speeds of up to 17.5 m²/h*.</p> | <p>Affordable Prints With Peace of Mind The UltraChrome PRO ink with four levels of grey produces brilliant prints that last up to 200 years. Cost-effective 700 ml ink cartridges ensure low printing costs.</p> | <p>Precision Media Feeding System Maximum output with Realtime Media Adjustment & Feedback System, a Media Inductive Roller System and a unique Roll Media Skew Reduction System.</p> |
|---|---|---|




*Based on 6-pass printing for high quality production, on photo media.
 **Up to 64" wide for SC-P20070, 44" for SC-P10070.

SPECIFICATIONS
SURECOLOR™ SC-P10070/P20070




| Model Number | SC-P10070 | SC-P20070 |
|-----------------------------------|---|-----------|
| Printer Width | 44" | 64" |
| Printing Technology | PrecisionCore™ MicroTFP Printhead | |
| Printhead | Nozzle Verification System | |
| Printing Method | Black colour ink : 4,000 nozzles (PK, MK, DGY, GY, LGY 800 nozzles each colour) | |
| Nozzle Configuration | Colour ink : 4,000 nozzles (C, VM, Y, LC, VLM 800 nozzles each colour) | |
| Print Direction | Bi-directional printing, uni-directional printing | |
| | Auto Head Alignment technology | |
| Print Quality | 2400x1200 dpi | |
| Maximum Resolution | 2400x1200 dpi | |
| Minimum Ink Droplet Volume | 3.5pl | |
| Performance*1 | 600 x 600dpi, 1.9 minutes | |
| Draft Mode | 1200 x 1200dpi, 3.0 minutes | |
| Normal Mode | 2400 x 1200dpi, 5.6 minutes | |
| Fine Mode | | |
| Ink System | Epson UltraChrome™ PRO Ink | |
| Ink Type | Cyan, Vivid Magenta, Yellow, Photo Black, Matte Black, Dark Grey, Grey, Light Grey, Light Cyan, Vivid Light Magenta | |
| Colours | 700ml/110ml (Bundled) | |
| Ink Capacity | | |
| Printer Software on CD-ROM | WindowsXP/Vista/7/8/8.1/10 (32/64bit) or later / MacOSX10.6.8 or later | |
| Printer Driver | Windows Server 2003 Standard/Standard *64bit, 2008 Standard/Standard *64bit /R2, 2012 or later 2003/2003 *64bit, 2008/2008R2 *64bit/2012 or later (Certification/Logo : Windows Server 2008/2008R2) | |
| Paper Handling | Friction Feed | |
| Paper Feed Method | 170mm | |
| Roll Dimensions | Roll paper : 254mm (10") - 1118mm (44") Roll paper : 254mm (10") - 1626mm (64") | |
| Paper Size & Thickness | Cut sheet : 210mm (A4)- 1118mm (44") 0.08-1.50mm | |
| Borderless | 254mm(10in.), 300mm(11.8in.), 329mm(A3+/A3++), 254mm(10in.), 300mm(11.8in.), 329mm(A3+/A3++), 406mm(16in.), 432mm(17in./USC), 508mm(20in.), 406mm(16in.), 432mm(17in./USC), 508mm(20in.), 515mm(20.3in./B2), 594mm(A1), 610mm(24in./A1+), 515mm(20.3in./B2), 594mm(A1), 610mm(24in./A1+), 728mm(29in./B1), 841mm(A0), 914(36in./A0+), 728mm(29in./B1), 841mm(A0), 914(36in./A0+), 1030mm(B0), 1118mm(44in/B0+) 1030mm(B0), 1118mm(44in/B0+), 1270mm(50in.), 1372mm(54), 1524(60in.) | |
| Roll Paper Remaining | The remaining amount is managed by the barcode print on Roll paper. | |
| Control Panel | 2.7" Colour LCD | |
| Colour & Size | 960 x 240 pix. | |
| Number of Dots | | |
| Connectivity | Hi-Speed USB | |
| Standard | 1000BASE-T (Recommended) / 100BASE-TX | |
| Ethernet | ESC/P raster | |
| Control Code | | |
| Memory | 1GB 1.5GB | |
| Main | | |
| Software | User's Guide(EN) Network Guide(EN) , LFP RemotePanel 2, EpsonColorCalibrationUtility, EpsonNet Setup, EpsonNet Config, EpsonNet Print (Windows only) | |
| PC Software | 'Remote Manager' HDD utility - Control of HDD functions | |
| Printer Web Function | LFP Accounting Tool (Job monitoring, consumable cost tracking), HDD Utility software (Web download) | |
| Software from Web Download | | |
| Electrical Specifications | AC100-240V 50/60Hz | |
| Voltage | 5A | |
| Rated Current | Operating: Approx. 95W; Sleep: Approx. 2.8W *Interface is 1000BASE-T; Power off (Stand-by): Less than 0.5W | |
| Power Consumption | | |
| Recommended Operating | Operating: 10°C - 35°C; Storage: -20°C - 40°C | |
| Temperature | Operating: 20% - 80% (no condensation); Storage: 5% - 85% (no condensation) | |
| Humidity | | |
| Acoustic Noise Level | Approx 50.5dB (A) Approx 51.1dB (A) less than | |
| Sound Pressure Level | Approx 65.3dB (A) Approx 67dB (A) less than | |
| Sound Power Level | | |
| System Requirement | Windows XP/Vista/7/8/8.1 (32/64bit) or later | |
| | CPU : Core 2 Duo 3.05GHz; Memory : Memory more than 1GB; HDD : Free space more than 32GB | |
| | Macintosh Mac OS X10.6.8 or later | |
| | CPU : Core 2 Duo 3.05GHz; Memory : Memory more than 1GB; HDD : Free space more than 32GB | |

Dimensions & Weight
SC-P10070
Weight: 126kg



SC-P20070
Weight: 171kg



*1 Figures represent print times only for Epson test sample image (A1 size) as shown, produced on Premium Photo paper.



A1:588x735mm

Ink Cartridge Compatibility

700 ml Ink Cartridges

| | |
|-----------------------|------------|
| ● Photo Black | C13T809100 |
| ● Cyan | C13T809200 |
| ● Magenta | C13T809300 |
| ● Yellow | C13T809400 |
| ● Light Cyan | C13T809500 |
| ● Vivid Light Magenta | C13T809600 |
| ● Dark Grey | C13T809700 |
| ● Matte Black | C13T809800 |
| ● Grey | C13T809900 |
| ● Light Grey | C13T809000 |

Supplies & Optional Accessories

| | |
|-------------------------|------------|
| Auto Cutter Spare Blade | C13S210040 |
| Cleaning Stick | C13S090013 |
| Maintenance Box | C13T619300 |
| Auto Take-up Reel Unit | C12C932201 |
| Roll Adapter | C12C932231 |
| Adobe® PostScript® 3™ | |
| Expansion Unit | C12C891131 |
| Hard Disk Unit | C12C848031 |



©2016 Epson Singapore Pte Ltd. All Rights Reserved. Reproduction in part or in whole, without the written permission from Epson, is strictly prohibited.

EPSON and EXCEED YOUR VISION are registered trademarks of Seiko Epson Corporation.

All other product names and other company names used herein are for identification purposes only and are the trademarks or registered trademarks of their respective owners.

Epson disclaims any and all rights in those marks. Print samples shown herein are simulations. The actual product design and contents may vary. Specifications are subject to change without notice and may vary between countries. Please check with local Epson offices for more information.

FUJIFILM

For more information or detailed product specification, please call or visit us at:
FUJIFILM Business Innovation Philippines Corp.
20th Floor, SM Aura Tower, 20th St. Corner McKinley Parkway, Taguig City 1630 Philippines
Tel. 632-8878-3200
fujifilm.com/ibph

Information correct at time of printing
Printed June 2016