



## COLOUR PRECISION. PHOTOGRAPHIC BRILLIANCE.

Epson presents you the benchmark in photographic quality - the SC-P5000 with superior colour reproduction. With Epson's PrecisionCore™ printhead, it produces images with incredible details and consistency. In addition, the UltraChrome™ HDX all-pigment ink set delivers outstanding colour accuracy and image durability in ultra-high resolution, with a wide colour gamut that achieves the most dynamic images.



17" Wide



Versatile  
Media  
Handling



Up to  
1.5mm  
Thick



## ENGINEERED FOR BUSINESS

### Advanced Printhead Technology

Highly advanced PrecisionCore printhead technology delivers incredibly consistent and accurate ink droplet placement.

### Photographic and Proofing Accuracy

The Epson UltraChrome HDX ink technology delivers accurate colours with superb black density, achieving smooth gradations and optical clarity.

### Efficient Workflow Solutions

Epson's innovative software solutions enhance printing processes, achieving affordable professional output.



<b>Model Number</b>	<b>SC-P5000</b>	
<b>Printing Technology</b>	Printing Method	PrecisionCore printhead Epson Variable-Sized Droplet Technology
	Black Nozzle Configuration	Light Light Black ink is used: 360 nozzles each color (x3) Violet ink is used: 360 nozzles each color (x2)
	Color Nozzle Configuration	Light Light Black ink is used: 360 nozzles each color (x7) Violet ink is used: 360 nozzles each color (x8)
	Print Direction	Bi-directional printing, uni-directional printing Auto Head Alignment technology Auto Nozzle Check technology Auto Switching between Photo BK and Matte BK Bar-code Print System
<b>Print Quality</b>	Maximum Resolution	2880 x 1440 dpi
	Minimum Ink Droplet Volume	3.5pl
<b>Performance*1</b>	Draft Mode	0.5 minutes
	Normal Mode	360 x 720dpi, 0.8 minutes
	Fine Mode	720 x 720dpi, 1.8 minutes
	Super Fine Mode	720 x 720dpi, 2.5 minutes
<b>Ink System</b>	Epson UltraChrome HDX	
	Cyan, Photo Black, Matte Black, Vivid Magenta, Yellow, Orange, Green, Light Cyan, Vivid Light Magenta, Light Black, Light Light Black*2	
<b>Ink Capacity</b>	200ml/80ml (Bundled)	
<b>Printer Software on CD-ROM</b>	Printer Driver	WindowsXP/Vista/7/8/8.1/10 (32/64bit) or later/MacOSX10.6.8 or later Windows Server 2003 Standard/Standard *64bit, 2008 Standard/Standard *64bit/R2, 2012 or later (Certification/Logo: Windows Server 2008/2008R2)
<b>Paper Handling</b>	Paper Path	Friction Feed (Auto switching between cut sheet and roll paper)
	Roll Dimensions	203mm-432mm, 2inch-core/3inch-core 2inch-core: Maxφ103mm/3inch-core: Maxφ150mm
	Paper Size (width) & Thickness	203mm (8") - 432mm (17"): Roll paper 203mm (8") - 432mm (17"): Cut Sheet 0.08-0.50mm: Roll paper 0.08-1.50mm: Cut Sheet
	Borderless	8/10/11/14/16/17inch, A4/A3/A3+/A2, 300mm: Roll paper 10/14/16/17inch, A4/A3/A3+, 300mm: Cut paper
	ASF Capacity: Max. sheets	ASF Cassette: Plain paper 250 sheets (A4-A2/US-C)
<b>Control Panel</b>	Color & Size	2.7 inch Color LCD
	Number of Dots	960 x 240 pix.
<b>Interface</b>	Hi-Speed USB, 10BASE-T/100BASE-TX/1000BASE-T	
<b>Control Code</b>	ESC/P raster	
<b>Memory</b>	Printer Main	256MB (Main)/128MB (Network)
<b>Environmental Characteristics</b>	Temperature	Operating: 10°C - 35°C Storage: -20°C - 40°C
	Humidity	Operating: 20 - 80% (no condensation) Storage: 5 - 85% (no condensation)
<b>Electrical Characteristics</b>	Voltage	AC 100-240V 50-60Hz
	Rated Current	0.70.4A
	Power Consumption	Operating: Approx. 52 W Ready: Approx. 20W Sleep: Approx. 5W *Interface is 1000BASE-T Power off (Stand-by): Less than 0.5W
<b>Acoustic Noise Level</b>	Sound Pressure Level <dB(A)>	Less than 47dB(A)
	Sound Power Level <B(A)>	Less than 6.2B(A)
<b>Utility Software for Windows OS</b>	PC Software for Windows OS	Printer Driver Installer Package User's Guide (EN) Network Guide (EN) LFP RemotePanel 2
<b>Software from Web download for Windows OS</b>	PC Software for Windows OS	LFP Accounting Tool (Job monitoring, consumable cost tracking) Epson Print Layout Firmware Updater (Firmware Package)
<b>Utility Software for Macintosh OS</b>	PC Software for Macintosh OS	Installer Package Epson Color Calibration Utility
<b>Software from Web download for Macintosh OS</b>	PC Software for Macintosh OS	Printer Driver User's Guide (EN) Network Guide (EN) Manual Launcher Software Updater
<b>System</b>	System Requirement	Windows XP/Vista/7/8/8.1/10 (32/64bit) or later CPU: Core 2 Duo 3.05GHz Memory: Memory more than 1GB HDD: Free space more than 32GB
		Epson Color Calibration Utility Manual Launcher Software Updater Adobe ICC Profile EpsonNet Setup EpsonNet Config EpsonNet Print  EpsonNet Setup Manager CopyFactory

**Dimensions & Weight**

**SC-P5000** (Stowed)  
**Weight:** Approx. 52kg



A2: 420 x 594mm

\*1 Figures represent print times only for the Epson test sample image as shown, produced on Plain (draft-line modes). Print speeds are engine only with total throughput time dependent on workflow configuration, paper type, software, file format/size, print resolution, ink coverage, networking, and other factors.

\*2 Users need to choose to configure the machine with either light light black or violet. Once this choice has been made, it is final and cannot be undone or switched at a later time. 99% Pantone coverage requires configuration with violet ink. Configured with light light black provides 98% Pantone coverage.

**Ink Cartridge Compatibility**

200ml Ink Cartridges

• Photo Black	C13T913100
• Cyan	C13T913200
• Vivid Magenta	C13T913300
• Yellow	C13T913400
• Light Cyan	C13T913500
• Vivid Light Magenta	C13T913600
• Light Black	C13T913700
• Matte Black	C13T913800
• Light Light Black	C13T913900
• Orange	C13T913A00
• Green	C13T913B00
• Violet	C13T913D00

**Supplies & Optional Accessories**

Spectroproofer	SpectroProofer Mounter 17" (C12C890631) + ILS30EP (C12C932021)
Roll Media Spindle	C12C811251
Printer Cutter Blade	C12C815351
Ink Maintenance Box	C13T619000
BorderFree	C13T619100
Maintenance Box	
Cleaning Sheet	C13S400045



© 2017 Epson Singapore Pte Ltd. All Rights Reserved. Reproduction in part or in whole, without the written permission from Epson, is strictly prohibited. EPSON and EXCEED YOUR VISION are registered trademarks of Seiko Epson Corporation. All other product names and other company names used herein are for identification purposes only and are the trademarks or registered trademarks of their respective owners. Epson disclaims any and all rights in those marks. Print samples shown are simulations only. Specifications and product availability are subject to change without notice and may vary between countries. Please check with local Epson offices for more information.

Dealer's Stamp  
**FUJIFILM**

For more information or detailed product specification, please call or visit us at  
**FUJIFILM Business Innovation Philippines Corp.**  
25th Floor SM Aura Tower, 26th St. Corner McKinley Parkway, Taguig City 1630 Philippines  
Tel. 632-4878-5200  
fujifilm.com/fbph

Information correct at time of printing  
Printed January 2017