



**LARGER THAN LIFE
PHOTO PRINTS
THAT COME ALIVE.**

Impeccable Photo Quality, Unparalleled Colour Accuracy.

Add a touch of extraordinary performance to your photo printing with the Epson SureColor™ 24-inch SC-P7530 and 44-inch SC-P9530 large format photo printers. Unparalleled wide colour gamut print quality with the UltraChrome PRO12 ink perfectly paired with Epson's PrecisionCore® MicroTFP® printhead, to deliver high quality prints at outstanding speeds. Expect nothing short of impeccable in the quality and accuracy of your photo prints.



SC-P7530



SC-P9530



IT'S IN THE DETAILS.

With Epson UltraChrome™ ink, the SureColor P-series printers redefine consistent, quality printing.

Outstanding Colour Quality

Wide colour gamut with the UltraChrome PRO12 and increased black density with Black Enhance Overcoat.

Exceptional Productivity

With dedicated Matte Black and Photo Black ink channels, print jobs can be continuous.

Trusted Reliability

The printers are designed to be dust-proof with an easy access hatch for printhead cleaning to ensure minimised downtime.



SPECIFICATIONS

SureColor SC-P7530 & SC-P9530

EPSON
EXCEED YOUR VISION

MODEL NUMBER	SC-P7530	SC-P9530
Printer Width	24"	44"
Printing Technology	PrecisionCore Inkjet Technology, Variable-Sized Droplet Technology	
Printing Method	MicroTFP Printhead	
Printhead	9600 nozzles (800 nozzles x 12 channels x 1 head)	
Nozzle Configuration	2400 x 1200 dpi	
Maximum Resolution	3.5pl	
Minimum Ink Droplet Volume	97 sec (Level 1)122 sec (Default) Premium Glossy	
Print Speed	Photo Paper 170gsm A1 size/ ISO Bike	219 sec (Level 1)285 sec (Default) Premium Glossy Photo Paper 170gsm B0 size/ ISO Bike
Ink System	UltraChrome PRO12 Pigment Ink	
Ink Type	Cyan, Vivid Magenta, Yellow, Light Cyan, Vivid Light Magenta, Orange, Green, Violet, Photo Black,	
Colours	Matte Black, Gray, Light Gray	
Ink Capacity	350ml, 700ml	
Paper Handling	Friction Feed	
Paper Path	2" roll core media: Max. 103 mm/6 kg, 3" roll core media: Max. 150 mm/6 Kg	
Maximum Roll Diameter / Weight	2" roll core media: Max. 103 mm/10kg, 3" roll core media: Max. 150 mm/10Kg	
Paper Width (Roll)	Roll Paper: 254 mm to 620 mm, Cutsheet: 210 mm to 620 mm	Roll Paper: 254 mm to 1118 mm, Cutsheet: 210 mm to 1118 mm
Paper Thickness	Roll : 0.08 mm to 0.5 mm, Cutsheet : 0.08 mm to 1.5 mm	
Control Panel	4.3 inch touch screen	4.3 inch Optical Touch Colour LCD
Connectivity	Super-Speed USB, 100BASE-TX /1000BASE-T	
Printer Interface	USB Interface (Hi-Speed USB/USB), 1000BASE-T/100BASE-TX	
Printer Language	ESC/P raster	
Memory	2GB	
Power and Operating Requirements	AC 100 to 240V 50/60Hz	
Power Requirements	3.4-1.6A	
Rated Current	Operating: Approx. 85W	Operating: Approx. 110W
	Ready: Approx. 32W	Ready: Approx. 32W
	Sleep: Approx. 3.4W	Sleep: Approx. 3.4W
Power Consumption	Power Off (Stand by): Approx. 0.3W	Power Off (Stand by): Approx. 0.3W
Temperature	Operating: 10°C to 35°C, Storage/Packing: -20°C to 60°C, Unpacking: -20°C to 40°C	
Humidity	Operating: 20 - 80% (no condensation), Storage: 5 - 85% (no condensation)	
Acoustic Noise Level	Operating: Approx. 49.5dB(A), Sleep: Approx. 31.5dB(A)	
Sound Pressure Level <db(A)>	Operating: Approx. 7.5B(A)	
Sound Power Level <B(A)>		
Utility Software	Windows Install Navi - Printer driver - EpsonNet Setup - EpsonNet Print - EpsonNet Config SE - Epson Software Updater - EPSON manuals - Manual Launcher - Epson Control DashboardMac Setup Navi EpsonNet Config SE Epson Software Updater	
Utility Software (Bundled in CD)	Windows Install Navi, Web Installer, Firmware Updater, PS Driver, HDI Driver, XPS Driver, Epson Media Installer, EpsonNet Setup Manager, Epson Device Admin, Epson Edge Dashboard, Epson Edge Print, Epson Print Layout, LFP Accounting tool, Adobe ICC Profiles, Mac Web Installer, Install Navi - Printer driver - EpsonNet Config - Epson Software Updater - Uninstaller - Epson Manuals, Epson Media Installer, Firmware Updater, Linux, Printer driver	
Utility Software (Web delivery)		
Printer Dimensions	Storage Dimensions (W x H x D) 1,401mm x 1,218mm x 667mm 1,909mm x 1,218mm x 667mm	
Storage Dimensions (W x H x D)	1,401mm x 1,218mm x 2,211mm 1,909mm x 1,218mm x 2,211mm	
Printing Dimensions (W x H x D)	121.7kg 153.8kg	
Weight		
What's in the box	Printer, Printer Stand, Initial Ink Cartridge, AC Power Cable, Setup Guide, Software CD-ROM, Maintenance Box.	
Options	SpectroProofer, SpectroPhotoMeter, ILS30EP, Auto Take Up Reel Unit, Hard Disk Unit, Adobe PostScript 3 Expansion Unit, Roll Media Adapter	
Consumables	Ink Cartridge, Maintenance Box, Auto Cutter Spare Blade, Borderless Replacement Pad Kit	

SC-P7530

Dimension & Weight
Weight: 121.7kg



SC-P9530

Dimension & Weight
Weight: 153.8kg



Supplies & Optional Accessories

SC-P7530	C11CH12402
SC-P9530	C11CH13402
SC-P7530/9530 PK IC (700ml)	C13T44N100
SC-P7530/9530 CY IC (700ml)	C13T44N200
SC-P7530/9530 VM IC (700ml)	C13T44N300
SC-P7530/9530 YL IC (700ml)	C13T44N400
SC-P7530/9530 LC IC (700ml)	C13T44N500
SC-P7530/9530 VL IC (700ml)	C13T44N600
SC-P7530/9530 LB IC (700ml)	C13T44N700
SC-P7530/P9530 MK IC (700ml)	C13T44N800
SC-P7530/9530 LI IC (700ml)	C13T44N900
SC-P7530/9530 OR IC (700ml)	C13T44NA00
SC-P7530/9530 GR IC (700ml)	C13T44NB00
SC-P7530/9530 VI IC (700ml)	C13T44ND00
SC-P7530/9530 PK IC (350ml)	C13T44V100
SC-P7530/9530 CY IC (350ml)	C13T44V200
SC-P7530/9530 VM IC (350ml)	C13T44V300
SC-P7530/9530 YL IC (350ml)	C13T44V400
SC-P7530/9530 LC IC (350ml)	C13T44V500
SC-P7530/9530 VL IC (350ml)	C13T44V600
SC-P7530/9530 LB IC (350ml)	C13T44V700
SC-P7530/9530 MK IC (350ml)	C13T44V800
SC-P7530/9530 LI IC (350ml)	C13T44V900
SC-P7530/9530 OR IC (350ml)	C13T44VA00
SC-P7530/9530 GR IC (350ml)	C13T44VB00
SC-P7530/9530 VI IC (350ml)	C13T44VD00

© 2020 Epson Singapore Pte Ltd. All Rights Reserved. Reproduction in part or in whole, without the written permission from Epson, is strictly prohibited. EPSON and EXCEED YOUR VISION are registered trademarks of Seiko Epson Corporation. All other product names and other company names used herein are for identification purposes only and are the trademarks or registered trademarks of their respective owners. Epson disclaims any and all rights in those marks. Print samples shown are simulations only. Specifications and product availability are subject to change without notice and may vary between countries. Please check with local Epson offices for more information.

FUJIFILM

For more information or detailed product specification, please call or visit us at
FUJIFILM Business Innovation Philippines Corp.
 25th Floor SM Aura Tower, 25th St. Corner McKinley Parkway, Taguig City 1630 Philippines
 Tel. 632-8878-5200
fujifilm.com/ibph

Information correct at time of printing
 Printed February 2020

Sales Enquiries
800 120 5564

[f](https://www.facebook.com/EpsonSEA) EpsonSEA [i](https://www.instagram.com/EpsonSEA) EpsonSEA [@EpsonSEA](https://www.twitter.com/EpsonSEA) [You Tube](https://www.youtube.com/EpsonSoutheastAsia) EpsonSoutheastAsia [in](https://www.linkedin.com/EpsonSoutheastAsia) Epson Southeast Asia

For latest specifications, visit www.epson.com.sg/p-series or call **800 120 5564**.

Epson Singapore Pte Ltd 1 Harbourfront Place, #03-02 HarbourFront Tower One, Singapore 098633. Tel: (65) 6586-5500 Fax: (65) 6271-9755

Epson Customer Care Centre 108 Pasir Panjang Road, #04-08 Golden Agri Plaza, Singapore 118535. Epson Helpdesk: 800 120 5564. Operating hours: Monday - Friday, 9am - 6pm, Saturday, 9am - 1pm. Closed on Sunday and Public Holiday.