





## **New Times, New Apeos**

The new "Apeos" offers advanced features with high security level and easy operability to help business diversify with times. "Apeos" devices are able to connect smoothly with a variety of solutions and services to realise an all new agile remote workstyle of working anytime, anywhere.







# Small - Smart - Scalable Solution for your everyday business requirements

## Apeos C3060 / C2560 / C2060

•					
Copy/Print	Scan	Fax*4	<b>Printing Resolution</b>	Control Panel	
Colour/Monochrome	Colour/Monochrome				•Wireless LAN
C3060 30 ppm*1	2 sided 20 *2*3			7" Tilted Colour	Supported
C2560 25 ppm*1	2 sided Scanning 80 ppm*2*3	Super G3 FAX	1,200 × 2,400 dpi <sup>*5</sup>	Touchscreen	•Mobile Supported
C2060 20 ppm*1	1 sided Scanning 55 ppm*3				•Cloud Interactive

<sup>\*1:</sup> A4 LEF. \*2: For Apeos C3060 / C2560 single pass DADF model (2 sided scanning). \*3: A4 LEF 200 dpi to Folder. \*4: Optional. \*5: Print Function.

#### Various combinations



Standard Configuration Model-1T



With 1 Tray Module\*



With 1 Tray Module



With 3 Tray Module\*



With Side Tray\* Supports distribution output for each of copy, print, and fax jobs

## Uncompromising usability along with compatibility

## Multipurpose device with small footprint and easy setup

- Compact design with width of 590 x depth of 659 mm
- Select a right configuration of 1, 2 or 4 trays as per your growing requirements





2 tray configuration with its optimal height and adjustable UI makes it easy to operate for all (including people with special needs).

Shared machines for offices.

Increase to maximum paper capacity of 2,096 sheets\*.

\* 80 gsm Paper, Standard + 3 Tray Module (optional).



#### Exceptional colour accuracy and print quality


- High-resolution printing of 1,200 x 2,400 dpi achieved with LED printhead
- Smooth slating line and text reproduction with image enhancement processing
- Digital Correction Technology IReCT\*, reduces colour-to-colour misregistration
- \* Image Registration Control Technology.



### Quick scanning of high-volume originals\*1

- Up to 80 ppm can be read at high speed in Scan<sup>\*2</sup>
- Up to 130 sheets can be loaded
- One pass DADF will not damage the original document
- Instantly scan without manual entry of each original size
- Automatically converts custom size originals to standard size
- \*1: Apeos C3060 / C2560 single pass DADF model.
- \*2: 1 pass 2 sided scanning. Our Standard Paper (A4 LEF), 200 dpi, to Folder.





Direct scan to or print from USB\* for efficient

#### \_: \_ \_ . . . .

- You can directly print the documents stored on a USB flash drive or scanned data can be directly stored on a USB flash drive without using a PC
- \* Optional.

operations



#### Quick startup and output for greater efficiency

- Fast Boot Mode prepares the operation panel in 6 seconds\*1
- $\bullet$  The control panel becomes operatable from Low Power Mode in approximately 1 second  $^{\star_2}$
- Quick warm up in less than 28 second
- First Copy Output Time in 4.9 seconds\*3
- \*1: Depending on the status of the main unit and configuration of options, it may not operate or take more than 6 seconds.
- \*2: Please specify the time to Sleep Mode longer than the time to Low Power Mode.
- \*3: A4 LEF for Apeos C3060 when in horizontal/Monochrome preferred mode.

#### Various finishing options are available according to your needs

#### Finisher-A2



#### Finisher-B4/B5 with Booklet Maker Unit



Supports single and double Staple-free Stapling \*1




- \*1: Staple-free stapling is available with Finisher-B5.
- \*2: Optional
- \*3: Booklet Maker Unit is required. When specifying Saddle Staple or Single Fold with Finisher-B4/B5, paper is not folded but creased.
- \*4: 80 gsm paper or less.

## Quick and simple operability

#### Simple layout with easy navigation

Black and gray tone UI gives better contrast for easy recognition.

- Icons are evenly spread for easy recognition
- Consistent operation steps of each function for easy recall
- Home screen personalisation for ease of access to commonly used functions
- Pin regular settings for registering frequent or repeated jobs
- Clear visible light notifications for completed or error jobs
- Subtle sound notification for alert and attention



#### Smartphone becomes a "portable operation panel"

Seamless connectivity with mobile devices for Copy, Fax, Print, Scan\*1 jobs using the Print Utility\*2 application.

- Mobile device can be used as an alternative UI for operations control to minimise common touch points
- Frequent settings can be saved as "Favourites"
- Directly send fax or email with the addresses stored in the smartphone
- Minimise printer touch points for hygiene reasons
- Quickly establish direct Wi-Fi connection by scanning the QR code on the user panel

Note: Connect to machine via wireless environment or Wi-Fi Direct connection.

- \*1: Scan to Mobile, E-mail, Scan to Folder.
- \*2: It can be downloaded free of charge from Google Play™ or App Store.

#### Flexibility in office layout

Supports wireless LAN environment\*1.

- Supports free addressing in the office with Wi-Fi support
- Up to five Wi-Fi Direct multifunction devices can be connected at the same time
- Supports direct mobile printing\*2
- Print Utility, AirPrint, and Mopria® Print Service are supported
- \*1: Optional.
- \*2: When connecting to Wi-Fi Direct.

## Print out from any multifunction device within the office

With Server-less On-Demand Print\*, you have the flexibility to print and collect the print outs from any of the connected multifunction devices.


- Improves productivity by printing from another available multifunction device when the current device is in use
- Up to 100 units can be linked
- Specific job settings can be revised at the device level to save time (1 sided to 2 sided, adding staple, all monochrome)
- \* Optional.

## Simple device management with Server-less Authentication

Server-less Authentication\* enables user information to be synchronised among multifunction devices in the same group and allows administrators to reduce their workloads.

- Simply tap your card to link the user ID with the multifunction device
- The ID information is automatically shared with the other multifunction devices in the same network
- Authentication can be performed with any devices in the office
- \* Optional.





## Various features saving time and effort in scanning operation


Scanned data can be transferred through a variety of methods including Email, URL, and send to PC (SMB/FTP/SFTP).

- Data can be sent by using multiple features simultaneously
- Improve your digitalisation process with features including automatic orientation of scanned page to upright position, correcting the skewed page, or removing blank pages
- In addition to TIFF and JPEG, the scanned data can be converted to OCR-enabled\* or high compression/ specific colour PDF or DocuWorks documents. Also they can be converted to editable Excel/Word documents\*
- With ScanAuto, you can easily send the scanned data to your e-mail address by simply pressing a button
- \* Optional

## Digitisation of paper documents for effortless document management

With Scan Delivery\*, you can automatically process and store scanned images by simply pressing the preset button for each workflow or document type.

- Automate to set file format, file name, OCR\*, etc.
- Automatically stores scanned and processed documents in the appropriate destination
- Specify particular words or characters in a document as the folder or file name
- $\, \bullet \,$  0 and other frequently mis-recognised characters can be read correctly
- \* Optional.





#### QR codes and bar codes application

Where QR code or bar code is available on the headsheet or content body of the original document for scanning, Scan Delivery will recognise and process the information accordingly.

## Streamline operations for remote work style

## Do not miss any faxes when you are working remotely

Paperless fax function automatically stores received faxes into folders which can be transferred to a PC or sent as emails.

- Received faxes can be forwarded to your mobile device by email
- Received faxes can be transferred to Working Folder\*1
- It can be sorted by fax number, date received, and person in charge\*2
- $\bullet$  Incoming fax processing can be switched by time, day of the week and  $\mathsf{period}^{*2}$
- For example, you can switch from paper-based output to an electronic transfer in a single operation\*<sup>2</sup>
- \*1: Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.
- \*2: Optional

## Easy and secure output even when you are working remotely


With Cloud On-Demand Print\*, you can register documents from a PC or mobile device to the cloud server and print them from the designated multifunction device.

- Can be operated securely using a User ID and password
- Fear of loss or stolen data is minimised
- No dedicated driver is required
- \* Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.

#### Share information anytime, anywhere

With Working Folder\* and internet access, documents can be viewed regardless of time and location.

- Can be linked smoothly with multifunction devices, DocuWorks, and mobile devices
- Documents in Working Folder can be printed from the control panel
- Scanned documents will be assigned a file name and stored in Working Folder. An email notification will be sent to relevant users



\* Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.

#### Supporting Universal Print by Microsoft


By registering multifunction devices to Universal Print by Microsoft in advance, users  $^{\!\!\!\!\!\!\!\!\!^{\, 1}}$  authenticated with Microsoft Entra ID  $^{\!\!\!\!\!\!\!\!\!^{\, 2}}$  can print from anywhere through cloud.

- $^{\star}1:$  Organizations with or Microsoft Windows Enterprise or Microsoft 365 subscriptions.
- \*2: Formerly Azure Active Directory.

#### Centralised cloud integration

Cloud Service Hub\* allows single sign-on to multiple cloud storage services.

- Specific storage location can be assigned for scanned documents directly from the multifunction device
- Searching documents from multiple cloud services is supported
- Full-text search on scanned documents can be performed with OCR



\* Cloud services provided by FUJIFILM Business Innovation. A separate contract is required.

#### Initiatives for environmental consideration



We are working to develop environmentally conscious products, including technologies that reduce the power consumption of multifunction devices and printers to achieve lower environmental impact.

Fujifilm Group introduced the certification program in which we clarify the environmental value of each product by assessments at the time of product development, conduct the evaluation based on our in-house certification criteria and certify the products\* that are excellent in reducing environmental impact as "Green Value Products".

This product was certificated as a "Silver" rank product that reduces environmental impact at a higher level than industries' standard.

\* Products and services excellent in reducing environmental impact are those designed in consideration of environmental impact throughout their life cycle from acquisition of raw materials, production, usage, disposition, to reuse.

#### Initiatives for energy conservation

- Achieve both high image quality and energy conservation by equipping the LED printhead that enables space and energy saving design, as well as Super EA-Eco toner that has lowtemperature fusing performance
- Reduce the power consumption with the smart power saving feature that solely powers on the required parts according to the functions being used by customers

#### Initiatives for resources conservation

- Staple-free stapling that helps reducing waste and that also can be used with peace of mind at certain places where need considerations for safety or any contamination
- Functions contributing to paper consumption reduction
   -Private Charge Print, Scan, Paperless Fax, Pages per
- Side/Multiple-Up etc.
- Adopt design for making products easy to reuse/recycle after use

## Safeguard important information

Information is an important asset which should be protected at all cost

#### Protect from unauthorised user

### Multiple options of setting user authorisation allow administrator to select a right combination as per given environment.

- Local Authentication
- Authentication by Remote Server\*
- IC Card Authentication\*
- User-specific feature access
- Private Charge Print
- \* Optional

## Additional layer of unwanted access can be created for specific users (e.g. guests).

- Secondary Ethernet Kit\*
- \* Optional.

#### **Protects Data**

### Protects against any malicious intent of hacking, tampering with device / system settings.

- Encryption of stored data
- Uses TPM\* 2.0 chip for encryption key management
- Deletes settings and document information all at once
- \* Trusted Platform Module

### Protects the information by means of strong encryption while transferring it between devices, servers etc.

- Encryption of communication paths by SSL/TLS or IPsec
- Encryption when transferring via SMBv3 and SFTP
- Scan file encryption/signature
- Email encryption and signature by S/MIME
- TLS version limit
- Elliptic curve cryptography
- WPA3

#### Protect from unauthorised access

Protects device settings at multiple levels by clearly demarking change restrictions for different target audience - End users, IT administrators and Service Engineers.

- Service representative operation restriction
- Account lock to prevent unauthorised access
- Information for changing the default password
- Warnings displayed when using global IP address

#### Prevents unauthorised program from installing without notice. Robust IT audits are supported with device data logs for easy tracking.

- Software signature verification
- Remote update restrictions
- IP address filtering
- Tampering detection at startup and automatic restoration when tampering is detected
- Prevention of tampering during operation
- Audit log
- Audit log system transfer

#### Prevents operation errors

### Prevents information leakage due to inadvertent mistakes by administrators and users.

- Scan documents to be delivered to fixed destination
- Re-enter fax recipient
- Annotations
- Hidden text printing\*
- \* Optional.

### Security certifications

 Certified with ISO/IEC 15408, which is the international standard for designing and operating IT security

#### Reliable support system

#### Easy solutions to resolve problems

From supplies replacement to unexpected device failures, most problems can be resolved without waiting for the service representatives or sales representatives.

#### 1. Resolve problem using the "Help" function on the device

- Self Help information is available on the control panel
- Self Help information can be accessed via the mobile device by scanning the QR code displayed on the control panel





#### 2. "Remote Assistance" with the help of operators

- Connects directly to the Support Centre
- An operator will remotely access the multifunction device to resolve the problem by guiding through the steps on the shared control panel

## Keeping a close eye on your multifunction device on a daily basis

Monitoring the multifunction device status to minimise operation down time.

- Check billing meter
- Automatically delivers consumables when cartridges level is low
- Detect machine errors for early invention to rectify the problem Note: You need to apply for using the EP service. (free of charge)

#### Making a backup of multifunction device's settings

Device Setup Editor is a free tool which helps you both, in editing device setting and creating a much-needed information backup for business continuity reasons.

- $\bullet\,$  A back up the device / printer settings can be created onto the PC
- Administrator can optimize device usage by viewing/editing these settings, best suited for their environment.
- When installing a new device, these settings can be migrated (or cloned) from the existing device to the new device

#### Apeos C3060 / C2560 / C2060 **Functions & Specifications**

#### Basic Specifications / Copy Function

	ecilicatio	ns / Copy Fun		60060	
Item		C3060	C2560	C2060	
Type Memory Car	acity	Desktop / Console 4 GB (Max: 4 GB)			
Memory Capacity Storage Device Capacity*1		128 GB			
Colour Capa		Full colour			
Scan Resolut		600 x 600 dpi			
Printing Reso		1,200 x 2,400 dpi			
		[Embedded Plug-in	s / Custom Services	] *3	
Warm-up Tir	me <sup>*2</sup>	When enabled: 28 stemperature)	seconds or less (23 o	degrees Celsius room degrees Celsius room	
Recovery Tin (Recovery Ti Sleep Mode)	me from	14 seconds or less (23 degrees Celsius	12 seconds or less room temperature)	12 seconds or less	
Original Size		Maximum of A3, 11 Book	x 17", 297 x 432 m	m for both Sheet and	
	Max	A3, 11 x 17"			
Paper Size	Min	A5 [Postcard (100 : Monarch, when usin			
	Image loss width	Lead edge 4.0 mm,	Trail edge 2.0 mm, R	Right/Left edge 2.0 mm	
Paper	Paper Tray	60 to 256 gsm			
Weight*4	Bypass Tray	60 to 216 gsm			
First Copy	B/W	4.9 sec. (A4 LEF / Monochrome priority mode)		rome priority mode)	
Output Time	Colour	6.7 sec. (A4 LEF / Colour priority mode)	8.1 sec. (A4 LEF / Colour pi	riority mode)	
	A4 LEF /	B/W: 30 ppm,	B/W: 25 ppm,	B/W: 20 ppm,	
	JIS B5 LEF	Colour: 30 ppm	Colour: 25 ppm	Colour: 20 ppm	
Continuous	A4	B/W: 23 ppm, Colour: 23 ppm	B/W: 19 ppm, Colour: 19 ppm	B/W: 16 ppm, Colour: 16 ppm	
Copy Speed*5	JIS B5	B/W: 17 ppm, Colour: 17 ppm	B/W: 14 ppm, Colour: 14 ppm	B/W: 11 ppm, Colour: 11 ppm	
.,	JIS B4	B/W: 20 ppm, Colour: 20 ppm	B/W: 16 ppm, Colour: 16 ppm	B/W: 13 ppm, Colour: 13 ppm	
	A3	B/W: 17 ppm, Colour: 17 ppm	B/W: 14 ppm, Colour: 14 ppm	B/W: 11 ppm, Colour: 11 ppm	
	Standard	500 sheets x 1-tray			
Paper Tray Capacity*6	Optional	1 Tray Module / 1 Tr 1-tray 3 Tray Module: 500	ay Module with Cab sheets x 3-tray	oinet: 500 sheets x	
	Max	2,096 sheets [Stand	dard + 3 Tray Module	e]	
Output Tray	Capacity*7	Upper Center: 250 sheets (A4 LEF), Lower Center: 250 sheets (A4 LEF)			
Power Suppl	У	AC220-240 V +/- 10 %, 8 A, 50/60 Hz common			
Maximum Po Consumption		1.76 kW (AC220 V Sleep Mode: 0.4 W Ready Mode: 83 W	+/- 10 %), 1.92 kW ( (AC230 V +/- 10 %) (AC230 V +/- 10 %)	(AC240 V +/- 10 %)	
		W 590 x D 659 x H W 590 x D 659 x H installed.)		onal 1 Tray Module is	
	Model-CPS	W 590 x D 659 x H with Cabinet is insta	alled.)	otional 1 Tray Module	
Dimensions		is installed.)	<u> </u>	otional 3 Tray Module	
		W 590 x D 659 x H W 590 x D 659 x H installed.)		onal 1 Tray Module is	
	Model-CPS-B			otional 1 Tray Module	
				otional 3 Tray Module	
Weight*8	Model-CPS	68 kg 79 kg (when option 91 kg (when option 94 kg (when option	al 1 Tray Module wit	h Cabinet is installed.)	
AACIRIIL .	Model-CPS-B	70 kg 81 kg (when option 93 kg (when option 96 kg (when option	al 1 Tray Module wit	th Cabinet is installed.)	
*1. The Ctores	ro Douiso Cana	city is not totally availa	bla fan anna		

- \*1: The Storage Device Capacity is not totally available for customers.

  \*2: It may change depending on usage conditions.

  \*3: Embedded Plug-ins / Custom Services are enabled as factory default. You can change the settings if needed.

  \*4: It is recommended to use our recommended paper. Correct print output may not be possible depending on the requirement.

  \*5: The speed may be reduced due to the image quality adjustment.

  \*6: 80 gsm paper.

  \*7: 70 gsm paper.

  \*8: Including Toner Cartridge.

#### **Print Function**

Item		Description
Туре		Built-in type
Continuous Print Speed*1		Same as the Basic Specifications / Copy Function
Printing	Standard	[PCL Driver] Standard: 1,200 x 2,400 dpi, High Quality: 1,200 x 2,400 dpi, High Resolution*2: 1,200 x 1,200 dpi
Resolution	Optional	[Adobe® PostScript® 3™ Driver] High Speed (Standard): 600 x 600 dpi, High Quality: 1,200 x 2,400 dpi, High Resolution*²: 1,200 x 1,200 dpi
Page	Standard	PCL5 / PCL6
Description Language	Optional	Adobe® PostScript® 3™
V	Standard	[PCL Driver] Windows 11 (64 bit), Windows 10 (32 bit / 64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit), Windows Server 2012 R2 (64 bit), Windows Server 2012 (64 bit)
Supported Operating		[Mac OS X Driver] macOS 13 / 12 / 11 / 10.15 / 10.14
System*3	Optional	[Adobe® PostScript® 3™ Driver] Windows 11 (64 bit), Windows 10 (32 bit / 64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit), Windows Server 2012 R2 (64 bit), Windows Server 2012 (64 bit) macOS 13 / 12 / 11 / 10.15 / 10.14
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T, USB3.0
interrace	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)

- \*1: The speed may be reduced due to the image quality adjustment. The printing speed may be reduced depending on the document.

  \*2: High Resolution mode is recommended for printing fine lines or cadastral maps.

  \*3: Please refer to our official website for the latest supported OS.

#### Scan Function

Item		Description	
Туре		Colour Scanner	
Scan Resolution		600 x 600 dpi, 400 x 400 dpi, 300 x 300 dpi, 200 x 200 dpi	
Scan Speed		Same as the Scan Speed for the Duplex Automatic Document Feeder	
Interface	Standard	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T	
interrace	Optional	Wireless LAN (IEEE 802.11a / b / g / n / ac)	

#### Fax Function (Optional)

Item	Description	
Original Size	Max: A3, 11 x 17", Long document (Longest 600 mm)	
Recording Paper Size	Max: A3, 11 x 17"; Min: A5	
Transmission Time	2 seconds and more but fewer than 3 seconds*1	
Transmission Mode	ITU-T G3	
Applicable Lines	Telephone subscriber line, PBX, Fax communication (PSTN), Maximum 3 ports*2 (G3-3 ports)	

- \*1: When A4 size document with approximately 700 characters is transmitted in standard image-quality (8 x 3.85 lines/mm) and in high-speed mode (28.8 kbps or faster, JBIG). Only indicates the time for transmitting the image information and does not include the communication control time. The total communication time will vary depending on the contents of the document, the type of machine receiving the fax, and line condition.
  \*2: No. of FAX lines is up to 3 ports. Port refers to number of channels for FAX.

#### **Duplex Automatic Document Feeder**

Daplex Materialic Document recaci					
Item		C2560	C2060		
Original Siz Paper Weig		Max: A3, 11 x 17"; Min: A5 <sup>+1</sup> 38 to 128 gsm (In Duplex: 50 to 128 gsm)			
Capacity*2		110 sheets	110 sheets		
Scan	Copy (A4 LEF, Simplex)	B/W: 25 ppm, Colour: 25 ppm	B/W: 20 ppm, Colour: 20 ppm		
Speed*3	Scan	B/W: 55 ppm, Colour: [Standard Document (A	55 ppm A4 LEF), 200 dpi, to Folder]		
Note: Installed for Model CDC or standard					

Note: Installed for Model-CPS as standard.
\*1: The minimum custom size is 125 x 85 mm.
\*2: 70 gsm paper.
\*3: The scanning speed varies depending on the documents.

#### Duplex Automatic Document Feeder [1 pass, 2 sided scanning]

			- 1	,	0-
	Item		C3060	C2560	
	Original Size / Paper Weight		Max: A3, 11 x 17"; Min: A6*1 38 to 128 gsm (In Duplex: 50 to 128 gsm)*2		
	Capacity*3		130 sheets		
	Scan Speed*4	Copy (A4 LEF, Simplex)	B/W: 30 ppm, Colour: 30 ppm	B/W: 25 ppm, Colour: 25 ppm	
		Scan	B/W: 55 ppm, Colour: 55 ppm (1 pass, 2 sided scanning: B/V [Standard Document (A4 LEF)	V 80 ppm, Colour 80 ppm	n)

- Note: Installed for Model-CPS-B as standard.
  \*1: The minimum custom size is 49 x 85 mm.
  \*2: The minimum custom size is 49 x 85 mm.
  \*3: 70 gsm paper.
  \*4: The scanning speed varies depending on the documents.

#### Notes

- Jif the storage media of the base unit fail, loss of received data, accumulated data, registered setting data, etc. may occur. In no event shall "the company" be liable for any damages whatsoever arising from loss of data.
- 2) Functional spare parts will be available for at least 7 years after the product is no longer manufactured

#### Side Tray (Optional)

Item	Description	
Paper Capacity*	100 sheets	
Dimensions	W 347 x D 419 x H 201 mm	

<sup>\* 70</sup> gsm paper

#### Finisher-A2 (Optional)

Item		Description		
Туре		Sort (Offset available) / Stack (Offset available)		
Paper Size		Max: A3, 11 x 17"; Min: Postcard (100 x 148 mm)		
Paper Weig	ht	60 to 256 gsm		
Paper Capacity*1		[Without Stapling] A4: 500 sheets; JIS B4: 250 sheets; A3 or larger: 200 sheets; Mixed Size Stacking*2: 250 sheets [With Stapling] 30 sets		
	Capacity	A4: 50 sheets (90 gsm or less), JIS B4 or larger: 30 sheets (90 gsm or less)		
Staple	Paper Size	Max: A3, 11 x 17"; Min: JIS B5 LEF		
·	Paper Weight	: 60 to 256 gsm		
	Position	Single stapling, Dual stapling		
Dimensions*3 / Weight		W 658 x D 461 x H 238 mm, 11 kg		

#### Finisher-B4 / B5 (Optional)

	, ,	1 /			
Item		Finisher-B4 Finisher-B5			
Туре		Sort (Offset available*1*2) / Stack (Offset available*1*2)			
Paper Size*3		Max: A3, 11 x 17"; Min: A5			
Paper Weigh	nt	60 to 256 gsm			
Paper Capacity*4		[Without Stapling] A4: 2,000 sheets, JIS B4 or larger: 1,000 sheets, Mixed Size Stacking*s: 300 sheets [With Stapling] A4: 100 sets or 1,000 sheets*6, JIS B4 or larger: 75 sets or 750 sheets [With Booklet Finishing*7] 50 sets or 600 sheets [With Booklet Finishing*7] 50 sets or 600 sheets			
	Capacity	50 sheets (90 gsm or less)	Staple: 50 sheets (90 gsm or less), Staple-free Staple*8*9: 10 sheets (80 gsm or less)		
Charala	Paper Size*10	Max: A3, 11 x 17"; Min: A5 LEF			
Staple	Paper Weight	60 to 256 gsm	Staple: 60 to 256 gsm, Staple-free Staple <sup>**9</sup> : 60 to 105 gsm		
	Position	Single stapling, Dual stapling	g		
	Number of Holes	2-hole / 4-hole punch or 2-ho	ole / 3-hole punch (US Specifications)		
Punch*11	Paper Size*12	Max:A3, 11×17"; Min: A5 LEF			
	Paper Weight	60 to 220 gsm			
Booklet	Capacity	Saddle Staple: 15 sheets; S	ingle Fold: 5 sheets		
Finishing*7	Paper Size	Max: A3, 11 x 17"; Min: A4,	, Letter		
i iiiisiiiiig	Paper Weight	Saddle Staple: 60 to 80 gsm	n <sup>*13</sup> , Single Fold: 60 to 105 gsm		
Dimensions*14		W 607 x D 653 x H 1,041 mm With Booklet Maker Unit: W 607 x D 673 x H 1,079 mm			
Weight		26 kg, Punch Kit: + 2 kg, Booklet Maker Unit: + 10 kg	29 kg, Punch Kit: + 2 kg, Booklet Maker Unit: + 10 kg		
Noto: Einicher	Note: Finisher-R4 / Finisher-R5 is available only when optional 1 Tray Module with Cabinet or 3				

Note: Finisher-B4 / Finisher-B5 is available only when optional 1 Tray Module with Cabinet or 3 Tray Module is attached to Main Unit.

Note: Only stapled stapling is available with Finisher-B4. You cannot add staple-free stapling function. Note: Both stapled stapling and staple-free stapling are available with Finisher-B5.

1: The offset feature is set to disabled by factory default. The setting can be changed as necessary.

2: Outputs less than 210 mm width are delivered without offset stacking.

3: Paper in the sizes larger than A3 or 11 x 17" or smaller than A5 are delivered to the Centre Tray.

4: 70 est paper.

- \*3 : Paper in the sizes larger than A3 or 11 x 17" or smaller than A5 are delivered to the Centre Tray.
  \*4 : 70 gsm paper.
  \*5 : When larger size sheets are stacked on top of smaller size sheets.
  \*6 : 75 sets or 750 sheets with dual stapling.
  \*7 : The Booklet Finishing function requires the optional Booklet Maker Unit for Finisher-B. Make a crease allows you to fold easily. After a job with the Booklet Finishing function specified has been output, the next job may not be delivered until the sheets are removed from the output tray. Also, if larger size sheets are stacked on top of smaller size sheets after a job with the Booklet Finishing function specified has been run, the next job may not be delivered until the sheets are removed from the output tray.
  \*8 : Staple-free stapling is available with Finisher-B5.
  \*9 : Staple-free stapling does not have binding force equal to stapled stapling. Bound part may be easily separated depending on the paper, temperature, humidity, and how the page is turned over.
  \*10: Available staple positions vary depending on the paper size.
  \*11: The Punch function requires the optional 2/4 Hole Punch Kit for Finisher-B or US 2/3 Hole Punch Kit for Finisher-B.
  \*12: Available number of punch holes varies depending on the paper size.
  \*13: Covers can be up to 220 gsm (Extra Heavyweight).
  \*14: Inner connector within the body is excluded.

#### **Enhanced basic functions**

#### Copy

- Output Color
- Paper Supply
   Reduce/Enlarge
- Slight Reduction
   Auto 2 Sided Output
- Pages per Side
   (2 Pages / 4 Pages / 8 Pages)
- Copy Output (uncollated/collated)
   Single Color / Dual Color Copy
- Copy (ID Card)
- Mixed Size Originals
- Original Size
   Image Enhancement
- Book Copying
   Edge Erase

- Image Shift
   Mirror Image / Negative Image
- Image Rotation
   Booklet Creation
- Multiple-Up x Booklet Creation2 Sided Book Copying
- Covers Poster
- Repeat Image
   Preset Repeat Image
- AnnotationsWatermark(optional)
- Joint JobSample Job

- Delete Outside / Delete Inside
   Staple / Staple-free Staple /
  Punch / Crease / Saddle Staple
- (optional)

#### Print

- Adobe® PostScript® 3™
- (optional) Multi-Model Print Driver 2
- Microsoft Universal Print
- Secure Print
- Sample Set
   Delayed Print
- Print from Folder
  Form Registration
  Multiple-Up
  Booklet Creation

- Multiple-Up x Booklet Creation
- Poster
- Covers / Separators

- Envelope printing
   Private Charge Print
   Charge Print
   Print from USB (optional)
   Staple / Staple-free Staple / Punch / Crease / Saddle Staple (optional)
- Server-less On-Demand Print (optional)

#### Fax (Optional)

- G3 × maximum 3 ports (optional)
- Internet Fax SIP Fax (optional)
- Send Direct Fax
   Address Book (maximum 5,000 entries)
- Broadcast Transmission / Group Transmission
   Redial / Resend Unsent Documents
- Rotate 90 Degrees
- Preview
- 2 Sided Scanning
- Resolution
- Lighten / Darken
   Original Type

- Mixed Size OriginalsTransmission Header
- Priority Send / Delay StartCover Page
- Remote Folder
   Transmission Report
- Activity Report
   Re-enter Recipient
- Prevents Unsolicited Faxes
   Prohibit Direct Fax
- Receive Paperless Fax
   Simple Image Log Support
- Paperless Fax Delivery (optional)

#### Scan

- Scan to Folder
- (TWAIN driver/Web browser)

  Transfer via SMB/FTP/SFTP
- Scan (URL)
- Scan to USB (optional)
- · Simultaneous transmission such as Email / Transfer via SMB, etc. ScanAuto
- Preview
- Color Scanning
- 2 Sided Scanning
   Mixed Size Originals
- File Format: TIFF / JPEG / PDF\*1 / XDW(DocuWorks)\*2
- Microsoft Excel/Word format(optional)
   Single File for Each Page
- Searchable Text (optional)
   Background Suppression
- Shadow SuppressionAuto Upright Orientation
- Skew Correction
   Skip Blank Pages
- Book Scanning
   Job Flow Sheets
- Scan Delivery (optional)
   1: High Compression / Specific Color /
   Searchable Text / Security / Signature /
   Optimise For Quick Web View

\*2: High Compression / Specific Color / Searchable Text / Security / Signature

#### Others

- Local AuthenticationRemote Authentication (optional)
- Microsoft Entra ID\* linked authentication (optional)
- IC Card Log In (optional)
   Serverless Authentication (optional)
- Secondary Ethernet (optional)
  Wi-Fi Support (optional)
- Data Encryption
- Data Overwrite (optional) Image Log (optional)
   Message screen from an administrator
- Job History Export
   \* Formerly Azure Active Directory

Note: More options may need to be added depending on the model.

### fujifilm.com/fbph

## **FUJ!FILM**

#### FUJIFILM Business Innovation Philippines Corp.

25th Floor, SM Aura Tower, 26th St. Corner McKinley Parkway, Taguig City 1630 Philippines Tel. 632-8878-5200

The available model varies depending on the country/region. Please ask the sales representatives for details

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements. Reproduction Prohibitions Please note that reproduction of the following is prohibited by law: \*Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. \*Unused postage stamps, post cards, etc. \*Certificate stamps stipulated by law: \*Peproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, drawings, photographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

family use or other similar uses within a limited circle.

Trademarks •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation.

•Apeos, DocuWorks, Working Folder, Cloud Service Hub, and Cloud On-Demand Print are registered trademarks or trademarks of FUJIFILM Business Innovation Corp.

•Microsoft, Edvice Directory, Azure, Microsoft Entra, Microsoft Edge, Excel, OneDrive, PowerPoint, SharePoint, Microsoft Teams, Windows, and Windows Server are registered trademarks of US Microsoft Corporation in the U.S. and other countries. +Apple, Mac, macOS, OS, KirPint, and Alirpint logo are trademarks of Apple Inc. registered in the U.S. and other countries and regions. •Adobe, Adobe logo, PostScript, and PostScript logo are either registered trademarks or trademarks of Apple in the United States and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. •OR Code is a registered trademarks or DeNSO WAVE HINCORPORATED. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.



#### For Your Safety

Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection Otherwise, electronic shock may result in the case of a failure or short circuit.

<sup>\*1: 70</sup> gsm paper.\*2: When larger size sheets are stacked on top of smaller size sheets.\*3: Width 478 mm when the paper support is stored.