

# ApeosPort C2410SD

A4 Colour Multifunction Printer

## Features



Colour



A4



24 ppm



Copy

Print

Fax

Scan



## High Performance & Productivity

- Compact design fits anywhere in your work space
- Fast colour printing of up to 24 ppm
- Equipped with an Automatic Document Feeder that supports scanning up to 20 ppm for Monochrome/Colour and a 250-sheet tray as standard
- Easy to connect with built-in Wi-Fi, gigabit Ethernet or USB

## Security

- Prevents information leakage with Confidential Print function
- Controls access to the MFPs functions
- Supports settings to delete temporary data files in memory



## Easy Operation

- Intuitive 2.8-inch colour touch panel for easy navigation
- Supports ID Copy function, which allows you to Copy the front and back of ID card onto one side of a single sheet
- Compatible with Mopria® and AirPrint, you can easily print from mobile devices
- Direct print\* from/ scan to a USB flash drive without using a computer

\*PDF/TIFF/JPEG

## Ecology

- Standard two-sided printing saves paper
- Supports ECO mode for easy presetting of features that save paper and toner



## Specifications

| Printing                                      |   |
|---|---|
| Display                                       | 2.8 inch (7.2 cm) LCD touch panel   |
| Print Speed: Up to                            | Black: 24 ppm (A4) / Colour: 24 ppm (A4)  |
| Time to First Page: As fast as                | Black: 10.6 seconds / Colour: 10.6 seconds  |
| Print Resolution                              | Black: 4800 Colour Quality, 600 x 600 dpi / Colour: 600 x 600 dpi, 4800 Colour Quality  |
| Memory  | 512 MB  |
| Hard Disk                                     | Not Available   |
| Copying                                       |   |
| Copy Speed: Up to                             | Black: 24 ppm (A4) / Colour: 24 ppm (A4)  |
| Time to First Copy: As fast as                | Black: 11.8 seconds / Colour: 15.2 seconds  |
| Scanning                                      |   |
| Scanner Type / ADF Scan                       | Flatbed scanner with ADF / Simplex  |
| A4/Ltr Simplex Scan Speed: Up to              | Black: 20 / 21 ppm / Colour: 20 / 21 ppm  |
| ADF Paper Input Capacity: Up to               | 50 pages 75 gsm   |
| Faxing  |   |
| Modem Speed                                   | Max is 33,600 bps, V.34 Half-Duplex Kbps  |
| Supplies                                      |   |
| Print Cartridge Yields up to:                 | 4,500 -page Black High Yield Cartridge / 4,500 -page Colour (CMY) High Yield Cartridge / 1,500 -page Black Cartridge / 1,500 -page Colour (CMY) Cartridges                      |
| Cartridge(s) Shipping with Product            | 750 -page Black Toner Cartridge, 500 -page Colour (CMY) Toner Cartridge   |
| Paper Handling                                |   |
| Included Paper Handling                       | 100-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed, 250-Sheet Input  |
| Paper Input Capacity: Up to                   | 250+1 pages 75 gsm  |
| Paper Output Capacity: Up to                  | 100 pages 75 gsm  |
| Media Types Supported                         | Hagaki Card, Paper Labels, Card Stock, Plain Paper, Envelopes, Glossy Paper   |
| Media Sizes Supported                         | A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Hagaki Card, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope  |
| General Information                           |   |
| Standard Ports                                | Gigabit Ethernet (10/100/1000), Front Hi-Speed USB Port Compatible with USB 2.0 Specification (Type A), 802.11b/g/n Wireless, USB 2.0 Specification Hi-Speed Certified (Type B) |
| Noise Level: Operating                        | Operating: 50 dBA (Print) / 50 dBA (Copy) / 44 dBA (Scan)   |
| Specified Operating Environment <sup>*1</sup> | Humidity: 8 to 80% <sup>*2</sup> Relative Humidity, Temperature: 10 to 32°C <sup>*3</sup> (excluding faults caused by condensation)   |
| Size (mm - H x W x D) / Weight (kg)           | 345 x 412 x 395 mm / 19.4 kg  |

<sup>\*1</sup> : Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. <sup>\*2</sup> : When the humidity is 80%, the temperature is 25.5°C or less. <sup>\*3</sup> : Humidity 45% or less when the temperature is 32°C

## Consumables<sup>\*1</sup>

| Product Name  | Product Code | Product Life       |
|---|--------------|--------------------|
| Black Use & Return Print Cartridge <sup>*2</sup>              | CT351267     | Up to 1,500 pages  |
| Cyan Use & Return Print Cartridge <sup>*2</sup>               | CT351268     | Up to 1,500 pages  |
| Magenta Use & Return Print Cartridge <sup>*2</sup>            | CT351269     | Up to 1,500 pages  |
| Yellow Use & Return Print Cartridge <sup>*2</sup>             | CT351270     | Up to 1,500 pages  |
| Black High Yield Use & Return Print Cartridge <sup>*2</sup>   | CT351263     | Up to 4,500 pages  |
| Cyan High Yield Use & Return Print Cartridge <sup>*2</sup>    | CT351264     | Up to 4,500 pages  |
| Magenta High Yield Use & Return Print Cartridge <sup>*2</sup> | CT351265     | Up to 4,500 pages  |
| Yellow High Yield Use & Return Print Cartridge <sup>*2</sup>  | CT351266     | Up to 4,500 pages  |
| Black High Yield Regular Print Cartridge                      | CT351291     | Up to 4,500 pages  |
| Cyan High Yield Regular Print Cartridge                       | CT351292     | Up to 4,500 pages  |
| Magenta High Yield Regular Print Cartridge                    | CT351293     | Up to 4,500 pages  |
| Yellow High Yield Regular Print Cartridge                     | CT351294     | Up to 4,500 pages  |
| Waste Print Bottle  | CWAA0973     | Up to 15,000 pages |

<sup>\*1</sup> : Average continuous black or continuous composite Colour (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798.

<sup>\*2</sup> : The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

### Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

For more information or detailed product specification, please call or visit us at

### FUJIFILM Business Innovation Philippines Corp.

25th Floor, SM Aura Tower, 26th St. Corner McKinley Parkway, Taguig City 1630 Philippines Tel. 632-8878-5200 [fujifilm.com/fbph](http://fujifilm.com/fbph)

•FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort is registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. •Mopria®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

The information is as of February, 2022. PIC-0194 PH (2111-R1)