

Scan Translation Service Supported Models

Supported Models

Item	Description
Colour Multifunction Device	Apeos C2060 ^{*7}
	Apeos C2560 ^{*7}
	Apeos C3060 ^{*7}
	Apeos C3070 ^{*7}
	Apeos C3570 ^{*7}
	Apeos C4570 ^{*7}
	Apeos C5240 ^{*7}
	Apeos C5570 ^{*7}
	Apeos C6570 ^{*7}
	Apeos C6580 ^{*7}
	Apeos C7070 ^{*7}
	Apeos C7580 ^{*7}
	Apeos C8180 ^{*7}
	ApeosPort C2060
	ApeosPort C2560
	ApeosPort C3060
	ApeosPort C3070
	ApeosPort C3570
	ApeosPort C4570
	ApeosPort C5570
	ApeosPort C6570
	ApeosPort C7070
	ApeosPort-IV C2270 ^{*1}
	ApeosPort-IV C2275
	ApeosPort-IV C3370 ^{*1}
	ApeosPort-IV C3371 ^{*1}
	ApeosPort-IV C3373
	ApeosPort-IV C3375
	ApeosPort-IV C4430 ^{*1} ^{*5}
	ApeosPort-IV C4470 ^{*1}
	ApeosPort-IV C4475
	ApeosPort-IV C5570 ^{*1}
	ApeosPort-IV C5575
	ApeosPort-IV C5580 ^{*1}
	ApeosPort-IV C6680 ^{*1}
	ApeosPort-IV C7780 ^{*1}
	ApeosPort-V C2275 ^{*6}
	ApeosPort-V C2276
	ApeosPort-V C3320
	ApeosPort-V C3373 ^{*6}
	ApeosPort-V C3374

Item	Description
	ApeosPort-V C3375 *6
	ApeosPort-V C3376
	ApeosPort-V C4475 *6
	ApeosPort-V C4476
	ApeosPort-V C5575 *6
	ApeosPort-V C5576
	ApeosPort-V C5580 *6
	ApeosPort-V C5585
	ApeosPort-V C6675 *6
	ApeosPort-V C6676
	ApeosPort-V C6680 *6
	ApeosPort-V C6685
	ApeosPort-V C7775 *6
	ApeosPort-V C7776
	ApeosPort-V C7780 *6
	ApeosPort-V C7785
	ApeosPort-VI C2271
	ApeosPort-VI C3370
	ApeosPort-VI C3371
	ApeosPort-VI C4471
	ApeosPort-VI C5571
	ApeosPort-VI C6671
	ApeosPort-VI C7771
	ApeosPort-VII C2273
	ApeosPort-VII C3321
	ApeosPort-VII C3372
	ApeosPort-VII C3373
	ApeosPort-VII C4421
	ApeosPort-VII C4473
	ApeosPort-VII C5573
	ApeosPort-VII C5588
	ApeosPort-VII C6673
	ApeosPort-VII C6688
	ApeosPort-VII C7773
	ApeosPort-VII C7788
	DocuCentre-IV C2263 *2 *4
	DocuCentre-IV C2263 N
	DocuCentre-IV C2265 *2 *4
	DocuCentre-IV C2265 N
	DocuCentre-IV C2275 *2 *5
	DocuCentre-IV C3373 *2 *5
	DocuCentre-IV C3375 *2 *5
	DocuCentre-IV C4475 *2 *5
	DocuCentre-IV C5575 *2 *5
	DocuCentre-V C2263 *2 *5

Item	Description
	DocuCentre-V C2265 *2 *5
	DocuCentre-V C2275 *2 *5 *6
	DocuCentre-V C2276 *2 *5
	DocuCentre-V C3373 *2 *5 *6
	DocuCentre-V C3374 *2 *5
	DocuCentre-V C3375 *2 *5 *6
	DocuCentre-V C3376 *2 *5
	DocuCentre-V C4475 *2 *5 *6
	DocuCentre-V C4476 *2 *5
	DocuCentre-V C5575 *2 *5 *6
	DocuCentre-V C5576 *2 *5
	DocuCentre-V C5580 *6
	DocuCentre-V C5585
	DocuCentre-V C6675 *2 *5 *6
	DocuCentre-V C6676 *2 *5
	DocuCentre-V C6680 *6
	DocuCentre-V C6685
	DocuCentre-V C7775 *2 *5 *6
	DocuCentre-V C7776 *2 *5
	DocuCentre-V C7780 *6
	DocuCentre-V C7785
	DocuCentre-VI C2271 *2
	DocuCentre-VI C3370 *2
	DocuCentre-VI C3371 *2
	DocuCentre-VI C4471 *2
	DocuCentre-VI C5571 *2
	DocuCentre-VI C6671 *2
	DocuCentre-VI C7771 *2
	DocuCentre-VII C2273 *2
	DocuCentre-VII C3372 *2
	DocuCentre-VII C3373 *2
	DocuCentre-VII C4473 *2
	DocuCentre-VII C5573 *2
	DocuCentre-VII C5588
	DocuCentre-VII C6673 *2
	DocuCentre-VII C6688
	DocuCentre-VII C7773 *2
	DocuCentre-VII C7788
Monochrome Multifunction Device	Apeos 2560 *7
	Apeos 3060 *7
	Apeos 3560 *7
	Apeos 4570 *7
	Apeos 5570 *7
	Apeos 6340 *7

Item	Description
	ApeosPort 2560 *7 ApeosPort 3060 *7 ApeosPort 3560 *7 ApeosPort 4570 *7 ApeosPort 5570 *7 ApeosPort-IV 2060 *1 ApeosPort-IV 3060 *1 ApeosPort-IV 3065 *1 ApeosPort-IV 3070 *1 ApeosPort-IV 4070 *1 ApeosPort-IV 5070 *1 ApeosPort-IV 6080 ApeosPort-IV 7080 ApeosPort-V 2060 ApeosPort-V 3060 ApeosPort-V 3065 ApeosPort-V 4020 ApeosPort-V 4070 ApeosPort-V 5070 ApeosPort-V 6080 ApeosPort-V 7080 ApeosPort-VII 4021 ApeosPort-VII 5021 DocuCentre-IV 6080 *2 *3 DocuCentre-IV 7080 *2 *3 DocuCentre-V 2060 *2 *3 *5 DocuCentre-V 3060 *2 *3 *5 DocuCentre-V 3065 *2 *3 *5 DocuCentre-V 4070 *2 DocuCentre-V 5070 *2 DocuCentre-V 6080 *2 DocuCentre-V 7080 *2
Printer	DocuPrint CM415 AP DocuPrint M465 AP
Production	ApeosPro C650 *7 ApeosPro C750 *7 ApeosPro C810 *7 Color C60 Printer Color C70 Printer PrimeLink C9065 Printer PrimeLink C9070 Printer

Note: Products for sale may differ according to country or region. For more information, please contact the FUJIFILM Business Innovation office or authorized dealers in each country/region.

*1: External Access Kit is required.

- *2: Scanner Kit is required.
- *3: Printer Kit is required.
- *4: Extension System Memory (2 GB) is required.
- *5: Built in HDD is required.
- *6: Extensible Customization Kit is required to use MFD Single Sign-on function. Later model (T2) is not required.
- *7: Scan Translation Service Linkage must be installed.