

# ApeosPort® C2410SD

A4 Colour Multifunction Printer

## Features



Colour



24 ppm



Copy

Print

Fax

Scan



## High Performance & Productivity

- Compact design fits anywhere in your work space
- Fast colour printing of up to 24 ppm
- Equipped with an Automatic Document Feeder that supports scanning up to 20 ppm for Monochrome/Colour and a 250-sheet tray as standard
- Easy to connect with built-in Wi-Fi, gigabit Ethernet or USB

## Easy Operation

- Intuitive 2.8-inch colour touch panel for easy navigation
- Supports ID Copy function, which allows you to Copy the front and back of ID card onto one side of a single sheet
- Compatible with Mopria® and AirPrint, you can easily print from mobile devices
- Direct print\* from/ scan to a USB flash drive without using a computer



\*PDF/TIFF/JPEG

## Security

- Prevents information leakage with Confidential Print function
- Controls access to the MFPs functions
- Supports settings to delete temporary data files in memory

## Ecology

- Standard two-sided printing saves paper
- Supports ECO mode for easy presetting of features that save paper and toner



# Specifications

Printing	
Display	2.8 inch (7.2 cm) LCD touch panel
Print Speed: Up to	Black: 24 ppm (A4) / Colour: 24 ppm (A4)
Time to First Page: As fast as <sup>*1</sup>	Black: 10.6 seconds / Colour: 10.6 seconds
Print Resolution	Black: 4800 Colour Quality, 600 x 600 dpi / Colour: 600 x 600 dpi, 4800 Colour Quality
Memory	512 MB
Hard Disk	Not Available
Copying	
Copy Speed: Up to	Black: 24 ppm (A4) / Colour: 24 ppm (A4)
Time to First Copy: As fast as <sup>*2</sup>	Black: 11.8 seconds / Colour: 15.2 seconds
Scanning	
Scanner Type / ADF Scan	Flatbed scanner with ADF / Simplex
A4/Ltr Simplex Scan Speed: Up to	Black: 20 / 21 ppm / Colour: 20 / 21 ppm
ADF Paper Input Capacity: Up to	50 pages 75 gsm
Faxing	
Modem Speed	Max is 33,600 bps, V.34 Half-Duplex Kbps
Supplies	
Print Cartridge Yields up to:	4,500 -page Black High Yield Cartridge / 4,500 -page Colour (CMY) High Yield Cartridge / 1,500 -page Black Cartridge / 1,500 -page Colour (CMY) Cartridges
Cartridge(s) Shipping with Product	750 -page Black Toner Cartridge, 500 -page Colour (CMY) Toner Cartridge
Paper Handling	
Included Paper Handling	100-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed, 250-Sheet Input
Paper Input Capacity: Up to	250+1 pages 75 gsm
Paper Output Capacity: Up to	100 pages 75 gsm
Media Types Supported	Hagaki Card, Paper Labels, Card Stock, Plain Paper, Envelopes, Glossy Paper
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Hagaki Card, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope
General Information	
Standard Ports	Gigabit Ethernet (10/100/1000), Front Hi-Speed USB Port Compatible with USB 2.0 Specification (Type A), 802.11b/g/n Wireless, USB 2.0 Specification Hi-Speed Certified (Type B)
Noise Level: Operating	Operating: 50 dBA (Print) / 50 dBA (Copy) / 44 dBA (Scan)
Specified Operating Environment <sup>*3</sup>	Humidity: 8 to 80% <sup>*4</sup> Relative Humidity, Temperature: 10 to 32°C <sup>*5</sup> (excluding faults caused by condensation)
Size (mm - H x W x D) / Weight (kg)	345 x 412 x 395 mm / 19.4 kg

\*1: The time from when the device starts the print job from standard sheet tray until the trailing edge of the first page exits into output tray. Numeric value may vary based on the output environment. \*2: Numeric value varies depending on the output environment. \*3: Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. \*4: When the humidity is 80%, the temperature is 25.5°C or less. \*5: Humidity 45% or less when the temperature is 32°C.

## Consumables<sup>\*1</sup>

Product Name	Product Code	Product Life
Black Use & Return Print Cartridge <sup>*2</sup>	CT351267	Up to 1,500 pages
Cyan Use & Return Print Cartridge <sup>*2</sup>	CT351268	Up to 1,500 pages
Magenta Use & Return Print Cartridge <sup>*2</sup>	CT351269	Up to 1,500 pages
Yellow Use & Return Print Cartridge <sup>*2</sup>	CT351270	Up to 1,500 pages
Black High Yield Use & Return Print Cartridge <sup>*2</sup>	CT351263	Up to 4,500 pages
Cyan High Yield Use & Return Print Cartridge <sup>*2</sup>	CT351264	Up to 4,500 pages
Magenta High Yield Use & Return Print Cartridge <sup>*2</sup>	CT351265	Up to 4,500 pages
Yellow High Yield Use & Return Print Cartridge <sup>*2</sup>	CT351266	Up to 4,500 pages
Black High Yield Regular Print Cartridge	CT351291	Up to 4,500 pages
Cyan High Yield Regular Print Cartridge	CT351292	Up to 4,500 pages
Magenta High Yield Regular Print Cartridge	CT351293	Up to 4,500 pages
Yellow High Yield Regular Print Cartridge	CT351294	Up to 4,500 pages
Waste Print Bottle	CWAA0973	Up to 15,000 pages

\*1: Average continuous black or continuous composite Colour (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798.

\*2: The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

### Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

For more information or detailed product specification, please call or visit us at

**FUJIFILM Business Innovation (Thailand) Co., Ltd.**

123 Sun Towers A Building, 23rd-26th Floor, Vibhavadi-Rangsit Road, Chomphon, Chatuchak, Bangkok 10900 Call Center: 02-660-8400

[fujifilm.com/fbth](http://fujifilm.com/fbth)

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements

•FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort is registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. •Mopria®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

The information is as of April, 2023.

PIC-0194 TH (2111-R2)