

ApeosPort[®] C3830SD

เครื่องมัลติฟังก์ชันสีขนาด A4

คุณสมบัติ



Colour



A4



38 หน้า/นาที



อุปกรณ์เสริม



ทำสำเนา

พิมพ์

แฟกซ์

สแกน



เครื่องพิมพ์ที่ให้งานประสิทธิภาพและความเร็วสูง

- พิมพ์ความเร็วสูงที่ 38 หน้า/นาที ใช้พื้นที่ติดตั้งน้อย
- ชุดป้อนเอกสารสองหน้าอัตโนมัติที่สแกน 2 ด้านพร้อมกันในครั้งเดียวช่วยรองรับการสแกนความเร็วสูงได้ถึง 94 แผ่นสำหรับขาว-ดำ และ 60 แผ่นสำหรับการสแกนสี
- ถาดกระดาษคู่ 650 แผ่นที่เป็นอุปกรณ์เสริมซึ่งประกอบด้วยถาดป้อนกระดาษเอนกประสงค์ 100 แผ่น และถาดกระดาษ 550 แผ่นจะช่วยรองรับการป้อนกระดาษความสูงได้ถึง 1,451 แผ่น
- ระบบเครือข่ายที่ยืดหยุ่น การใช้งานกิกะบิตอีเทอร์เน็ตจะช่วยเพิ่มความเร็วในการสื่อสารระหว่างเครือข่ายและเครื่องพิมพ์ รวมทั้งชุด Wi-Fi อุปกรณ์เสริมที่ช่วยให้การเชื่อมต่อแบบไร้สายง่ายขึ้น

ความปลอดภัย

- ป้องกันข้อมูลรั่วไหลด้วยฟังก์ชันการพิมพ์แบบปลอดภัยสำหรับข้อมูลที่เป็นความลับ
- ควบคุมการเข้าใช้ฟังก์ชันต่างๆ ภายในเครื่องมัลติฟังก์ชัน
- รองรับการยืนยันตัวตนด้วย IC Card* คุณสามารถระบุตัวตนได้อย่างง่ายดายโดยไม่ต้องใส่ชื่อและรหัสผู้ใช้ *อุปกรณ์เสริม
- มีตัวเลือกเสริมที่รองรับการตั้งค่าในการลบไฟล์ข้อมูลชั่วคราวออกจากหน่วยความจำและฮาร์ดดิสก์ได้

ใช้งานง่าย

- หน้าจอสัมผัสขนาด 4.3 นิ้วที่ช่วยให้ใช้งานง่าย เหมือนใช้แท็บเล็ต
- รองรับแอปพลิเคชันแบบกำหนดเองต่างๆ เช่น การทำสำเนาบัตร และ ศูนย์กลางการสแกน ช่วยเพิ่มความยืดหยุ่นและขยายฟังก์ชันการใช้งานได้มากขึ้น
- ใช้งานร่วมกับ Mopria® และ AirPrint คุณสามารถพิมพ์งานจากอุปกรณ์เคลื่อนที่ได้อย่างง่ายดาย
- พิมพ์โดยตรง* จาก / สแกนไปยังหน่วยความจำ USB โดยไม่ต้องใช้เครื่องคอมพิวเตอร์ *PDF/TIFF/JPEG

ประหยัด

- ช่วยประหยัดการใช้กระดาษด้วยการพิมพ์ 2 ด้านมาตรฐาน
- รองรับโหมด ECO ที่สามารถตั้งค่าคุณสมบัติต่างๆ ไร้ลังงานได้อย่างง่ายดาย ช่วยประหยัดทั้งกระดาษและผงหมึก

ชุดป้อนเอกสารสองหน้าอัตโนมัติ (สแกน 2 ด้านพร้อมกันในครั้งเดียว)

หน้าจอสัมผัสขนาด 4.3 นิ้ว



ถาดรับกระดาษ (150 แผ่น)

พอร์ต USB

ถาดกระดาษมาตรฐาน 250 แผ่น

ถาด Bypass (1 แผ่น)


อุปกรณ์เสริม

ถาดกระดาษคู่ 650 แผ่น

ถาดป้อนกระดาษ 550 แผ่น และ ถาดป้อนกระดาษเอนกประสงค์ 100 แผ่น

อุปกรณ์เสริม

ถาดกระดาษ 550 แผ่น



Specifications

Printing	
Display	4.3-inch (10.9 cm) Colour touch screen
Print Speed: Up to	Black: 38 ppm (A4) / Colour: 38 ppm (A4)
Time to First Page: As fast as ^{*1}	Black: 8 seconds / Colour: 8 seconds
Print Resolution	Black: 1200 x 1200 dpi, 4800 Colour Quality (2400 x 600 dpi) / Colour: 1200 x 1200 dpi, 4800 Colour Quality (2400 x 600 dpi)
Memory	2048 MB
Hard Disk	Option available
Copying	
Copy Speed: Up to	Black: 38 ppm (A4) / Colour: 38 ppm (A4)
Time to First Copy: As fast as ^{*2}	Black: 7.9 seconds / Colour: 12.3 seconds
Scanning	
Scanner Type / ADF Scan	Flatbed scanner with ADF / DADF (single pass Duplex)
A4/Ltr Duplex Scan Speed: Up to	Black: 94 / 100 ppm / Colour: 60 / 64 ppm
A4/Ltr Simplex Scan Speed: Up to	Black: 47 / 50 ppm / Colour: 30 / 32 ppm
ADF Paper Input Capacity: Up to	100 pages 75 gsm
Faxing	
Modem Speed	Max is 33,600 bps, V.34 Half-Duplex Kbps
Supplies	
Toner Cartridge Yields (up to)	7,000-page Colour (CMY) Ultra High Yield Cartridges, 10,500-page Black Ultra High Yield Cartridge
Imaging Kit Estimated Yield: Up to	125,000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage
Cartridge(s) Shipping with Product	2,000-page Colour (CMY) Toner Cartridges, 3,000-page Black Toner Cartridge
Paper Handling	
Included Paper Handling	250-Sheet Input, 150-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed
Optional Paper Handling	550-Sheet Tray, 650-Sheet Duo Tray
Paper Input Capacity: Up to	Standard: 250+1 pages 75 gsm / Maximum: 1450+1 pages 75 gsm
Paper Output Capacity: Up to	150 pages 75 gsm
Media Types Supported	Card Stock, Paper Labels, Plain Paper, Vinyl Labels
Media Sizes Supported	10 Envelope, 7 3/4 Envelope, 9 Envelope, A4, A5, B5 Envelope, C5 Envelope, DL Envelope, Hagaki Card, Executive, Folio, JIS-B5, Legal, Letter, Statement, Universal, Oficio, A6
General Information	
Standard Ports	USB 2.0 Specification Hi-Speed Certified (Type B), Gigabit Ethernet (10/100/1000), Front USB 2.0 Specification Hi-Speed Certified port (Type A), Rear USB 2.0 Specification Hi-Speed Certified Port (Type A)
Wi-Fi	Option available (802.11 a/b/g/n/ac Wireless)
Noise Level: Operating	Print: 52 dBA / Copy: 55 dBA / Scan: 51 dBA
Specified Operating Environment ^{*3}	Humidity: 8 to 80% ^{*4} Relative Humidity, Temperature: 10 to 32°C ^{*5} (excluding faults caused by condensation)
Size (mm - H x W x D) / Weight (kg)	462 x 442 x 588 mm / 27.1 kg

*1: The time from when the device starts the print job from standard sheet tray until the trailing edge of the first page exits into output tray. Numeric value may vary based on the output environment. *2: Numeric value varies depending on the output environment. *3: Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. *4: When the humidity is 80%, the temperature is 25.5°C or less. *5: Humidity 45% or less when the temperature is 32°C.

Options

Product Name	Product Code
550-Sheet Tray	EC104314
650-Sheet Duo Tray	EC104316
Wireless Print Server	EC104320
500 GB Hard Disk	EC104326
Contactless Authentication Device	EC104333

Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

Consumables^{*1}

Product Name	Product Code	Product Life
Black Ultra High Yield Use & Return Toner Cartridge ^{*2}	CT203466	Up to 10,500 pages
Cyan Ultra High Yield Use & Return Toner Cartridge ^{*2}	CT203467	Up to 7,000 pages
Magenta Ultra High Yield Use & Return Toner Cartridge ^{*2}	CT203468	Up to 7,000 pages
Yellow Ultra High Yield Use & Return Toner Cartridge ^{*2}	CT203469	Up to 7,000 pages
Black Ultra High Yield Regular Toner Cartridge	CT203512	Up to 10,500 pages
Cyan Regular Toner Cartridge	CT203513	Up to 7,000 pages
Magenta Regular Toner Cartridge	CT203514	Up to 7,000 pages
Yellow Regular Toner Cartridge	CT203515	Up to 7,000 pages
Black Use and Return Imaging Kit ^{*2}	CT300294	Up to 125,000 pages
Black and Color Use and Return Imaging Kit ^{*2}	CT300295	Up to 125,000 pages
Black Regular Imaging Kit	CT300298	Up to 125,000 pages
Black and Color Regular Imaging Kit	CT300299	Up to 125,000 pages
Waste Toner Bottle	CVAA0972	Up to 25,000 pages

*1: Average continuous black or continuous composite Colour (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798.

*2: The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

บริษัท ฟุจิฟิล์ม บิสซิเนส อินโนเวชัน (ประเทศไทย) จำกัด

123 อาคารชั้นทาวเวอร์ เอ ชั้น 23-26 ถนนวิภาวดีรังสิต จอมพล จตุจักร กรุงเทพฯ 10900
โทร: 02-660-8000 แฟกซ์: 02-617-6748-9 Call Center: 02-660-8400

fujifilm.com/fbth

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

•FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort is registered trademarks of FUJIFILM Business Innovation Corp. •Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. •Mopria®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

The information is as of April, 2023.

PIC-0192 TH (2111-R1)