

ApeosPort[®] Print C2410SD

เครื่องพิมพ์สีขนาด A4

คุณสมบัติ



24 หน้า/นาที



เครื่องพิมพ์ที่ให้งานประสิทธิภาพและความเร็วสูง

- ดีไซน์เล็กกระทัดรัดที่เหมาะกับทุกพื้นที่ในออฟฟิศคุณ
- พิมพ์สีด้วยความเร็วสูงถึง 24 หน้า/นาที และใช้เวลาในการทำสำเนาแผ่นแรกเพียง 10.9 วินาที
- การใช้งานกระดาษที่ยืดหยุ่นสามารถรองรับได้ทั้งกระดาษการ์ด กระดาษขนาดเล็ก และซองจดหมาย
- เชื่อมต่อกับ Wi-Fi ในตัว, กิกะบิตอีเทอร์เน็ต หรือ USB ได้อย่างง่ายดาย

ความปลอดภัย

- ป้องกันข้อมูลรั่วไหลด้วยฟังก์ชันการพิมพ์แบบปลอดภัยสำหรับข้อมูลที่เป็นความลับ
- ควบคุมการเข้าใช้ฟังก์ชันต่างๆ ภายในเครื่องพิมพ์
- รองรับการตั้งค่าที่สามารถลบไฟล์ข้อมูลชั่วคราวออกจากหน่วยความจำได้


ใช้งานง่าย

- หน้าจอแสดงผลแบบสองบรรทัด ช่วยให้ติดตั้งค่าและตรวจสอบข้อมูลที่สำคัญของระบบได้อย่างสะดวกและง่ายดาย
- ใช้งานร่วมกับ Mopria® และ AirPrint คุณจึงสามารถพิมพ์งานจากอุปกรณ์เคลื่อนที่ได้อย่างง่ายดาย

ประหยัด

- ช่วยประหยัดการใช้กระดาษด้วยการพิมพ์ 2 ด้านมาตรฐาน
- รองรับโหมด ECO ที่สามารถตั้งค่าคุณสมบัติต่างๆ ไว้ล่วงหน้าได้อย่างง่ายดาย ช่วยประหยัดทั้งกระดาษและหมึก

หน้าจอ LCD ขาว-ดำ สองบรรทัด



Specifications

Printing	
Display	2-line All Points Addressable (APA) monochrome LCD display
Print Speed: Up to	Black: 24 ppm (A4) / Colour: 24 ppm (A4)
Time to First Page: As fast as* ¹	Black: 10.9 seconds / Colour: 10.9 seconds
Print Resolution	Black: 4800 Colour Quality, 600 x 600 dpi / Colour: 600 x 600 dpi, 4800 Colour Quality
Memory	512 MB
Hard Disk	Not Available
Supplies	
Print Cartridge Yields (up to)	4,500 -page Black High Yield Cartridge / 4,500 -page Colour (CMY) High Yield Cartridges / 1,500 -page Black Cartridge / 1,500 -page Colour (CMY) Cartridges
Cartridge(s) Shipping with Product	750 -page Black Toner Cartridge, 500 -page Colour (CMY) Toner Cartridge
Paper Handling	
Included Paper Handling	100-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed, 250-Sheet Input
Paper Input Capacity: Up to	250+1 pages 75 gsm
Paper Output Capacity: Up to	100 pages 75 gsm
Media Types Supported	Paper Labels, Card Stock, Plain Paper, Envelopes, Glossy Paper
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Hagaki Card, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope
General Information	
Standard Ports	802.11b/g/n Wireless, USB 2.0 Specification Hi-Speed Certified (Type B), Ethernet 10/100/1000 BaseTX (RJ-45)
Noise Level: Operating	Operating: 52 dBA (Print)
Specified Operating Environment* ²	Humidity: 8 to 80%* ³ Relative Humidity, Temperature: 10 to 32°C* ⁴ (excluding faults caused by condensation)
Size (mm - H x W x D) / Weight (kg)	244 x 412 x 395 mm / 16.1 kg

*1: The time from when the device starts the print job from standard sheet tray until the trailing edge of the first page exits into output tray. Numeric value may vary based on the output environment. *2: Depending on the paper used, the print quality may be degraded until the temperature and humidity environment just before use and the inside of the printer fit into the installation environment. *3: When the humidity is 80%, the temperature is 25.5°C or less. *4: Humidity 45% or less when the temperature is 32°C

Consumables*¹

Product Name	Product Code	Product Life
Black Use & Return Print Cartridge* ²	CT351267	Up to 1,500 pages
Cyan Use & Return Print Cartridge* ²	CT351268	Up to 1,500 pages
Magenta Use & Return Print Cartridge* ²	CT351269	Up to 1,500 pages
Yellow Use & Return Print Cartridge* ²	CT351270	Up to 1,500 pages
Black High Yield Use & Return Print Cartridge* ²	CT351263	Up to 4,500 pages
Cyan High Yield Use & Return Print Cartridge* ²	CT351264	Up to 4,500 pages
Magenta High Yield Use & Return Print Cartridge* ²	CT351265	Up to 4,500 pages
Yellow High Yield Use & Return Print Cartridge* ²	CT351266	Up to 4,500 pages
Black High Yield Regular Print Cartridge	CT351291	Up to 4,500 pages
Cyan High Yield Regular Print Cartridge	CT351292	Up to 4,500 pages
Magenta High Yield Regular Print Cartridge	CT351293	Up to 4,500 pages
Yellow High Yield Regular Print Cartridge	CT351294	Up to 4,500 pages
Waste Print Bottle	CWAA0973	Up to 15,000 pages

*1: Average continuous black or continuous composite Colour (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798.

*2: The Use and Return consumables are sold with at a special price contingent upon customer's agreement to use them only once and return them to us for remanufacturing or recycling. For details, please refer to our website.

Notes

Although Use and Return consumables are initially installed, consumables without the single-use term, which may be refilled or remanufactured by you or a third party, are available. For details, please refer to our website.

บริษัท ฟุจิฟิล์ม บิสซิเนส อินโนเวชัน (ประเทศไทย) จำกัด
 123 อาคารชั้นทาวเวอร์ เอ ชั้น 23-26 ถนนวิภาวดีรังสิต จอมพล จตุจักร กรุงเทพฯ 10900
 โทร: 02-660-8000 แฟกซ์: 02-617-6748-9 Call Center: 02-660-8400

fujifilm.com/fbth

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements. •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPort is registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Apple, AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries. •Mopria®, the Mopria® Logo, and the Mopria Alliance™ word mark and logo are registered and/or unregistered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

The information is as of April, 2023.

PIC-0200 TH (2111-R1)