



## ApeosPrint C4030

A4 Colour Printer Catering to your everyday business needs



## **FUJIFILM Business Innovation Corp.**

# New Times, New Apeos

The new "Apeos" offers advanced features with high security level and easy operability to help business diversify with times.

"Apeos" devices are able to connect smoothly with a variety of solutions and services to realise an all new agile remote workstyle of working anytime, anywhere.

Colour / A4 40 ppm USB, Ethernet, Wi-Fi\* connectivity \*Optional

#### Superb printing quality

- Print resolution up to 1,200 x 2,400 dpi
  Super EA-Eco toner for fine text and fine
- lines

  Rich colour expression with LED
- printhead and IReCT\*
- \* Image Registration Control Technology

#### Fast printing speed

- Print up to 40 ppm on A4 size
- Automatic 2-sided printing
- High reliability with robust design for 300,000-pages machine life.

#### ECO support

Toner save function in increments of 1%

FULKEILM

 Super EA-Eco toner: Fusing achieved at a low temperature contributes to low power consumption

### Flexible. Secure. Reliable

Offices can easily use different FUJIFILM devices thanks to shared functions across the lineup.

## Supporting Universal Print by Microsoft\*1

By registering ApeosPrint C4030 to Universal Print by Microsoft in advance, users<sup>\*2</sup> authenticated with Azure AD can print from anywhere through cloud.

\*1: Optional Storage (SSD) is required.

\*2: Organizations with Microsoft Windows Enterprise or Microsoft 365 subscriptions

## Print out from any printer within the office

With Server-less On-Demand Print\*, you have the flexibility to print and collect the print outs from any of the connected printer.

- Improves productivity by printing from another available device when the current device is in use
- Up to 100 devices can be linked
   \* Optional

#### Safeguard important information

- Prevents paper information leakage with Secure Print and Private Charge Print with IC card authentication\*. With Image Log\*, job logs and the image itself can be stored and managed, enabling prompt investigation upon information leakage.
- Newly support WPA3 as latest wireless LAN security protocol and adopt TPM (Trusted Platform Module) 2.0, as a security chip that conforms to the latest standards with enhanced encryption
- Detects tampering of device software and self-repairing feature protects and repairs device software against tampering events
- Provides more robust and secured office environment with enhanced security feature of both hardware and software
- \* Optional

#### Reliable support system

From consumables replacement to unexpected device failures, most problems can be resolved without waiting for the service or sales representatives.

- Resolve problem using the "Help" function on the device
- "Remote Assistance" with the help of operators



### ApeosPrint C4030, catering to your everyday business printing needs

#### User-friendly colour touch panel

- Home screen personalisation for ease of access to commonly used functions
- When using Private Charge Print, you can easily select and delete the documents viewing the thumbnails\* shown on the panel.



\* Optional Storage (SSD) is required for thumbnail view.

Smart & scalable

#### Quick printing from your mobile device and USB flash drive

- You can print photos and documents (DocuWorks/PDF) stored in your iOS or Android mobile device.
- Connect to Machine via Wireless Environment or Wi-Fi Direct Connection\*



Print from mobile devices

- You can easily print from mobile devices using Print Utility, AirPrint, and Mopria® Print Service.
- You can directly print the documents stored on a USB flash drive for efficient operations\*

\* Optional

#### ApeosPrint C4030 can be installed just the way you like. As a desktop device, under a counter, or a console central printer.





#### From printing on envelopes and thick paper to producing promotional materials

- Automatic adjustment of pressure to print envelopes
- A smooth paper feed path so that thick paper can run stably
- Supports long paper up to 215.9 x 520 mm\*

```
* Long Papers are fed from Bypass Tray.
```

#### 1. 5-inch colour touch panel:

Intuitive colour touch panel lets you find just what you want at a glance

- 2. USB port\*: Use your own USB flash drive to print directly
- 3. Output tray: Capacity is 250 sheets
- 4. Bypass Tray (150 sheets): Supports various paper types such as envelopes and postcards
- 5. Standard Tray (550 sheets): For standard users. Supports various types & sizes of paper
- 6. 550-Sheet Feeder\* (550 sheets): Paper feeding capacity is 2,350 sheets at maximum. High scalability for high-volume printing needs

8

7. Caster\*:

For easy installation and moving on the floor

- 8. Cabinet\*: Convenient for storing paper and consumables
- 9. IC Card Reader\*: You can use Private Charge Print with your IC card

\* Optional



### ApeosPrint C4030 Functions & Specifications

Items Printing Mathed		Description LED Electrophotography		
Printing Method		38 seconds or less (23 degrees Celsius room temperature).		
Warm-up Time		20 seconds or less from Sleep Mode.		
Continuous Simplex		Colour: 40 ppm, B/W: 40 ppm		
Print Speed*1		Colour: 26.9 ppm, B/W: 26.9 ppm		
First Print Output Time* <sup>2</sup>		Colour: 5.3 seconds (A4), B/W: 5.1 seconds (A4)		
Printing Resolution	Standard	[PCL Driver] Standard: 1,200 x 2,400 dpi, High Quality: 1,200 x 2,400 dpi, High Resolution: 1,200 x 1,200 dpi		
	Optional	[Adobe® PostScript® 3 <sup>™</sup> Driver] High Speed (Standard): 600 x 600 dpi, High Quality: 1,200 x 2,400 dpi, High Resolution: 1,200 x 1,200 dpi		
Paper Size	Standard Tray	A6 <sup>*3</sup> , JIS B6 <sup>*3</sup> , A5, JIS B5, ISO B5, A4, Statement (139.7 x 215.9 mm), Executive (184 x 267 mm), Letter, 8.5 x 13" (215.9 x 330.2 mm), Legal, Custom Size (Width: 76.2 to 215.9 mm, Length <sup>*4</sup> : 190.5 to 355.6 mm)		
	Bypass Tray	A6, JIS B6, A5, JIS B5, ISO B5, A4, Statement (139.7 x 215.9 mm), Executive (184 x 267 mm), Letter, 8.5 x 13" (215.9 x 330.2 mm), Legal, COM-10, Monarch, DL, C5, Custom Size (Width: 64 to 215.9 mm, Length: 127 to 520 mm)		
	Optional Tray	550-Sheet Feeder: A5, JIS B5, ISO B5, A4, Statement (139.7 x 215.9 mm), Executive (184 x 267 mm), Letter, 8.5 x 13" (215.9 x 330.2 mm), Legal, Custom Size (Width: 76.2 to 215.9 mm, Length: 190.5 to 355.6 mm)		
	2 Sided Printing	A4, JIS B5, A5, Letter, 8.5 x 13" (215.9 x 330.2 mm), Legal, Executive (184 x 267 mm) , Custom Size (Width: 139.7 to 215.9 mm, Length: 203.2 to 355.6 mm)		
	Standard Tray	60 to 220 gsm		
Paper	Bypass Tray	60 to 220 gsm		
Weight*5	Optional Tray	550-Sheet Feeder: 60 to 220 gsm		
	2 Sided Printing	60 to 176 gsm		
Paper Tray Capacity*6	Standard	Standard Tray: 550 sheets, Bypass Tray: 150 sheets		
	Optional	550-Sheet Feeder: 550 sheets		
	Max	2,350 sheets [Standard + 550-Sheet Feeder x 3]		
Output Tray Capacity*6		250 sheets		
CPU		ARM Dual Core 1.3 GHz		
Memory Capacity		4 GB (Max: 4 GB)		
Storage Device	e Capacity*7	3.6 GB, Optional: 82 GB*8		
Page Description	Standard	PCL5 / PCL6		
Language	Optional	Adobe® PostScript® 3™		
Supported Operating System*9	Standard	[PCL Driver] Windows 11 (64 bit), Windows 10 (32 bit / 64 bit), Windows Server 2022 (64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit), Windows Server 2012 R2 (64 bit), Windows Server 2012 (64 bit) [Mac OS X Driver] macOS 12 / 11 / 10.15 / 10.14		
	Optional	[Adobe® PostScript® 3 <sup>™</sup> Driver] Windows 11 (64 bit), Windows 10 (32 bit / 64 bit), Windows Server 2022 (64bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit), Windows Server 2012 R2 (64 bit), Windows Server 2012 (64 bit) macOS 12 / 11 / 10.15 / 10.14		
Interface	Standard Optional	Ethernet 1000BASE-T / 100BASE-TX / 10BASE-T, USB3.0 Wireless LAN (IEEE 802.11a / b / g / n / ac)		
Network Proto		TCP/IP (Ipd, IPP, Port9100)		
Power Supply <sup>*10</sup>		AC220-240 V +/- 10 %, 8 A, 50/60 Hz common		
Operating Noise*11*12		In Operation: 6.9 B. 52.9 dB (A)		
,		Ready Mode: 4.8 B, 32.8 dB (A)		
Maximum Power Consumption	Max Average	1,260 W (AC220 V +/- 10 %), 1,430 W (AC240 V +/- 10 %) Ready Mode: 72 W (AC230 V) In Operation: 665 W (AC230 V) Sleep Mode: 0.4 W (AC230 V)		
		W 427.4 x D 465.5 x H 407.5 mm		
Dimensions				

Note: Custom Paper Size setting may be required depending on the paper size. \*1: When Continuously Printing Original in A4 (Plain). The performance may be reduced depending on the paper type and the paper size. The speed may be reduced due to the intervent enductment of the paper size.

the image quality adjustment. \*2: When feeding from feeder tray of machine. Numeric value varies depending on output environment

\*3: When using A6 / JIS B6 paper with the Standard Tray, the optional A5 LEF / A6 Tray Guide is required.

### fujifilm.com/fbth

## **FUJ!FILM**

#### FUJIFILM Business Innovation (Thailand) Co., Ltd.

123 Suntowers A Building, 23rd-26th Floor, Vibhavadi-Rangsit Road, Chomphon, Chatuchak, Bangkok 10900 Tel: 02-660-8000 Fax: 02-617-6748-9 Call Center: 02-660-8400

### บริษัท ฟูจิฟิล์ม บิสซิเนส อินโนเวชั่น (ประเทศไทย) จำกัด

123 อาคาร์ซันทาวเวอร์ เอ ชั้น 23-26 ถนนวิภาวดีรังสิต จอมพล จตุจักร กรุงเทพฯ 10900 โทร: 02-660-8000 แฟกซ์: 02-617-6748-9 Call Center: 02-660-8400

\*4: When the optional A5 LEF / A6 Tray Guide is attached, the length is 148 to 190.5 mm.
\*5: It is recommended to use our recommended paper. Correct print output may not be possible depending on the requirement.
\*6: 80 gsm paper.
\*7: The Storage Device Capacity is not totally available for customers.
\*8: When the optional Storage (SSD) is installed.
\*9: Please refer to our official website for the latest supported OS.
\*10: Power outbut that provide the above power level is recommended Maximum.

- \*10: Power outlets that provide the above power level is recommended. Maximum machine measured current: 8 A.
   \*11: Measured in accordance to ISO7779. Unit B: Sound Power Level LWAd. Unit dB:

Radiated Sound Pressure Level LpAm (bystander position), as reference value. \*12: Main unit only.

#### Options

options			
Product Name	Product Code	Product Name	Product Code
550-Sheet Feeder	EC104521	Multi-Language Font Kit	EC104208
Caster	EC104525	USB Memory Kit	EL300976
Cabinet	EC104526	Security Expansion Kit	EL300980
A5 LEF / A6 Tray Guide	EC104520	Remote Authentication Kit	EL300999
Wireless Network Kit 2	EC104218	Data Overwrite Kit	EC104531
Storage (SSD)	EL300984	TC/SC Additional Font ROM Kit	EL300982
External Access Kit	EL300978	Embedded IC Card Reader B	EC104697
Adobe <sup>®</sup> PostScript <sup>®</sup> 3™ Kit	EL300973	Software / Product Manual	EL300971
Adobe <sup>®</sup> PostScript <sup>®</sup> 3™ Kit lal	bel ED201136		

#### Consumables

Consumables					
Product Name	Product Code	Product Life			
Drum Cartridge Black (Starter)	—	Up to 60,000 pages*1			
Drum Cartridge Cyan (Starter)	—	Up to 60,000 pages*1			
Drum Cartridge Magenta (Starter)	_	Up to 60,000 pages*1			
Drum Cartridge Yellow (Starter)	_	Up to 60,000 pages*1			
Drum Cartridge Black	CT351398	Up to 60,000 pages*1			
Drum Cartridge Cyan	CT351399	Up to 60,000 pages*1			
Drum Cartridge Magenta	CT351400	Up to 60,000 pages*1			
Drum Cartridge Yellow	CT351401	Up to 60,000 pages*1			
Toner Cartridge Black (Starter)	—	Up to 7,000 pages*2			
Toner Cartridge Cyan (Starter)	_	Up to 5,000 pages*2			
Toner Cartridge Magenta (Starter)	_	Up to 5,000 pages*2			
Toner Cartridge Yellow (Starter)	_	Up to 5,000 pages*2			
Toner Cartridge Standard Black	CT203974	Up to 7,000 pages*2			
Toner Cartridge Standard Cyan	CT203975	Up to 5,000 pages*2			
Toner Cartridge Standard Magenta	CT203976	Up to 5,000 pages*2			
Toner Cartridge Standard Yellow	CT203977	Up to 5,000 pages*2			
Toner Cartridge High-capacity Black	CT203978	Up to 15,000 pages*2			
Toner Cartridge High-capacity Cyan	CT203979	Up to 11,000 pages*2			
Toner Cartridge High-capacity Magenta	CT203980	Up to 11,000 pages*2			
Toner Cartridge High-capacity Yellow	CT203981	Up to 11,000 pages*2			
Fusing unit 220v	CWAA1064	Up to 100,000 pages			
Transfer Module	CWAA0960	Up to 100,000 pages			
Waste Toner Container	CWAA1010	Up to 30,000 pages*3			
Paper Roller Kit	CWAA1013	Up to 100,000 pages			

 Paper Roller Kit
 CWAA1013
 Up to 100,000 pages

 \*1: The number of printable pages is a reference value derived from the average of 3 sheets printed in A4, 1 sided, image coverage per colour 5 %, Colour/Monochrome rate 50 : 50 in one setting, under continuous printing usage conditions. The actual number of printable pages may vary to below half the reference value, depending on paper type, paper direction, input/output tray settings, initialization operations upon powering ON/OFF the device, tuning operations to maintain print quality, and other such usage environment conditions.

 \*2: Published value based on ISO/IEC 19798 standards. The actual number of printable pages may vary significantly from the published value, depending on printing content, paper size, paper type, usage conditions, initialization operations upon powering ON/OFF the device, tuning operations to maintain print quality, and other such usage environment conditions.

 \*3: The number of printable pages is a reference value when printing in A4, 1 sided, image coverage per colour 5 %, Colour/Monochrome rate 50 : 50. The actual number of printable pages may vary significantly from the reference value, depending on printing content, that the type, usage conditions, initialization operations upon powering ON/OFF the device, tuning operations to maintain print quality, and other such usage coverage per colour 5 %, Colour/Monochrome rate 50 : 50. The actual number of printable pages may vary significantly from the reference value, depending on printing content, paper size, paper type, usage conditions, initialization operations upon powering ON/OFF the device, tuning operations to maintain print quality, and other

powering ON/OFF the device, tuning operations to maintain print quality, and other such usage environment conditions.

Notes 1. To comply with paper weight specifications, it is recommended to use our recommended paper 2. For comply may not be printed correctly depending on usage conditions. Document may not be printed correctly depending on usage conditions. 2. Functional spare parts will be available for at least 7 years after the product is no longer manufactured.

The available model varies depending on the country/region. Please ask the sales representatives for details

The product specifications, appearance and other details in this brochure are subject to change without notice for improvements.

Reproduction Prohibitions Please note that reproduction of the following is prohibited by law : •Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. •Unused postage stamps, post cards, etc. •Certificate stamps stipulated by law. •Reproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, drawings, photographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

the purpose of personal use, family use or ourer similar uses within a minuted unce. **Trademarks** •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •ApeosPrint and DocuWorks are registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •Adobe, Adobe logo, PostScript and PostScript logo are either registered trademarks or trademarks of Adobe in the United States and/or other countries. •Mopria the Mopria Logo, and the Mopria Alliance word mark and logo are registered and/or unregistered trademarks and the service marks of Apple Inc. registered in the U.S. and other countries. •Apple AirPrint and Mac are trademarks of Apple Inc. registered in the U.S. and other countries and regions. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

#### For Your Safety

Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection. Otherwise electronic shock may result in the case of a failure or short circuit.