






Small in size with enhanced user experience and seamless connectivity

The Apeos 2150 provide improved features for better performance and productivity.

Productivity

One-Pass Duplex Scan


Quick scanning improved longevity and energy efficient operation with one single pass scan.



ID Card Copying

Single Card Mode

Automatic straightening and centralise skewing saves significant amount of time for the operator and improves overall productivity.



Multiple Mode

Automatically aligns multiple ID card copying




Aligns & prints multiple cards.



Cards & different sized IDs (e.g. passports) can also be copied at the same time.

Custom Size Paper Output

Different processes require different media size. With the new customisation feature, paper size can be adjusted according to your work processes for desired agility.



*Only with Bypass Tray

Colour Scanning

Colour scanning can be done directly from a PC. Digitalise your edited notes in full colour for easy review and time saving.



Note: Format such as PDF/JPEG/PNG can be selected.

Auto Print Out Rotation

Easy collation of multiple print sets for ease of handling and distribution.

Note: If you set the paper in Tray1 with SEF, the paper in Tray2 or Bypass Tray must be set with LEF.

(LEF/SEF: Long Edge Feed/ Short Edge Feed)



Sorted & ready to take from the center tray.

Performance

Copy / Print

21 ppm

Scan*

Colour: 38 ppm B/W: 40 ppm

Paper Weight

60 - 216 gsm

Operability

Simple user interface for ease of operation.



Connectivity

Seamless connectivity with mobile devices for day-to-day operations to improve work efficiency.

Print Utility

Send/Receive print and scan jobs between mobile devices and the MFP.



Automatically launch the Print Utility app just by tapping on the NFC tag for direct print/scan.



Wi-Fi Direct is supported

Connect mobile devices directly to the MFP with Wi-Fi Direct to print/scan.



Configuration

Various options are available according to your needs.







DADF model

Platen model

		Apeos 2150 NDA	Apeos 2150 ND
Print Speed		21 ppm	21 ppm
Automatic Document Feeder		Standard	Optional
Duplex Unit		Standard	Standard
Copy (Monochrome)		Standard	Standard
Print	USB / LAN	Standard	Standard
(Monochrome)	Wi-Fi	Optional	Optional
Scan (Colour)	USB / LAN	Standard	Standard
	Wi-Fi	Optional	Optional

The compatible with the environment

It fits in with the RoHS order. Also, TEC value*1 being rarely suppressing an energy consumption 0.31 kWh achievement. It is suppressing the emission of ultrafine particle (UFP*2), too.

^{* 1} pass, 2 sided scanning: Standard Document (A4 LEF), 200 dpi, using TWAIN driver(USB)

^{*1:} The value by the measurement method which was specified by international ENERGY STAR program (Version 3.0). *2: Ultrafine Particle

Apeos 2150 NDA / Apeos 2150 ND Functions & Specifications

Basic Specifications / Copy Function

		Apeos 2150 NDA	Apeos 2150 ND	
Туре		Desktop		
Memory Capacit	.y	512 MB (Max: 512 MB)		
Storage Device C	Capacity	_		
Scan Resolution		600 x 600 dpi		
Printing Resoluti	on	600 x 600 dpi		
Warm-up Time		18 seconds or less (23 degrees Celsius room temperature)		
Recovery Time (Recovery Time from Sleep mode)		13 seconds or less (23 deg temperature)	rees Celsius room	
Original Size		Maximum of A3, 11 x 17" for both Sheet and Book		
	Max	A3, 11 x 17"		
Paper Size	Min	A5		
	Image loss width	Lead edge 5.0 mm, Trail edge 5.0 mm, Right/Left edge 5.0 mm		
Paper Weight*1	Paper Tray	60 to 90 gsm		
Paper Weight	Bypass Tray	60 to 216 gsm		
First Copy Outpu	ıt Time	7.4 sec. (A4 LEF)		
	A4 LEF / JIS B5 LEF	21 ppm		
Continuous	JIS B5	12 ppm		
Copy Speed*2	A4	15 ppm		
Speed	JIS B4	12 ppm		
	A3	10 ppm		
D T	Standard	250 sheets x 1-tray + Bypas	ss Tray 100 sheets	
Paper Tray Capacity*3	Optional	One Tray Module: 500 sheets		
Сарасіту	Max	850 sheets (Standard + One Tray Module)		
Output Tray Cap	acity* ³	250 sheets (A4 LEF)		
Power Supply		AC220-240 V +/- 10 %, 6 A	, 50/60 Hz common	
		1.3 kW (AC220 V +/- 10%)	1.3 kW (AC220 V +/- 10%)	
Mayinguna Dayya	Canaumantian	1.4 kW (AC240 V +/- 10%)	1.4 kW (AC240 V +/- 10%)	
Maximum Powe	Consumption	Sleep mode: 0.7 W (AC220 V)	Sleep mode: 0.7 W (AC220 V)	
		Ready mode: 58 W (AC220 V)	Ready mode: 58 W (AC220 V)	
Dimensions* ⁴		W 595 x D 580 x H 559 mm (Standard)	W 595 x D 580 x H 480 mm (Standard)	
		W 595 x D 580 x H 669 mm (When One Tray Module is installed.)	W 595 x D 580 x H 590 mm (When One Tray Module is installed.)	
		W 595 x D 681 x H 1060 mm (When One Tray Module and Cabinet are installed.)	W 595 x D 681 x H 982 mm (When One Tray Module and Cabinet are installed.)	
Weight*5		32 kg	28 kg	

*1: It is recommended to use our recommended paper. Correct print output may not be possible depending on the requirement. *2: The speed may be reduced due to the image quality adjustment. The performance may be reduced depending on the paper type. *3: 80 gsm paper. *4: Excluding Power Cord. Duplex Automatic Document Feeder Extesion tray is closed. *5: Excluding Toner Cartridge.

Print Function

Item		Description
Туре		Built-in type
Continuous Print Speed		Same as the Basic Specifications / Copy Function
Printing Resolution		600 x 600 dpi
Page Description Language		HBPL (Host Based Print Language)
Supported Operating System*1		Windows 10 (32 bit / 64 bit), Windows 8.1 (32 bit / 64 bit), Windows Server 2019 (64 bit), Windows Server 2016 (64 bit), Windows Server 2012 R2 (64 bit), Windows Server 2012 (64 bit)
Interface	Standard	Ethernet 100BASE-TX / 10BASE-T, USB2.0
	Optional	Wireless LAN (IEEE 802.11 b / g / n)
	*	-

^{*1:} Please refer to our official website for the latest supported OS.

Scan Function

Item	Description
Туре	Colour Scanner
Scan Resolution	600 x 600 dpi*1, 400 x 400 dpi, 300 x 300 dpi, 200 x 200 dpi, 150 x 150 dpi
Scan Speed	Same as the Scan Speed for the Duplex Automatic Document Feeder
Interface	Same as the Print Function

^{*1:} Monochrome binary only.

Duplex Automatic Document Feeder

Item		Description
Original S Weight	iize / Paper	Max: A3, 11 x 17"; Min: A5 38 to 128 gsm (In Duplex: 50 to 128 gsm)
Capacity ³	k1	110 sheets
	Copy (A4 LEF Simplex)	B/W: 21 ppm
	Scan	B/W: 30 ppm, Colour: 26 ppm (1 pass, 2 sided scanning: B/W 40 ppm, Colour 38 ppm) [Standard Document (A4 LEF), 200 dpi, using TWAIN driver (USB)]
Dimensio	ns	W 540 x D 498 x H 125 mm
Weight		8 kg

Note: This item is standard for Apeos 2150 NDA, optional for Apeos 2150 ND. *1: 80 gsm paper. *2: The scanning speed varies depending on the documents.

One Tray Module (Optional)

(0 0.0.10.1)
Description
Max: A3, 11 x 17" Min: A5
60 to 216 gsm
500 sheets x 1-tray
W 540 x D 540 x H 111 mm
11 kg

^{*1: 80} gsm paper

Notes

Functional spare parts will be available for at least 7 years after the product is no longer manufactured

fujifilm.com/fbvn

FUJ!FILM

FUJIFILM Business Innovation Vietnam Co., Ltd.

Head Office

12th Floor, Vincom Center 72 Le Thanh Ton, Dist. 1, HCMC Tel: (84-28) 38 290 038 Fax: (84-28) 38 290 032

14th Floor, VCCI Tower 9 Dao Duy Anh, Dong Da Dist., Ha Noi Tel: (84-24) 38 241 063 Fax: (84-24) 38 241 113

Hai Phong Branch

5th Floor, TD Office Building 20A Le Hong Phong, Ngo Quyen Dist., Hai Phong Tel: (84-225) 3859 236 Fax: (84-225) 3859 239

Da Nang Branch

3rd Floor, Danabook Building 76-78 Bach Dang, Hai Chau Dist., Danang Tel: (84-236) 3892 896 Fax: (84-236) 3892 895

The available model varies depending on the country/region. Please ask the sales representatives for details.

The product specifications, appearance and other details in this brochure are subject to change without notice for improv

Reproduction Prohibitions Please note that reproduction of the following is prohibited by law: Domestic and foreign currencies, government-issued securities, and national bonds and local bond certificates. Unused postage stamps, post cards, etc. Certificate stamps stipulated by law. Reproducing works forming the subject matter of copyright (literary works, musical works, paintings, engravings, maps, cinematographic works, drawings, photographic works, etc.) is not permitted unless the reproduction is for the purpose of personal use, family use or other similar uses within a limited circle.

Trademarks •FUJIFILM and FUJIFILM logo are registered trademarks or trademarks of FUJIFILM Corporation. •Apeos is registered trademarks or trademarks of FUJIFILM Business Innovation Corp. •All product names and company names mentioned in this brochure are trademarks or registered trademarks of their respective companies.

For Your Safety



Before using the product, read the Instruction Manual carefully for proper use. Use the product with the power source and voltage specified. Be sure to establish ground connection. Otherwise, electronic shock may result in the case of a failure or short circuit.