

Movie Recording mode

Setting	Size	Movie Compression	Frame rate	Codec / YUV / Bit depth	Bit rate	Shutter Speed	
						v1.02	v2.00
DCI4K 17:9 4K 16:9	4096 x 2160 3840 x 2160	All-Intra	29.97p	H.265(HEVC) / 4:2:0 / 10bit H.264 / 4:2:0 / 8bit	400Mbps	1/8000~1/24 sec.(*3)	1/8000~1/4 sec.
			25.00p				
			24.00p				
			23.98p				
		Long-GOP	59.94p	H.265(HEVC) / 4:2:0 / 10bit H.264 / 4:2:0 / 8bit (*1)	200Mbps 100Mbps	1/8000~1/24 sec.(*3)	←
			50.00p				
			29.97p				
			25.00p				
Uncompressed (HDMI Outupt)	24.00p	— (*2) / 4:2:2 / 10bit	— (*2)	1/8000~1/24 sec.(*3)	←		
	23.98p						
	29.97p						
	25.00p						
FHD 17:9 FHD 16:9	2048 x 1080 1920 x 1080	All-Intra	59.94p	H.265(HEVC) / 4:2:0 / 10bit H.264 / 4:2:0 / 8bit	200Mbps	1/8000~1/4 sec.	←
			50.00p				
			29.97p				
			25.00p				
		Long-GOP	24.00p	H.265(HEVC) / 4:2:0 / 10bit H.264 / 4:2:0 / 8bit	200Mbps 100Mbps 50Mbps	1/8000~1/4 sec.	1/8000~1/24 sec.(*3)
			23.98p				
			59.94p				
			50.00p				
		Uncompressed (HDMI Outupt)	29.97p	— (*2) / 4:2:2 / 10bit	— (*2)	1/8000~1/4 sec.	←
25.00p							
24.00p							
23.98p							
FHD 16:9 High speed Rec.	1920 x 1080	Long-GOP	120p (2x/4x/5x) 100p (2x/4x/5x)	H.265(HEVC) / 4:2:0 / 10bit H.264 / 4:2:0 / 8bit	200Mbps (Recording)	1/8000~1/100 sec.(*3)	←

*1 Not compatible with DCI4K.

*2 Codec and bit rate will be changed depends on the recorder.

*3 Cannot choose slower shutter speed than framerate